

Product datasheet

Specifications



APC Smart-UPS C 1000VA LCD 230V

SMC1000I

! To be discontinued on: 31 December 2023

! To be end-of-service on: 31 December 2027

! To be discontinued

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Rated power in W	600 W
Rated power in VA	1000 VA
Product or component type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 320 C14
Output connection type	8 IEC 320 C13 2 IEC Jumpers
Battery type	Lead-acid battery
Provided equipment	CD with software Documentation CD USB cable

Batteries & Runtime

Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1
Battery life	3...5 year(s)
Replacement battery	APCRBC142
Battery power in VAh	170 VAh runtime
Battery charger power	56 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Entry level
Redundant	No

Physical

Colour	Black
Height	21.9 cm
Width	17.1 cm
Depth	43.9 cm
Net weight	17.27 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Input voltage limits	170...300 V adjustable 180...287 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5 % at full load
Maximum configurable power in VA	1000 VA
Maximum configurable power in W	600 W
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	CE CSA GOST VDE EAC
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic level	41 dBA
Heat dissipation	100 Btu/h
Operating altitude	0...10000 ft

Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

Control panel	Multifunction LCD status and control console
Free slots	0
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rate	455 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	37.6 cm
Package 1 Width	59.5 cm
Package 1 Length	32.8 cm
Package 1 Weight	19.55 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)

SMC1000I is replaced by:

1x



APC Smart-UPS 1000VA, Tower, LCD 230V with SmartConnect Port
SMC1000IC
