



Compact Low-maintenance SR060E





In general slip rings are used to transmit power, signals or data from a stationary to a rotating platform.

The SR060E is a compact, economical slip ring for up to 3 power and 2 signal transmissions.

New innovative contact materials ensure long service life and extremely low-maintenance operation. The round shape with smooth surfaces and high protection level allows easy cleaning.

Compact

- Dimensions 60 x 98 mm.
- · Can be used as a pair starting from just 60 mm shaft distance of the sealing rollers.
- Various component configurations for the transmission paths, max. 3 x load and 2 x signal transmission.
- · Easily accessible connections.
- · Load current up to 20 A.

Low-maintenance

- Maintenance cycles only every 100 million revolutions.
- · No contact oil required.
- Easy cleaning high protection level IP64.

Applications for slip rings

Flowpack and blister packaging machines, robots and handling equipment, rotary tables

SR060E XX V100 Order code 0 000

a Hollow shaft 20 = ø 20 mm [0.79"] 21 = ø 21 mm [0.83"] 22 = Ø 22 mm [0.87"]

24 = ø 24 mm [0.94"] 25 = ø 25 mm [0.98"] (other diameters on request)

 Number of signal / data channels 0 or 2

Number of load channels 0, 2 or 3

Max. load current 0 = no load channels

1 = 16 A, 240 V AC/DC 2 = 20 A, 240 V AC/DC

Contact material signal / data channels 0 = no signal / data channels

3 = silver / precious metal

Protection 2 = 1P64

• Version number (options) V100 = without option > V100 = option on request

| Technical data | |
|-------------------------|--|
| Hollow shaft diameter | up to max. ø 25 mm [0.98"] |
| Voltage/current loading | |
| load channels | 240 V AC/DC, max. 16 A |
| | 240 V AC/DC, max. 20 A (order option 2) |
| signal / data channels | 48 V AC/DC, max. 2 A |
| Contact resistance | |
| load channels | ≤ 1 Ohm (dynamic) 1) |
| signal / data channels | \leq 0.1 Ohm (silver / precious metal) ²⁾ |
| Insulation resistance | 10 ³ MOhm (at 500 V DC) |
| Dielectric strength | 1000 V eff. (60 sec.) |
| Speed max. | 500 min ⁻¹ |
| Torque | < 0,2 Nm |
| | |

| Service life | typ. 500 million revolutions |
|---|--|
| | (at room temperature) |
| | depends on installation position |
| Maintenance cycles | first maintenance after 50 million revolutions, |
| | all further maintenance intervals after |
| | 100 million revolutions |
| Maintenance | contact oil not required |
| | |
| Material pairing | |
| Material pairing load channels | copper / bronze |
| | copper / bronze silver / precious metal |
| load channels | The state of the s |
| load channels signal / data channels | silver / precious metal |

¹⁾ Voltage measurement, ambient temperature, DC series connection, ohmic load, min. 4 A test current.

^{2) 2-}wire resistance measurement, ambient temperature, 6.5-digit digital multimeter or similar, values without testing cable.





Slip rings


Compact Low-maintenance SR060E

Dimensions

Dimensions in mm [inch]







- 1 Screw terminal M5 for load transmission
- 2 Screw terminal M4 for signal transmission
- 3 Protective cover for the stator connections with screwed assembly (only IP64)
- 4 $\,-\,$ Flat pin connection for load transmission
- 5 Flat pin connection for signal transmission
- 6 Rotating connection ring
- 7~-~4~x~socket~set~screw~DIN~914~M6
- 8 Maintenance window
- 9 Protective cover for connections
- 10 Torque stop