

Features

- Available in E6 series
- Unit height of 8.5 mm
- Current rating up to 7.5 A
- RoHS compliant*

Applications


- Input/output of DC/DC converters
- Power supplies for:
 - · Portable communication equipment
 - · Camcorders
 - LCD TVs

SRR1208 Series - Shielded High Power Inductors


Electrical Characteristics

| | Inductance 1 KHz | | | Test | CDE | RDC | l rms | I sat |
|-----------------|------------------|--------|-----------|--------------------|----------------------|-------------|-------------|-------|
| Bourns Part No. | (µH) | Tol. % | Q Ref. | Frequency (MHz) | SRF Min. (MHz) | Max. (Ω) | Max. (A) | Typ. |
| SRR1208-2R5ML | 2.5 | ± 20 | 20 | 7.96 | 37 | 0.011 | 7.50 | 10.00 |
| SRR1208-4R5ML | 4.5 | ± 20 | 24 | 7.96 | 30 | 0.014 | 6.50 | 10.00 |
| SRR1208-6R5ML | 6.5 | ± 20 | 25 | 7.96 | 20 | 0.018 | 6.00 | 8.40 |
| SRR1208-100ML | 10 | ± 20 | 20 | 2.52 | 15 | 0.021 | 5.00 | 6.70 |
| SRR1208-120ML | 12 | ± 20 | 19 | 2.52 | 11 | 0.025 | 4.80 | 6.50 |
| SRR1208-150ML | 15 | ± 20 | 21 | 2.52 | 11 | 0.036 | 4.00 | 5.60 |
| SRR1208-180ML | 18 | ± 20 | 21 | 2.52 | 9.0 | 0.040 | 3.80 | 4.00 |
| SRR1208-220ML | 22 | ± 20 | 23 | 2.52 | 7.0 | 0.043 | 3.50 | 4.00 |
| SRR1208-270ML | 27 | ± 20 | 23 | 2.52 | 6.5 | 0.048 | 3.00 | 4.30 |
| SRR1208-330YL | 33 | ± 15 | 23 | 2.52 | 6.5 | 0.062 | 2.80 | 3.80 |
| SRR1208-390YL | 39 | ± 15 | 25 | 2.52 | 6.0 | 0.076 | 2.50 | 3.40 |
| SRR1208-470YL | 47 | ± 15 | 24 | 2.52 | 5.0 | 0.085 | 2.20 | 3.10 |
| SRR1208-560YL | 56 | ± 15 | 23 | 2.52 | 5.0 | 0.110 | 2.00 | 2.80 |
| SRR1208-680YL | 68 | ± 15 | 20 | 2.52 | 5.0 | 0.135 | 1.80 | 2.60 |
| SRR1208-820YL | 82 | ± 15 | 18 | 2.52 | 4.0 | 0.150 | 1.60 | 2.30 |
| SRR1208-101YL | 100 | ± 15 | 15 | 0.796 | 4.0 | 0.170 | 1.50 | 2.10 |
| SRR1208-121YL | 120 | ± 15 | 15 | 0.796 | 3.0 | 0.190 | 1.40 | 2.00 |
| SRR1208-151YL | 150 | ± 15 | 14 | 0.796 | 3.0 | 0.240 | 1.30 | 1.72 |
| SRR1208-181YL | 180 | ± 15 | 14 | 0.796 | 2.5 | 0.270 | 1.20 | 1.70 |
| SRR1208-221KL | 220 | ± 10 | 13 | 0.796 | 2.5 | 0.380 | 1.10 | 1.45 |
| SRR1208-271KL | 270 | ± 10 | 13 | 0.796 | 2.0 | 0.400 | 0.95 | 1.25 |
| SRR1208-331KL | 330 | ± 10 | 13 | 0.796 | 1.8 | 0.650 | 0.85 | 1.12 |
| SRR1208-391KL | 390 | ± 10 | 14 | 0.796 | 1.6 | 0.670 | 0.80 | 1.10 |
| SRR1208-471KL | 470 | ± 10 | 14 | 0.796 | 1.4 | 0.850 | 0.70 | 0.95 |
| SRR1208-561KL | 560 | ± 10 | 14 | 0.796 | 1.4 | 0.900 | 0.65 | 0.90 |
| SRR1208-681KL | 680 | ± 10 | 13 | 0.796 | 1.2 | 1.00 | 0.60 | 0.82 |
| SRR1208-821KL | 820 | ± 10 | 12 | 0.796 | 1.2 | 1.15 | 0.55 | 0.77 |
| SRR1208-102KL | 1000 | ± 10 | 11 | 0.252 | 1.0 | 1.65 | 0.50 | 0.67 |
| SRR1208-122KL | 1200 | ± 10 | 10 | 0.252 | 0.80 | 2.00 | 0.40 | 0.57 |
| SRR1208-152KL | 1500 | ± 10 | 10 | 0.252 | 0.75 | 2.35 | 0.36 | 0.55 |
| SRR1208-182KL | 1800 | ± 10 | 20 | 0.252 | 0.70 | 3.40 | 0.46 | 0.48 |
| SRR1208-222KL | 2200 | ± 10 | 20 | 0.252 | 0.65 | 4.20 | 0.40 | 0.42 |
| SRR1208-272KL | 2700 | ± 10 | 20 | 0.252 | 0.60 | 5.20 | 0.35 | 0.38 |
| SRR1208-332KL | 3300 | ± 10 | 20 | 0.252 | 0.50 | 6.40 | 0.32 | 0.35 |
| SRR1208-392KL | 3900 | ± 10 | 20 | 0.252 | 0.45 | 7.80 | 0.30 | 0.32 |
| SRR1208-472KL | 4700 | ± 10 | 20 | 0.252 | 0.42 | 9.60 | 0.28 | 0.30 |
| SRR1208-562KL | 5600 | ± 10 | 18 | 0.252 | 0.40 | 12.0 | 0.25 | 0.28 |
| SRR1208-682KL | 6800 | ± 10 | 18 | 0.252 | 0.38 | 15.2 | 0.22 | 0.25 |
| SRR1208-822KL | 8200 | ± 10 | 16 | 0.252 | 0.35 | 17.0 | 0.20 | 0.22 |
| SRR1208-103KL | 10000 | ± 10 | 24 | 0.0796 | 0.30 | 19.2 | 0.18 | 0.20 |

Schematic




Recommended Layout



| General Specifications |
|--------------------------------|
| Test Voltage1 V |
| Operating Temperature |
| 40 °C to +125 °C |
| (Temperature rise included) |
| Storage Temperature |
| 40 °C to +125 °C |
| Resistance to Soldering Heat |
| 260 °C for 5 sec. |
| Rated Current |
| Ind. drop of 10 % typ. at Isat |
| Temperature Rise |
| 40 °C max. at rated Irms |
| |
| Materials |
| |

Core.....Ferrite DR & RI core Wire Enameled copper BaseLCP E4008 Terminal Cu/Ni/Sn


Packaging......400 pcs. per reel







*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011. Specifications are subject to change without notice. Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Packaging Specifications







DIMENSIONS: $\frac{MM}{(INCHES)}$

BOURNS®

Asia-Pacific: Tel: +886-2 2562-4117 • Email: asiacus@bourns.com

EMEA: Tel: +36 88 520 390 • Email: eurocus@bourns.com

The Americas: Tel: +1-951 781-5500 • Email: americus@bourns.com

www.bourns.com

Legal Disclaimer Notice



This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns® product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification. Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns® products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns® standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns® standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns® standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns® standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns® standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Users shall not sell, transfer, export or re-export any Bourns® products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns® products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: http://www.bourns.com/legal/disclaimers-terms-and-policies

PDF: http://www.bourns.com/docs/Legal/disclaimer.pdf

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

SRR1208-820YL SRR1208-560YL SRR1208-180ML SRR1208-221KL SRR1208-270ML SRR1208-100ML

SRR1208-4R5ML SRR1208-390YL SRR1208-2R5ML SRR1208-220ML SRR1208-561KL SRR1208-821KL

SRR1208-391KL SRR1208-271KL SRR1208-120ML SRR1208-6R5ML SRR1208-181YL SRR1208-150ML

SRR1208-152KL SRR1208-331K SRR1208-152K SRR1208-821K SRR1208-2R5M SRR1208-151K SRR1208-475ML

SRR1208-220M SRR1208-391K SRR1208-180M SRR1208-470Y SRR1208-102K SRR1208-101K

SRR1208-270M SRR1208-272KL SRR1208-472KL SRR1208-562KL SRR1208-332KL SRR1208-330YL SRR1208-101KL SRR1208-101YL SRR1208-102KL SRR1208-331KL SRR1208-121YL SRR1208-470YL SRR1208-471KL

SRR1208-681KL SRR1208-680KL SRR1208-680YL SRR1208-151YL SRR1208-151KL SRR1208-222KL SRR1208-330Y SRR1208-271K SRR1208-680K SRR1208-151YL SRR1208-390Y SRR1208-150M SRR1208-820Y SRR1208-330Y SRR1208-221K SRR1208-471K SRR1208-181Y SRR1208-101Y SRR1208-561K SRR1208-100M SRR1208-560Y SRR1208-685M SRR1208-121Y SRR1208-101Y SRR1208-392KL SRR1208-100M SRR1208-560Y SRR1208-685M SRR1208-121Y SRR1208-120M SRR1208-392KL SRR1208-100M SRR1208-560Y SRR1208-682KL SRR1208-121Y SRR1208-182KL SRR1208-392KL SRR1208-103KL