

# ENSTO

## SPCM181815T

### Cubo S enclosure

Code SPCM181815T  
 GTIN 6418677166655  
 Name Cubo S enclosure Ensto Cubo S  
 Size 175 x 175 x 150 mm, 50 mm base,  
 metric knockouts, transparent cover, PC

Description Ensto Cubo S is a series of small to medium size enclosures available with knockouts or plain sides. The base of the enclosures is equipped with unique slots for printed circuit boards.



## Technical specification

### Technical specification

**Content:** Enclosure base, cover, cover screws, mounting screws

### Dimensions

**Weight:** 0.72 kg  
**Width:** 175 mm  
**Volume :** 459.38 cm<sup>3</sup>  
**Size:** 175 x 175 x 150  
**Height:** 175 mm  
**Depth:** 150 mm  
**Inner depth:** 135.5 mm  
**Outer base depth:** 50 mm  
**Outer cover height:** 100 mm

### Temperatures

**Operating temperature:** -40 ... +80 °C  
**Short term temperature range:** -40 ... +120 °C

### Materials

**Base:** Fiberglass reinforced polycarbonate  
**Cover:** Polycarbonate

<b>Cover screws:</b>	Polyamide
<b>Gasket:</b>	Polyurethane
<b>Material selection:</b>	Polycarbonate

## Colors

<b>Color:</b>	Grey
---------------	------

## Features

<b>Knockouts:</b>	4 x M12/20 + 4 x M16/25 + 10 x M12/20
-------------------	---------------------------------------

## Mechanical

<b>Impact strength:</b>	IK 08
-------------------------	-------

## Certificates

<b>Standards:</b>	EN 62208, GOST R
-------------------	------------------

## Ratings

<b>Degree of protection:</b>	IP66/IP67
<b>Flammability rating:</b>	UL 746C 5 inch flame test
<b>ETIM class:</b>	EC000261

## ETIM

---

### ETIM

<b>Width:</b>	175 mm
<b>Colour:</b>	Grey
<b>Material:</b>	Plastic
<b>Height:</b>	175 mm
<b>Depth:</b>	150 mm
<b>Type of surface:</b>	Untreated
<b>RAL-number:</b>	7035
<b>Wall fastening possible:</b>	true
<b>Suitable for outdoor set-up:</b>	true
<b>Impact strength:</b>	IK08
<b>Degree of protection (IP):</b>	IP67
<b>Pole fastening:</b>	false
<b>With glazed door:</b>	false
<b>Tackable:</b>	false
<b>Wall build in:</b>	false
<b>Pitched roof:</b>	false
<b>EMC-version:</b>	false
<b>With ventilation door:</b>	false
<b>With backside door:</b>	false
<b>Floor installation possible:</b>	false

## Packaging

---

### Default package

<b>Unit:</b>	PCS
<b>Size:</b>	1