San Ace 160 AD 9ADW type

ACDC Fan

Features

High Airflow and High Static Pressure

This fan delivers a maximum airflow of 8.2 m³/min and maximum static pressure of

Low Noise and Low Power Consumption

This fan operate with a noise level of 58 dB(A) and power consumption of 22 W. Also, the PWM control function enables the control of fan speed, contributing to lowering noise and improving energy efficiency of devices.

Wide Operating Voltage Range

This fan has an input voltage range of 100 to 240 VAC, supporting both 100 and 200 VAC systems.

Water and Dust Protection

This fan achieves excellent IP56* water and dust protection, maintaining stable operation in harsh environments.

*The degree of protection (IP code) is defined by IEC 60529 (International Electrotechnical

Commission).
The protection rating applies only to electrical components (motor coils and electronic components) in our fans.
The mechanical components other than the electrical components are not subject to



160 x 160 x 51 mm

Specifications

Lead wire model

The models listed below have pulse sensors with PWM control function.

Model no.	Rated voltage [V]	Operating voltage range [V]	Frequency [Hz]	PWM duty cycle* [%]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. a [m³/min]	irflow [CFM]	Max. stat	tic pressure [inchH ₂ O]	SPL [dB(A)]	Operating temperature [°C]	Expected life [h]
9ADW1601P5H003	100 to 240	90 to 264	50/60	100	0.46	22	4150	8.2	290	167	0.66	58	-20 to +70	40000/60°C
SADWIOUIFSHUUS	100 to 240	30 10 204	30/00	0	0.10	4.0	1500	3.07	108	44	0.17	31	-20 10 +70	(70000/40°C)

^{*} PWM frequency is 25 kHz. Models without ratings for 0% PWM duty cycle have zero speed at 0%. When control terminal is open, speed is the same as at 0% duty cycle.

The models listed below have no sensors.

1110 1110 4010 1101												
Model no.	Rated voltage [V]	Operating voltage range [V]	Frequency [Hz]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. airflow [m³/min] [CFM]	Max. st [Pa]	atic pressure [inchH ₂ O]	SPL [dB(A)]	Operating temperature [°C]	Expected life [h]
9ADW1601H5002	100 to 240	90 to 264	50/60	0.46	22	4150	8.2 290	167	0.66	58	-20 to +70	40000/60°C (70000/40°C)

Terminal model

The models listed below have pulse sensors with PWM control function.

Model no.	Rated voltage [V]	Operating voltage range [V]	Frequency [Hz]	PWM duty cycle* [%]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. a [m³/min]	irflow [CFM]	Max. stat [Pa]	tic pressure [inchH ₂ O]	SPL [dB(A)]	Operating temperature [°C]	Expected life [h]
9ADW1601P5HT03	100 to 240	90 to 264	50/60	100	0.46	22	4150	8.2	290	167	0.66	58	-20 to +70	40000/60°C
9ADW 1001F3H103	100 to 240	90 10 204	50/60	0	0.10	4.0	1500	3.07	108	44	0.17	31	-20 10 +70	(70000/40°C)

^{*} PWM frequency is 25 kHz. Models without ratings for 0% PWM duty cycle have zero speed at 0%. When control terminal is open, speed is the same as at 0% duty cycle.

The models listed below have no sensors.


Model no.	Rated voltage [V]	Operating voltage range [V]	Frequency [Hz]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. air [m³/min]	rflow [CFM]	Max. stat [Pa]	ic pressure [inchH ₂ O]	SPL [dB(A)]	Operating temperature [°C]	Expected life [h]
9ADW1601H5T02	100 to 240	90 to 264	50/60	0.46	22	4150	8.2	290	167	0.66	58	-20 to +70	40000/60°C (70000/40°C)


Models with the following sensor specifications are also available as options: Lock sensor Low-speed sensor

Common Specifications —	
-	
	Frame: Aluminum (Black coating), Impeller: Plastic (Flammability: UL 94V-0)
☐ Expected life · · · · · · · · · · · · · · · · · · ·	Refer to specifications
	(L10 life: 90% survival rate for continuous operation in indoor free air at 60°C, rated voltage)
	Expected life at 40°C is for reference only.
☐ Motor protection function · · · · · · · · · ·	· ·
Dielectric strength · · · · · · · · · · · · · · · · · · ·	·
_ Dicicettie strength	30/00 TIZ, 1300 VAO, 101 1 Hilliate
	(Lead wire model: between lead wire conductors and frame, Terminal model: between terminal and frame)
☐ Insulation resistance · · · · · · · · · · · · · · · · · · ·	10 MO min. at 500 VDC
	(Lead wire model: between lead wire conductors and frame, Terminal model: between terminal and frame)
□ C	·
	A-weighted sound pressure level (SPL) at 1 m away from the air inlet.
Operating temperature · · · · · · · · · · · · · · · · · · ·	
Storage temperature · · · · · · · · · · · · · · · · · · ·	-30 to +70°C (Non-condensing)
Lead wire	(AC power input) L: Orange N: Gray
	Sensor Yellow (Control) Brown (GND) Black
☐ Mass ······	
☐ Ingress protection ······	IP56 (Excluding the connectors of terminal models)

San Ace 160 AD SADW type


■ Airflow - Static Pressure Characteristics






SADWI

PWM Duty - Speed Characteristics Example



PWM Input Signal Example


Input signal waveform



$$V_{IH}=4.75$$
 to 5.25 V $V_{IL}=0$ to 0.4 V
PWM duty cycle (%) = $\frac{T_1}{T} \times 100$ PWM frequency 25 (kHz) = $\frac{1}{T}$ Current source (Isource) = 1.0 mA max. (when control voltage is 0 V)
Current sink (Isink) = 10 mA max. (when control voltage is 5.25 V)


When the PWM control terminal is open, the fan speed is the same as the speed at 0% PWM duty cycle. A TTL input can be used for the PWM input signal.

Example of Connection Schematic



Specifications for Pulse Sensors


Output circuit: Open collector




 V_{CE} = +60 V max. Ic=10 mA max. [V_{OL}=V_{CE} (SAT)=1.2 V max.]

Output waveform (Need pull-up resistor)


In case of steady running



Dimensions (unit: mm) (With pulse sensor with PWM control function)



Terminal model M4×0.7 Depth 6






A Connector contact


No.3 No.1

Pin arrangement Connector (Model no.:TE Connectivity: 1-172160-9)

Connector (woder no 12 Connectivity. 1-172100-3)								
Function	Input							
L	AC							
No connection	-							
N	AC							
PWM	DC							
GND	DC							
Sensor	DC							
	Function L No connection N PWM GND							

Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)





Options

Finger guards

Terminal model wiring harness

Model no.: 109-619E, 109-619H, 109-620 Model no.: 489-1647

Notice

- ●Please read the "Safety Precautions" on our website before using the product.
- The products shown in this catalog are subject to Japanese Export Control Law. Diversion contrary to the law of exporting country is prohibited.

For protecting fan bearings against electrolytic corrosion near strong electromagnetic noise sources, we provide effective countermeasures such as Electrolytic Corrosion Proof Fans and EMC guards. Contact us for details.

SANYO DENKI CO., LTD.

3-33-1 Minami-Otsuka, Toshima-ku, Tokyo 170-8451, Japan TEL: +81 3 5927 1020

https://www.sanyodenki.com/