

3-348-843-03 5/11.04

- Very short response times thanks to BET technology (bidirectional energy transformation)
- · Auto-ranging output with 120 W, 240 W or 320 W
- Output power is doubled in short-time operating range
- Minimum residual ripple
- · Very good dynamic control parameters
- Addressable RS 232 interface / analog interface as standard equipment
- Optional IEEE 488 interface
- Integrated sequence function for the generation of automatic voltage and current sequences
- · Calibration procedure for menu-driven balancing
- Output ON / OFF function
- Output terminals at front and rear panels
- Master-slave operation for parallel and series connection
- · Protection against overvoltage, overcurrent and excessive temperature
- Minimal power loss







### **Description**

The SSP KONSTANTER series (single output system power supplies) includes programmable, voltage and current regulated DC power supplies with 120 W, 240 W or 320 W of output power. They include a  $\mu P\text{-controlled}$  operating system and are furnished with an addressable RS 232C serial interface as standard equipment. Up to 30 instruments can thus be controlled from a single PC port.

An IEEE 488 interface can be optionally integrated. Both PC interfaces allow for complete control of all instrument functions, and support the querying of measurement values, set-up parameters and instrument conditions.

Manual adjustment of voltage and current is accomplished with two rotary pulse generators with adjustable resolution.

Two 4-place multifunction displays allow for the accurate read-out of measurement values (V, A, W), as well as menu-driven parameter adjustments for a multitude of additional functions such as setting range limitation, overvoltage protection, delayed overcurrent shut-down or programmable digital signal inputs and outputs.

Up to 243 settings can be stored to memory and can be recalled either individually or sequentially, e.g. for the generation of specific current or voltage sequences. The advanced circuit technology is capable of essentially load-independent response times of less than 1 ms.

The output parameters can thus be superimposed with AC signals with values up into the kHz range with the analog interface which is furnished as standard equipment.

The measuring function is equipped with an extreme value memory, limit monitoring signals and a hold function.

# **Applications**

Electrical and electronic devices may be subjected to substantial fluctuations from the power supply depending upon where they are used, as well as ambient conditions. This is especially true where stabilization and back-up systems are not used.

A typical example is represented by automotive electrical systems during operation of the starter motor.

It is thus imperative that R&D, production and testing departments assure that electrical equipment is capable of fulfilling all required functions at any point in time under conditions of this sort

GOSSEN-METRAWATT provides you with support in fulfilling these objectives with the SSP KONSTANTER series SSP 120 / 240 / 320.

SSP-KONSTANTERs are capable of high rates of throughput, especially where automated test systems for routine testing are concerned.

The short response time assures the most accurate possible replication of quickly changing voltage or current characteristics. This allows for easy testing and simulation of the performance of load components dependent upon dynamic supply voltage.

The integrated calibration procedure and the included calibration report make the SSP KONSTANTER the ideal solution for use in ISO 9000 certified production facilities and test laboratories.

# Adjustable Functions

- Voltage and current setpoint values
- Voltage and current limit values (softlimits)
- Output ON and OFF
- Overvoltage protection threshold
- Overcurrent protection (limiting with/without shut-down)
- Delay time for overcurrent shut-down
- Power-on condition
- Reset instrument parameters
- Save instrument parameter settings
- Individual or sequential recall of instrument parameter settings
- Sequence function
- Function selection for trigger input
- Function selection for digital control outputs
- Operating parameters for measuring functions (storage of extreme values, limit value monitoring, display resolution)
- Calibration procedure
- Self-test trigger
- Operating parameters for PC interfaces (device address, SRQ masks, data rate etc.)

# **Query Functions**

- Momentary voltage, current and power measurement values
- Minimum and maximum voltage and current measurement values
- Current instrument parameter settings
- Current operating condition (control type, excessive temperature, busy)
- Events (power failure, excessive temperature, overvoltage, overload, programming error)
- Memory contents
- Device identification
- Calibration date

#### **Protection and Additional Functions**

- Sensor terminals equipped with pole reversal protection and automatic activation (auto-sensing)
- Control panel operating elements can be disabled
- Overvoltage-protected outputs
- Pole reversal protection at outputs (Sense line)
- Protection against excessive temperature
- Parameter settings memory protected with backup battery
- Master-slave link
- Inrush current limiting
- Temperature controlled fan

# **Auto-Sensing**

Switch-over to sense mode (remote sensing) is possible to compensate the voltage drop in the load conductors.

If the Sense terminals are connected to the appropriate output terminals, remote sensing is automatically activated.

Max. compensatable voltage drop: 1 V / load conductor

# **Control Panel Disabling**

The operating elements can be protected against unauthorized operation by pressing a key, with a command from the PC or with a signal to the trigger input.

# **Output Activation and Shut-Down**

The power output can be switched on and off by pressing a key, with a command from the PC or with a signal to the trigger input (no electrical isolation).

#### **Power-On Condition**

Any of the following conditions can be selected for the instrument after mains power has been switched on:

- reset = default settings (0 V, 0 A, output inactive etc.)
- recall = latest settings

(as before last disconnection from mains)

- standby = latest settings, except with inactive output

#### **Overcurrent Protection**

A selection can be made between one of the following output functions for the use of current control:

- OCP off = continuous current limiting (UI characteristic curve)
- OCP on = output is deactivated if current limiting duration exceeds DELAY time

DELAY time: adjustable from 0.00 to 99.99 sec.

#### **Trigger Selection**

The floating trigger input can be set up to control any one of the following functions at the analog interface:

- output = switch the power output on and off
- local lock = disable the control panel
- recall = step by step recall of individual settings from memory
- sequence = start / stop the SEQUENCE function
- minmax = activate and deactivate storage
  - of extreme values to memory
- off = has no effect on instrument settings, although status query is possible via PC interface

# Storage of Extreme Measurement Values

The MINMAX function automatically acquires minimum and maximum voltage and current values as they occur, and saves them to memory.

# **Limit Value Monitoring**

This function compares momentary voltage and/or current values with the adjustable limit values (HI, LO). If any of the limit values are violated, a message is read out to the PC interfaces or the digital control outputs at the analog interface.

# **Memory Function**

The memory function allows for the storage and recall of instrument settings which are protected with a backup battery. The memory includes three storage areas:

- 10 memory locations for complete instrument settings
- 243 memory locations for the SEQUENCE function (voltage setpoint value USET, current setpoint value ISET, dwell time TSET, signal status SSET)
- 2 memory locations (HI, LO) for measuring function limit monitoring

#### **SEQUENCE Function**

The SEQUENCE function allows for the automatic recall of settings which have been stored to the SEQUENCE memory.

The SEQUENCE function includes the following parameters:

START = memory location start addressSTOP = memory location stop address

- REPETITION = number of sequence repetitions (1 to 255, or 0 for continuous repetition)

- TSET = dwell time specific to the memory location


(10 ms to 99.99 s)

 TDEF = dwell time independent of the memory location (10 ms to 99.99 s)

Additional pause, abort, restart

#### Application Example:

Generation of a voltage sequence in accordance with DIN 40 839 (automotive electrical system voltage while starting the engine)



#### Comment:

Adherence to the voltage rise and drop times is only guaranteed in a restricted load resistance range.

# **Programmable Control Outputs**

The analog interface is equipped with two digital control outputs for reading out status messages to external monitoring systems, for switching external components on and off or for the creation of links

The status of the outputs can be directly defined, or can be set in accordance with the following instrument conditions:

- Output ON / OFF
- Voltage / current regulation
- Running / completed SEQUENCE function
- SSET signal status specific to the SEQUENCE step
- Measuring function limit monitoring

#### **Calibration Procedure**

The integrated calibration procedure allows for re-adjustment of setting tolerances and measuring accuracy without opening the instrument. Output parameters including voltage and current offset and upper range value, which are automatically adjusted one after the other and measured with an external precision multimeter, can be entered with the keypad or via the PC interface. The processor permanently stores these data for the correction of internal D-A and A-D converters.

# **Applicable Regulations and Standards**

IEC 61010-1/EN 61010-1/ VDE 0411-1	Safety requirements for electrical equipment for measurement, control and laboratory use
EN 60529 VDE 0470 Part 1	Test instruments and test methods Degrees of protection provided by enclosures (IP code)
DIN EN 61326 VDE 0843 Part 20	Electrical equipment for measurement, control and laboratory use – EMC requirements

### **General Characteristics**

#### Output

Termnals

Output front panel, 2 x 4 mm safety jacks

rear panel, 6-pin screw terminal block,

plug-in version

Sensor rear panel, in 6-pin screw terminal block,

plug-in version

Analog interface rear panel, 11-pin screw terminal block,

plug-in version

Controller principle Primary discontinuous-action controller

with BET-technology

Operating modes adjustable constant-voltage /


constant-current source with automatic,

sharp transition

Output isolation Floating output with "safe electrical isola-

tion" against mains input and PC interfaces; max. admissible potential output – earth 120 V; Capacitance output – earth (housing) 60 nF

#### Output operating range



#### Short-time operating range:

If the instrument is operated in the short-time range for a lengthy period of time, the excessive temperature protection system may be tripped, thus deactivating the output.

#### **Analog Interface**

Connection 11-pin screw terminal block,

plug-in version

Reference Potential minus pole at output, floating TRG input

Connector Pin Assignments:

PIN	Designation	Function		
1	SIG1 OUT	digital, programmable open collector outputs		
2	SIG2 OUT	(max. 30 V— / 20 mA)		
3	TRG IN -	digital, programmable control input		
4	TRG IN +	(low: < 1.0 V, high: 4 26 V), floating input		
5	+15 V	auxiliary voltage: +15 V / max. 50 mA		
6	AGND	reference point connected to -output		
7	U <sub>set</sub> -	analog, inverted voltage control input $(0 \dots -5 \text{ V corresponds to } 0 \dots \text{U}_{nom.}, \text{Ri} = 10 \text{ k}\Omega)$		
8	U <sub>set</sub> +	analog voltage control input (0 +5 V corresponds to 0 $U_{nom.}$ , $Ri=10~k\Omega$ )		
9	I <sub>set</sub> +	analog current control input $(0 \dots +5 \text{ V corresponds to } 0 \dots \text{I}_{nom.}, \text{ Ri} = 10 \text{ k}\Omega)$		
10	U-MON	output voltage measurement output (0 10 V corresponds to 0 $U_{nom.}$ , $Ri = 9.8 \text{ k}\Omega$		
11	I-MON	output current measurement output (0 10 V correspond to 0 $I_{nom.}$ , $Ri = 9.4 \text{ k}\Omega$ )		

#### Addressable V.24/RS 232C Interface

Input 9-pin subminiature socket
Output 9-pin subminiature plug

Operating Mode half-duplex, asynchronous, XON / XOFF
Data Rate adjustable from 50 to 19,200 bits / sec.
Device Address adjustable from 0 to 30, or UNL (un-list)

Max. Setting Rate approx. 15 settings / sec.

Max. Measuring

Rate approx. 7 measurements / sec.

#### IEC 625/IEEE 488 Interface (optional)

Terminal 24-pin socket connector

per IEC 625.1, IEEE488.1

Interface SH1 SOURCE HANDSHAKE functions Handshake source function

AH1 ACCEPTOR HANDSHAKE Handshake sink function

T6 TALKER

Talker function with series query and automatic final addressing,

without secondary address and without

speak-only mode

L4 LISTENER

Listener function with automatic final addressing, without secondary address and without listen-only mode

SR1 SERVICE REQUEST Service request function

RL1 REMOTE / LOCAL

Switch-over function between remote/ manual operation with interlocking

DC1 DEVICE CLEAR

Reset function including Selected

Device Clear

PP1 PARALLEL POLL

Parallel query function with remote

setting

DT1 DEVICE TRIGGER

Trigger function

CO no controller function

E1/2 Open collector driver

Codes / Formats in compliance with IEEE 488.2

Device Address adjustable from 0 to 30, or UNL (un-list)

Max. Setting Rate approx. 40 settings / sec.

Max. Meas. Rate approx. 15 measurements / sec.

**Power Supply** 

Connectors In: 10 A IEC inlet plug connector

Out: 10 A IEC inlet socket connector,

no switch, no fuse

Line Voltage 230 V~, +10 / -15%, 47 ... 63 Hz

Power Consumption see Characteristic Values

Inrush Current max. 50 A<sub>s</sub>

Mains Fusing 1 ea. T 4 A / 250 V (6.3 x 32 mm, UL)

internal: 1 ea. T 5 A / 250 V (5 x 20 mm)

#### **Electrical Safety**

Safety Class I

Measuring Category: II for mains inlet

I for output and interfaces

Contamination Level 2

Earth Leakage Current typ. 2.5 mA

Electrical Isolation test voltage
Mains / Output-PE 1.35 kV~

Mains-Output 2.7 kV~ (type test: 3.7 kV~)

IEC 61010-1:1990 + A1:1992 / DIN EN 61010-1: 1993 /

VDE 0411-1:1994

DIN VDE 0160:1988 + A1:1989 class W1 EN 60950:1992 / VDE 0805:1990

Protection IP 20 for housing and mains terminals,

output and analog interface; IP 00 for PC interfaces per

IP 00 for PC interfaces per IEC 529: 1989

EN 60529: 1991 VDE 0470-1: 1992

Extract from table on the meaning of IP codes

IP XY (1 <sup>st</sup> digit X)	Protection against foreign object entry	IP XY (2 <sup>nd</sup> digit Y)	Protection against the penetration of water
0	not protected	0	not protected
1	≥ 50.0 mm Ø	1	vertically falling drops
2	≥ 12.5 mm Ø	2	vertically falling drops with enclosure tilted 15°

#### **Electromagnetic Compatibility EMC**

Product Standard EN 61326-1:1997 + A1: 1998 Interference Emission EN 55022:1998 class A

Interference Immunity EN 61000-4-2:1995 performance feature A

EN 61000-4-3:1996 + A1:1998

performance feature B

EN 61000-4-4:1995 performance feature B EN 61000-4-5:1995 performance feature B EN 61000-4-6:1996 performance feature B EN 61000-4-11:1994 performance feature B

#### **Ambient Conditions**

Vibration Resistance IEC 68-2-6: 1990

10 ... 55 Hz, 0.3 mm, 1 oct. / min. 3 x 30 min.

Impact Resistance IEC 68-2-27: 1989

15 gr., 11 ms, semi-sinusoidal, 3 x 6 impacts

Temperature Range operation: 0 ... 50° C at > 40° C current derating

storage: -25 ... +75° C

Humidity operation: ≤ 75% relative humidity,

no condensation allowed

Cooling with built-in fan

air intake: side panel / air outlet: rear panel

# **Mechanical Design**

Type benchtop instrument, suitable for rack mounting

Dimensions

(W x H x D) benchtop unit: 221.5 x 102 x 397.5 mm


19" rack unit: 1/219" x 2 standard height

units x 400 mm

Weight benchtop unit: approx. 2.8 kg

IEEE 488 interface (option): approx. 0.1 kg

#### **Dimensional Drawing (benchtop instrument)**



# **Electrical Values, 120 W Series**

- Unless otherwise indicated, all data represent maximum values and are valid within an operating temperature range of 0 to 50° C, the nominal power range and a line voltage range of 230 V  $\pm$  10% after a warm-up period of 30 minutes.
- Percentages refer to the respective setting value or measured value

Description (abbreviated designation)		SSP 120-20	SSP 120-40	SSP 120-80
Туре		32 N 20 RU 10 P	32 N 40 RU 6 P	32 N 80 RU 3 P
Nominal Output Data	Voltage Setting Range	0 20 V	0 40 V	0 80 V
	Current Setting Range	0 10 A	0 6 A	0 3 A
	Continuous Power at Tu ≤ 40° C	max. 120 W	max. 120 W	max. 120 W
Short-Ti	me Rating for t < 90 s / Tu ≤ 25° C	max. 200 W	max. 240 W	max. 240 W
	Current Derating at Tu > 40° C	– 0.25 A / K	- 0.15 A / K	– 0.07 A / K
Output Operating Characteristics				
Setting Resolution [display (< $10.00 / \ge 10.00$ ), remote]	Voltage Current	5 mV / 10 mV, 5 mV 2.5 mA	10 mV 2 mA	20 mV 1 mA
Overall Setting Tolerance at 23 $\pm$ 5° C including System Deviation for Load / Line	Voltage Current	0.15% + 30 mV 0.4% + 35 mA	0.15% + 40 mV 0.5% + 20 mA	0.15% + 80 mV 0.5% + 10 mA
Static System Deviation <sup>1)</sup> at 100% Load Variation <sup>1)</sup>	Voltage Current	15 mV 20 mA	10 mV 10 mA	10 mV 10 mA
Static System Deviation <sup>1)</sup> at 10% Line Voltage Variation <sup>1)</sup>	Voltage Current	5 mV 8 mA	5 mV 5 mA	5 mV 5 mA
Residual Ripple 1)	Voltage (10 Hz 10 MHz) Current (10 Hz 1 MHz)	10 mV <sub>rms</sub> 25 mA <sub>rms</sub>	10 mV <sub>rms</sub> 20 mA <sub>rms</sub>	10 mV <sub>rms</sub> 10 mA <sub>rms</sub>
Common-Mode Interference (10 Hz 1 MHz)		0.5 mA <sub>rms</sub>	0.5 mA <sub>rms</sub>	0.5 mA <sub>rms</sub>
Settling Time (voltage) with Sudden Load Variations of 10 to 90% I <sub>nom.</sub>	Tolerance $\Delta I = 80\%$	40 mV 200 μs	80 mV 200 μs	160 mV 200 μs
Under and Overshooting with Sudden Load Variations of 50 A / ms	$\Delta$ I = 80%	400 mV	400 mV	800 mV
Response Time (voltage) with Setpoint Change $0 \rightarrow 100\%$ with Setpoint Change $100\% \rightarrow 0$	Tolerance Open-Circuit / Nominal Load Open-Circuit / Nominal Load	40 mV 1 ms / 1 ms 1 ms / 1 ms	80 mV 1 ms / 1 ms 1 ms / 1 ms	160 mV 4 ms / 4 ms 4 ms / 4 ms
Response Time (current) with Setpoint Change $0 \rightarrow 100\%$ with Setpoint Change $100\% \rightarrow 0$	Tolerance Short-Circuit / Nominal Load Short-Circuit / Nominal Load	100 mA < 5 ms / < 5 ms < 5 ms / < 5 ms	60 mA < 5 ms / < 5 ms < 5 ms / < 5 ms	30 mA < 10 ms / < 10 ms < 10 ms / < 10 ms
Measurement Value Display (4-place)				
Measuring Resolution [display (< 10.00 / ≥ 10.00), query]	Voltage Current Power	2 mV / 10 mV, 2 mV 1 mA, 1 mA 0.1 W, 0.1 W	10 mV, 4 mV 1 mA, 0.6 mA 0.1 W, 0.1 W	10 mV, 8 mV 1 mA, 0.5 mA 0.1 W, 0.1 W
Measuring Accuracy at 23 $\pm$ 5° C for Values $>$ 0.1% of Nominal Value	Voltage Current Power	0.15% + 30 mV 0.4% + 25 mA 0.55% + 0.5 W	0.15% + 40 mV 0.5% + 15 mA 0.65% + 0.6 W	0.15% + 80 mV 0.5% + 10 mA 0.65% + 0.8 W
Protective Functions				
Output Overvoltage Protection, Threshold	Setting Range Setting Resolution Setting Tolerance	0 25 V 0.1 V 2% + 0.2 V	0 50 V 0.2 V 2% + 0.4 V	0 100 V 0.4 V 2% + 0.8 V
Protection against Pole Reversal – Load Capacity	Continuous	10 A	6 A	3 A
Reverse Voltage Resistance	Continuous	40 V	80 V	100 V
General				
Power Supply 1)	Line Voltage	230 V~ +10 / -15% 47 63 Hz	230 V~ +10 / -15% 47 63 Hz	230 V~ +10 / -15% 47 63 Hz
Power Consumption	at Nominal Load in Standby Mode at max. Short-Time Power	280 VA, 180 W 45 VA, 15 W 450 VA	280 VA, 170 W 45 VA, 15 W 500 VA	280 VA, 170 W 45 VA, 15 W 500 VA
Efficiency	at Nominal Load	> 70%	> 80%	> 80%
Switching Frequency	Typical	200 kHz	200 kHz	200 kHz
Article Number		K320A	K321A	K322A

<sup>1)</sup> Indicated values are increased by a factor of approximately 1.2 within a mains input voltage range of -10% to -15%.

# Electrical Values, 240 /320 W Series

- Unless otherwise indicated, all entries represent maximum values and are valid within an operating temperature range of 0 to  $50^{\circ}$  C, the nominal power range and a line voltage range of  $230 \text{ V} \pm 10\%$  after a warm-up period of 30 minutes.
- Percentages refer to the respective setting value or measured value

SSP 240-20	SSP 240-40	SSP 240-80	SSP 320-32
32 N 20 RU 20 P	32 N 40 RU 12 P	32 N 80 RU 6 P	32 N 32 RU 18 P
0 20 V	0 40 V	0 80 V	0 32 V
0 20 A	0 12 A	0 6 A	0 18A
max. 240 W	max. 240 W	max. 240 W	max. 320 W
max. 320 W	max. 360 W	max. 360 W	max. 430 W
– 0.5 A / K	-0.3 A / K	– 0.15 A / K	- 0.5 A / K
5 mV / 10 mV; 5 mV 5 mA / 10 mA; 5 mA	10 mV 3.33 mA / 10 mA; 3.33 mA	20 mV 2 mA	10 mV 5 mA / 10 mA; 5 mA
0.15 % + 40 mV 0.5 % + 70 mA	0.15 % + 45 mV 0.5 % + 45 mA	0.15 % + 80  mV 0.5 % + 25  mA	0.15 % + 50 mV 0.5 % + 70 mA
25 mV 30 mA	18 mV 30 mA	18 mV 15 mA	30 mV 40 mA
5 mV 8 mA	5 mV 8mA	5 mV 5 mA	10 mV 20 mA
15 mV <sub>eff</sub> 50 mA <sub>eff</sub>	15 mV <sub>eff</sub> 25 mA <sub>eff</sub>	15 mV <sub>eff</sub> 20 mA <sub>eff</sub>	$$30\text{mV}_{\text{eff}}$$ $50\text{mA}_{\text{eff}}$ (Ja $>10\%\text{U}_{\text{nen}}$
0.5 mA <sub>eff</sub>	0.5 mA <sub>eff</sub>	0.5 mA <sub>eff</sub>	0.5 mA <sub>eff</sub>
40 mV 600 μs	80 mV 300 μs	160 mV 200 μs	64 mV 500 μs
450 mV	450 mV	800 mV	450 mV
40 mV 1 ms / 1 ms 1 ms / 1 ms	80 mV 1 ms / 1 ms 1 ms / 1 ms	160 mV 4 ms / 4ms 4 ms / 4ms	64 mV 1 ms / 1 ms 1 ms / 1 ms
200 mA < 5 ms / < 5 ms < 5 ms / < 5 ms	120 mA < 5 ms / < 5 ms < 5 ms / < 5 ms	60 mA < 10 ms / < 10 ms < 10 ms / < 10 ms	180 mA < 5 ms / < 5 ms < 5 ms / < 5 ms
2 mV / 10 mV; 2 mV 2 mA; 10 mA; 2 mA	10 mV; 4 mV 2 mA / 10 mA; 1.2 mA	10 mV; 8 mV 1 mA; 0.6 mA	10 mV; 4 mV 2 mA; 10 mA; 2 mA 0.1 W; 0.1 W
0.15 % + 40 mV 0.5 % + 70 mA 0.65 % + 1.4 W	0.15 % + 40 mV 0.5 % + 25 mA 0.65 % + 1 W	0.15 % + 80 mV 0.5 % + 15 mA 0.65 % + 1.2 W	0.15 % + 40 mV 0.5 % + 70 mA 0.65 % + 1.4 W
0 25 V 0.1 V 2 % + 0.2 V	0 50 V 0.2 V 2 % + 0.4 V	0 100 V 0.4 V 2 % + 0.8 V	0 40 V 0.2 V 2 % + 0.4 V
20 A	12 A	6 A	18 A
40 V	80 V	100 V	64 V
230 V~ +10 / -15 % 47 63 Hz	230 V~ +10 / -15 % 47 63 Hz	230 V~ +10 / -15 % 47 63 Hz	230 V~ +10 / -15 % 47 63 Hz
510 VA; 350 W 45 VA; 15 W 620 VA	500 VA; 340 W 45 VA; 15 W 690 VA	500 VA; 340 W 45 VA; 15 W 690 VA	650 VA; 460 W 50 VA; 15 W 770 VA
> 68 %	> 70 %	> 70 %	> 69 %
200 kHz	200 kHz	200 kHz	200 kHz
K330A	K331A	K332A	K334A

<sup>1)</sup> Indicated values are increased by a factor of approximately 1.2 within a mains input voltage range of -10% to -15%.

### **Order Information**

Description (Short-Form)	Туре	Article No.
SSP 120-20	32 N 20 RU 10 P	K320A
SSP 120-40	32 N 40 RU 6 P	K321A
SSP 120-80	32 N 80 RU 3 P	K322A
SSP 240-20	32 N 20 RU 20 P	K330A
SSP 240-40	32 N 40 RU 12 P	K331A
SSP 240-80	32 N 80 RU 6 P	K332A
SSP 320-32	32 N 32 RU 18 P	K334A
IEEE488-Interface	for SSP-KONSTANTER Types 32 N, Weight: 172 g, Mass: 150 x 100 x 60 (L x W x H)	K380A

### **Accessories**

#### Mounting

Description	Comment	Article No.
19" Adapter, 1 x 32 N	Required for mounting 1 type 32 N instrument to a 19" rack Weight: 214 g (packed in polyethylene bag)	K990A
19" Adapter, 2 x 32 N	Required for mounting 2 type 32 N instruments to a 19" rack Weight: 50 g (packed in polyethylene bag)	K990B
Mains Jumper Cable, 0.4 meters long	The cable is equipped with one 10 A inlet connector plug and one 10 A inlet connector socket.  Used for cascading mains power when several instruments are mechanically connected to a single multi-channel unit. The system thus requires only one mains outlet.  Weight: 102 g (packed in polyethylene bag)	K991A
RS 232 Bus Cable, 0.4 meters long	For cascading the RS 232 data line when several series SSP 32N instruments are mechanically connected to a single multi-channel unit. (extension cable with 9-pin socket / 9-pin plug) Weight: 72 g (packed in polyethylene bag)	K931B
RS 232 Bus Cable, 2 meters long	For connecting one instrument to an RS 232 interface. (extension cable with 9-pin socket / 9-pin plug) Weight: 232 g (packed in polyethylene bag)	GTZ 3241 000 R0001
IEEE / IEEE Bus Cable, 2 meters long	For connecting an instrument to the IEEE 488 bus system Weight: 358g (packed in polyethylene bag)	K931A

#### Software (available as download from the internet)

Туре	Designation	Article No.	
K930D	LabView, device driver for SSP-KONSTANTER SSP 120, 240, 320 SSP 500, 1000, 2000, 3000	K930D	
K930E	LabWindows / CVI, device driver for SSP -KONSTANTER SSP 120, 240, 320 SSP 500, 1000, 2000, 3000	K930E	
K930F	HPVEE / VXI PnP, device driver for SSP-KONSTANTER SSP 120, 240, 320 SSP 500, 1000, 2000, 3000	K930F	

Edited in Germany ullet Subject to change without notice ullet A pdf version is available on the internet

