Cartridge Fuse, 6.3x32 mm, up to 50 A, high melting I²t





UL 248-14 · 250 VAC	100 VDC · Time-Lag T
---------------------	----------------------

Description

- Robust 6.3x32 fuse for high power and inrush current requirements

Unique Selling Proposition

- High I2t at high breaking capacity rating

- Current Range up to 50 A

See below: Approvals and Compliances

Applications

- Single-phase high current applications up to 50 A **References**

Pigtail Type SUT-H 6.3x32 Pigtail Corresponding Fuseholder

Weblinks

pdf datasheet, html-datasheet, General Product Information, Packaging details, Distributor-Stock-Check, Detailed request for product

Technical Data

Rated Voltage	250 VAC/ 100 VDC		
Rated current	10 - 50 A		
Breaking Capacity	500A - 10kA		
Characteristic	Time-Lag T		
Admissible Ambient Air Temp.	-40 °C to 85 °C		
Climatic Category	40/085/21 acc. to IEC 60068-1		
Material: Tube	Ceramic		
Material: Endcaps	Nickel-Plated Brass		
Material: Filler	Sand		
Unit Weight	2.8 g		
Storage Conditions	0 °C to 50 °C, max. 70% r.h.		
Product Marking	 Type, Rated current, Rated Voltage, Certification marks 		

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: SUT-H

Approval Logo	Certificates	Certification Body	Description
c FL us	UL Approvals	UL	UL File Number: E184831
Product standards			
Product standards that	are referenced		
Organization	Design	Standard	Description
(H)	Designed according to	UL 248-14	Low voltage fuses - Part 14: Additional fuses
CSA Group	Designed according to	CSA22.2 No. 248.14	Low-Voltage Fuses - Part 14: Supplemental Fuses

SUT-H 6.3x32


Application standards

Application standards where the product can be used

Organization	Design	Standard	Description	
IEC	Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of informatechnology equipment.	
Compliances				
The product comp	blies with following Guide Lines			
Identification	Details	Initiator	Description	
CE	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.	
RoHS	RoHS	SCHURTER AG	EU Directive RoHS 2011/65/EU	
	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.	
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.	

Dimension [mm]


- 6.3 mm



Pre-Arcing Time			
Rated Current In	1.35 x In max.	2.0 x In min.	2.0 x In max.
10 A - 50 A	60 min	5 s	60 s

SUT-H 6.3x32

Time-Current-Curves



All Variants

Rated Cur- rent [A]	Rated Vol- tage [VAC]	Rated Vol- tage [VDC]	Breaking Capacity	Voltage Drop 1.0 In typ. [mV]	Power Dissi- pation 1.0 In typ. [mW]	Melting I²t 10.0 In typ. [A²s] c R ius	Order Number
10	250	100	1)	142	1420	364 •	8020.0602.H
12	250	100	1)	114	1368	788 •	8020.0603.H
15	250	100	1)	116	1739	1058 •	8020.0604.H
20	250	100	1)	111	2213	3540 •	8020.0605.H
25	250	100	1)	99	2476	5275 ●	8020.0606.H
30	250	100	1)	109	3258	2475 •	8020.0607.H
40	250	80	2)	100	3998	5867 •	8020.0608.H
50	250	70	3)	96	4810	9908 •	8020.0609.H

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

1) 500A @ 250VAC, $\cos\!\phi$ = 0.7-0.8 / 10kA @ 125VAC , $\cos\!\phi$ = 0.7-0.8 / 500A @ 100VDC, τ <= 3ms

2) 500A @ 250VAC, $\cos\varphi$ = 0.7-0.8 / 10kA @ 125VAC , $\cos\varphi$ = 0.7-0.8 / 500A @ 80VDC, τ <= 3ms

3) 500A @ 250VAC, $\cos \phi$ = 0.7-0.8 / 10kA @ 125VAC , $\cos \phi$ = 0.7-0.8 / 500A @ 70VDC, τ <= 3ms

|--|--|

The specifications, descriptions and illustrations indicated in this document are based on current information. All content is subject to modifications and amendments. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability and test each product selected for their own applications.

Fuses

ELECTRONIC COM

29.10.2018