SANYO DENKI

San Ace 40V Splash Proof Fan



Features

High Static Pressure

This fan delivers a maximum static pressure of 555 Pa, $^{\rm (1)}$ which is about 1.38 times higher compared to our current model. $^{\rm (2)}$

Low Noise and Energy Saving

The PWM control function enables the control of fan speed, contributing to lowering noise and improving energy efficiency of devices.

Water and Dust Protection

This fan achieves excellent $\mathsf{IP68}^{\scriptscriptstyle{(3)}}$ water and dust protection, maintaining stable operation in harsh environments.

(1) For models 9WPA0412P3G001 and 9WPA0424P3G001

(3) The degree of protection (IP code) is defined by IEC 60529 (International Electrotechnical Commission) as follows.

$40 \times 40 \times 28$ mm

Specifications -

The models listed below have ribs and pulse sensors with PWM control function. For models without ribs, append "1" to the end of model numbers.

Model no.	Rated voltage [V]	Operating voltage range [V]	PWM duty cycle* [%]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. a [m³/min]	airflow [CFM]	Max. pres [Pa]	static ssure [inchH ₂ O]	SPL [dB(A)]	Operating temperature [°C]	Expected life [h]
9WPA0412P3G001	12	10.8 to 13.2	100	0.50	6.0	22200	0.63	22.2	555	2.22	53	-20 to +70	40000/60°C (70000/40°C)
			20	0.06	0.72	5000	0.14	4.9	28.1	0.11	21		
9WPA0424P3G001	24	21.6 to 26.4	100	0.25	6.0	22200	0.63	22.2	555	2.22	53		
			20	0.06	1.44	9200	0.26	9.1	95	0.38	34		

* PWM frequency is 25 kHz. Models without ratings for 0% PWM duty cycle have zero speed at 0%. When control terminal is open, speed is the same as at 100% duty cycle.

The models listed below have ribs and pulse sensors. For models without ribs, append "1" to the end of model numbers.

Model no.	Rated voltage [V]	Operating voltage range [V]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. a [m³/min]	irflow [CFM]	Max pre [Pa]	. static essure [inchH ₂ 0]	SPL [dB(A)]	Operating temperature [°C]	Expected life [h]
9WPA0412H3001	12	7 to 13.8	0.34	4.1	19500	0.52	10.2	275	1 5 1	10	20 to 170	40000/60°C
9WPA0424H3001	24	14 to 27.6	0.17	4.1	18500	0.52	10.5	375	1.01	40	-20 10 +70	(70000/40°C)

Models with the following sensor specifications are also available as options: Without sensor

Common Specifications

Material ······	Frame: Plastic (Flammability: UL 94V-0), Impeller: Plastic (Flammability: UL 94V-0)
Expected life ·····	Refer to specifications (L10 life: 90% survival rate for continuous operation in indoor free air at 60°C, rated voltage) Expected life at 40°C is for reference only.
\Box Motor protection function \cdots	Locked rotor burnout protection, Reverse polarity protection
□ Dielectric strength ······	50/60 Hz, 500 VAC, for 1 minute (between lead wire conductors and frame)
\Box Insulation resistance \cdots	10 $M\Omega$ min. at 500 VDC (between lead wire conductors and frame)
\Box Sound pressure level (SPL) $\cdots \cdots$	A-weighted sound pressure level (SPL) at 1 m away from the air inlet.
□ Operating temperature ······	Refer to specifications (Non-condensing)
□ Storage temperature ·····	-30 to +70°C (Non-condensing)
Lead wire ·····	⊕ Red ⊖ Black Sensor) Yellow Control) Brown
	(For models without PWW control function, there is no speed control wiring.)
Mass ·····	60 g
□ Ingress protection ······	IP68

San Ace 40W SWPA type

Airflow - Static Pressure Characteristics

Airflow

9WPA0412H3001



Airflow

9WPA0424H3001

PWM Duty - Speed Characteristics Example



PWM Input Signal Example

Input signal waveform



 $V_{\text{IH}} = 4.75 \text{ to } 5.25 \text{ V} \quad V_{\text{IL}} = 0 \text{ to } 0.4 \text{ V}$ PWM duty cycle (%) = $\frac{T_1}{T} \times 100$ PWM frequency 25 (kHz) = $\frac{1}{T}$

Current source (Isource) = 1.0 mA max. (when control voltage is 0 V) Current sink (Isink) = 1.0 mA max. (when control voltage is 5.25 V)

When the PWM control terminal is open, the fan speed is the same as the speed at 100% PWM duty cycle. The PWM signal can be used with open collector or drain input. Note that when using an open collector or drain input, or inputting a different voltage or frequency, the speed relative to the PWM duty cycle may differ from this specification.

Example of Connection Schematic





Specifications for Pulse Sensors



9WPA0424P3G001

Output circuit: Open collector



Ic=5 mA max. [Vol=VcE (SAT)=0.6 V max.] Rated voltage 24 V fan (Without PWM control function) VCE = +27.6 V max. Ic=5 mA max. [VoL=VCE (SAT)=0.6 V max.]



Output waveform (Need pull-up resistor)

T_{1 to 4} ≒ (1/4) T₀ T_{1 to 4} ≒ (1/4) T₀=60/4N (s) N=Fan speed (min⁻¹)



Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)



Options

Finger guards

Model no.: 109-059, 109-059H

Notice

Please read the "Safety Precautions" on our website before using the product.
The products shown in this catalog are subject to Japanese Export Control Law. Diversion contrary to the law of exporting country is prohibited.

For protecting fan bearings against electrolytic corrosion har strong electromagnetic noise sources, we provide effective countermeasures such as Electrolytic Corrosion Proof Fans and EMC guards. Contact us for details.

SANYO DENKI CO., LTD. 3-33-1 Minami-Otsuka, Toshima-ku, Tokyo 170-8451, Japan TEL: +81 3 5927 1020

https://www.sanyodenki.com/

The names of companies and/or their products specified in this document are the trade names, and/or trademarks and/or registered trademarks of such respective companies. San Ace, SANUPS, and SANMOTION are trademarks of SANYO DENKI CO., LTD.

Specifications are subject to change without notice.