# DG12

# IEC Appliance Inlet C14 with Filter, Circuit Breaker TA35 (recessed)



Screw-on with IP67



Screw-on A



Screw-on B

C14	C18		
70° C	70° C		

# Description

- Panel mount :
- Screw-on or snap-in mounting from front side
- 3 Functions :
- Appliance Inlet protection class I or II , Circuit breaker type TA35 2-pole , Line filter in standard and medical version
- Quick connect terminals 6.3 x 0.8 mm

### **Unique Selling Proposition**

- IP67 protection
- Recessed rocker switch
- Various mounting options
- V-Lock cord retaining

# Approvals and Compliances

#### **Characteristics**

See below:

- All single elements are already wired
- Circuit Breaker non-illuminated or illuminated
- Suitable for use in equipment according to IEC/UL 60950 Suitable for use in medical equipment according to IEC/UL 60601-1

#### Other versions on request

- Other rocker marking
- Medical version M80
- Capacitance CX1
- Variants in white
- Filter version with high inductance

#### References

Alternative: version without line filter DG11

#### Weblinks

pdf data sheet, html data sheet, General Product Information, Distributor-Stock-Check, Accessories, Detailed request for product, Landing Page

#### **Technical Data**

1 - 10A @ Ta 40 °C / 250 VAC; 50 Hz 1 - 15A @ Ta 40 °C / 250 VAC; 60 Hz	appliance inlet/-outlet	C14 C18 acc. to IEC 60320-1 UL 498, CSA C22.2 no. 42 (for cold		
standard < 0.5 mA (250 V / 60 Hz) medical < 5 µA (250 V / 60 Hz)		conditions) pin-temperature 70 °C, 10A, Protection Class I or II		
> 1.7 kVDC between L-N > 2.7 kVDC between L/N-PE Test voltage (2 sec)	Circuit Breakers	Acc. IEC/EN 60934, UL 1077, CSA 22.2 no. 235 2-pole rocker switch, illuminated or nor		
-25 °C to 60 °C		illuminated. Optional with undervoltage- or remote trip release		
25/060/21 acc. to IEC 60068-1		Short circuit capacity Icn: 2000 A		
from front side IP40 or IP65 / IP67 acc. to IEC 60529	Line Filter	Standard and Medical Version, IEC		
Suitable for appliances with protection		60939, UL 60939-3, CSA C22.2 no. 8 Technical Details		
Quick connect terminals 6.3 x 0.8 mm	MTBF	> 100'000h acc. to MIL-HB-217 F		
Screw: max 8 mm Mounting screw torque max 0.5 Nm : S =1.0/1.2/1.5/2.0/2.5/3.0 mm				
	$\begin{array}{l} 1-15A @ Ta 40 °C / 250 VAC; 60 Hz\\ standard < 0.5 mA (250 V / 60 Hz)\\ medical < 5 \muA (250 V / 60 Hz)\\ > 1.7 kVDC between L-N\\ > 2.7 kVDC between L/N-PE\\ Test voltage (2 sec)\\ -25 °C to 60 °C\\ \hline \\ \hline \\ \hline \\ 25/060/21 acc. to IEC 60068-1\\ from front side IP40 or IP65 / IP67 acc.\\ to IEC 60529\\ \hline \\ \\ Suitable for appliances with protection\\ class I or II acc. to IEC 61140\\ \hline \\ \\ Quick connect terminals 6.3 x 0.8 mm\\ \hline \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\$	1 - 15A @ Ta 40 °C / 250 VAC; 60 Hz         standard < 0.5 mA (250 V / 60 Hz)		

#### Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

# DG12

# Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: DG12

Approval Logo	Certificates	Certification Body	Description
10	VDE Approvals	VDE	Certificate Number: 40049092
c <b>FL</b> us	UL Approvals	UL	UL File Number: E495089

## **Product standards**

Product standards that are referenced

Organization	Design	Standard	Description
IEC.	Designed according to	IEC 60320-1	Appliance couplers for household and similar general purposes
IEC.	Designed according to	IEC 60939	Passive filters for suppressing electromagnetic interference
IEC.	Designed according to	IEC 61058-1	Switches for appliances. Part 1. General requirements
(JL)	Designed according to	UL 498	Standard for Attachment Plugs and Receptacles
(JL)	Designed according to	UL 60939-3	Electromagnetic interference filters
GE CSA Group	Designed according to	CSA C22.2 no. 42	General Use Receptacles, Attachment Plugs, and Similar Wiring Devices
GE CSA Group	Designed according to	CSA C22.2 no. 8	Electromagnetic interference (EMI) filters
EC (P) (P) (CSA GGC CSA	Designed according to Designed according to Designed according to Designed according to	IEC 61058-1 UL 498 UL 60939-3 CSA C22.2 no. 42	Switches for appliances. Part 1. General requirements Standard for Attachment Plugs and Receptacles Electromagnetic interference filters General Use Receptacles, Attachment Plugs, and Similar Wiring Devices

# **Application standards**

Application standards where the product can be used

Organization	Design	Standard	Description
IEC.	Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of information technology equipment.
IEC.	Designed for applications acc.	IEC 60601-1	Medical electrical equipment - Part 1: General requirements for basic safety and essential performance


# Compliances


The product complies with following Guide Lines

Identification	Details	Initiator	Description
CE	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/836
<b>5</b> 0	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.
<b>√</b> -Lock		SCHURTER AG	V-Lock system are based on a matching plug-dose combination. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.
T	Medical Equipment	SCHURTER AG	Suitable for use in medical equipment according to IEC/UL 60601-1


# Dimension [mm]


Snap-in version







Screw-on A








### Screw-on B



#### Screw-on with IP67




# **Technical Data of Filter-Components**

Rated Current [A]	Filter-Type	Inductances L [mH]	Capacitance CX [nF]	Capacitance CY [nF]	<b>R [Μ</b> Ω]
1	Standard Version	2 x 12	220	2.2	1
2	Standard Version	2 x 5.2	220	2.2	1
3	Standard Version	2 x 4	220	2.2	1
4	Standard Version	2 x 2	220	2.2	1
6	Standard Version	2 x 0.8	220	2.2	1
8	Standard Version	2 x 0.6	220	2.2	1
10	Standard Version	2 x 0.4	220	2.2	1
15	Standard Version	2 x 0.1	220	2.2	1
10	Medical Version (M5)	2 x 0.4	220	-	1

# Diagrams


Standard Version, medical Version M80


Medical version M5, protection class I



1) Line, 2) Load

Medical version M5, protection class II








# DG12

**Attenuation Loss** 


- - - - 50 $\Omega$  differential mode \_\_\_\_\_ 50 $\Omega$  common mode




## Effect of ambient temperature

Ambient Temperature [°C]	Correction factor
-30	0.76
-20	0.81
0	0.90
+23	1.00
+40	1.03
+50	1.04
+60	1.06

# **Time-Current-Curves**







#### **Configuration Code TA35**

1)

2)


See configuration code of TA35 rocker 2pole





exceeded in the end application.

3) Only on request (approvals pending)



#### **Configuration Code TA35**

I g I

Screw version A

See configuration code of TA35 rocker 2pole



1)

2)



The rated current of the line-filter must not be

exceeded in the end application.

3) Only on request (approvals pending)

### **ORDER CODE**

Table 1 Selection for type TA35

Order example




Table 1 Selection for type TA35

# ORDER CODE

Order example Number of switched poles 2-pole Number of protected poles 2 1 TA35-CBD W 120 C0 F CBD Switch without CBT illumination No other features Switch illuminated 240 V C12 C32 120 V C14 C34 Other versions on request Colours Switch front Rocker non-illuminated illuminated w black white \_ в black black 3 black red transparent \_ 4 black \_ green transparent 6 orange transparent black \_ Other colours on request **Rocker legend** Surface Illustration Colour of print 0 F embossed NO ЩO printed white н ЩO S printed black Κ 0 L printed white \_ 0 black M printed Other legends on request Position of the rocker Rated current In (A) legend e.g. I / O Code Code I<sub>n</sub> l<sub>n</sub> 1,0 J10 8,0 080 J20 10,0 100 2,0 4,0 040 12,0 120\* D 5,0 050 15,0 150\* 6,0 060 \*) UL / CSA only Other rated currents on request

# Variants

Circuit Break	ker			Filter		Connector				
Rated Cur- rent [A]	Rocker co- lour	Illumination	TA35 Code	Rated Cur- rent [A]	Filter Type	Protection Class	Color	Mounting	IP-Protection	Order Number
1	black	non-illumi- nated	CBDBLJ10C0	1	Standard Version	I	black	Screw-on A	IP40	3-108-854
10	white	non-illumi- nated	CBDWM100C0	10	Standard Version	I	black	Screw-on A	IP40	3-109-572
10	white	non-illumi- nated	CBDWM100C0	10	Standard Version	I	black	Snap-in 1.5	IP40	3-109-575
10	white	non-illumi- nated	CBDWM100C0	10	Standard Version	I	black	Screw B	IP40	3-109-698
10	white	non-illumi- nated	CBDWM100C0	10	Standard Version	I	black	Screw	IP67	3-118-974
15	white	non-illumi- nated	CBDWM150C0	15	Standard Version	I	black	Screw-on A	IP40	3-109-573
2	white	non-illumi- nated	CBDWMJ20C0	2	Standard Version	I	black	Screw-on A	IP40	3-109-557
3	white	non-illumi- nated	CBDWM030C0	3	Standard Version	I	black	Screw-on A	IP40	3-109-558
4	black	non-illumi- nated	CBDBF040C0	4	Standard Version	I	black	Screw-on A	IP40	3-109-559
6	white	non-illumi- nated	CBDWM060C0	6	Standard Version	I	black	Screw-on A	IP40	3-109-560
8	white	non-illumi- nated	CBDWM080C0	8	Standard Version	I	black	Screw-on A	IP40	3-109-561
10	white	non-illumi- nated	CBDWM100C0	10	Medical Version (M5)	I	black	Screw-on A	IP40	3-108-465
10	white	non-illumi- nated	CBDWM100C0	10	Medical Version (M5)	I	black	Screw B	IP40	3-118-982

#### Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging unit 10 Pcs

## Mating Outlets/Connectors

Category / Description

#### Appliance Outlet Overview complete



4787, Mounting: Screw-on mounting, Appliance Outlet: IEC Solder terminals, 10 A, Suitable for appliances with pro- tection class I	4787
4788, Mounting: Snap-in version, Appliance Outlet: IEC Solder terminals or quick connect terminals, 10 A, Suitable for appliances with protection class I	4788
IEC Appliance Outlet F or H, Screw-on Mounting, Front Side, Solder, PCB or Quick-connect Terminal	5091
Appliance Outlet further types to DG12	
Connector Overview complete	
4782 Mounting: Power Cord, 3 x 1 mm <sup>2</sup> / 3 x 18 AWG, Cable, Connector: IEC C13	4782



4782 Mounting: Power Cord, 3 x 1 mm <sup>2</sup> / 3 x 18 AWG, Cable, Connector: IEC C13	4782
4785 Mounting: Power Cord, 3 x 1 mm <sup>2</sup> / 3 x 18 AWG, Cable, Connector: IEC C13	4785
4300-06 Mounting: Power Cord, 3 x 1 mm <sup>2</sup> / 3 x 18 AWG, Cable, Connector: IEC C13	4300-06
	1000 00
4781 Mounting: Power Cord, 3 x 1 mm <sup>2</sup> / 3 x 18 AWG, Cable, Connector: IEC C15	4781
	170.4
4784 Mounting: Power Cord, 3 x 1 mm <sup>2</sup> / 3 x 18 AWG, Cable, Connector: IEC C15	4784
Connector further types to DG12	
connector futurer types to DGT2	

# Mating Outlets/Connectors shuttered



Power Cord Overview complete

VAC13KS, Overview, V-Lock cord retaining, diverse Connector IEC C13, diverse, black VAC13KS
Power Cord further types to DG12

21.03.2019