

RE13-SA05

RE1

NON-CONTACT SAFETY SWITCHES





Ordering information

| Туре | Part no. |
|-----------|----------|
| RE13-SA05 | 1062011 |

Other models and accessories → www.sick.com/RE1



Detailed technical data

Features

| System part | Sensor and actuator |
|--|---------------------|
| Sensor principle | Magnetic |
| Number of N/O contacts | 2 |
| Number of N/C contacts | 0 |
| Number of signaling contacts | 0 |
| Safe switch on distance S _{ao} | 7 mm |
| Safe switch off distance S _{ar} | 20 mm |
| Active sensor surfaces | 1 |
| Actuation directions | 3 |

Safety-related parameters

| B _{10d} parameter | 2 x 10 ⁷ switching cycles (with small load) |
|------------------------------------|---|
| Туре | Type 4 (EN ISO 14119) |
| Actuator coding level | Low coding level (EN ISO 14119) |
| Safe state in the event of a fault | The switch has no internal fault detection and is unable to assume a safe state in the event of a fault. Fault detection is performed by the connected safety-related logic unit. |

Interfaces

| Connection type | Cable |
|-----------------|-------|
| Length of cable | 5 m |
| Cable material | PVC |

Electrical data

| Type of output | Reed contacts |
|-------------------|---------------|
| Switching voltage | ≤ 30 V DC |
| Switching current | ≤ 100 mA |

Mechanical data

| Design | Rectangular |
|------------------------|-----------------------|
| Dimensions (W x H x D) | 26 mm x 36 mm x 13 mm |
| Weight | 0.3 kg |

| _ | |
|-------------------------------|----------------------------------|
| Ambient data | |
| Enclosure rating | IP67 (IEC 60529) |
| Ambient operating temperature | -20 °C +60 °C |
| Storage temperature | -20 °C +60 °C |
| Vibration resistance | 10 Hz 55 Hz, 1 mm (EN 60947-5-3) |
| Shock resistance | 30 g, 11 ms (EN 60947-5-3) |
| Classifications | |
| ECI@ss 5.0 | 27272402 |

Glass-fiber reinforced PPS

EC002544

EC002544

ECI@ss 5.0 27272402 ECI@ss 5.1.4 27272402 ECI@ss 6.0 27272402 ECI@ss 6.2 27272402 ECI@ss 7.0 27272402 ECI@ss 8.0 27272402 ECI@ss 8.1 27272402 ECI@ss 9.0 27272402


Housing material

ETIM 5.0


ETIM 6.0

UNSPSC 16.0901 39122205

Dimensional drawing (Dimensions in mm (inch))



Response range




Connection diagram

REx3: sensor connections (plug M8)



| 1 BN | N/O |
|------|-------------|
| 2 WH | N/O contact |
| 3 BU | N/O contact |
| 4 BK | N/O contact |

Sensor timing



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

