

WL12G-302431 W12G

SMALL PHOTOELECTRIC SENSORS





Illustration may differ

Ordering information

Included in delivery: BEF-KH-W12 (2)

| Other models and accessories | - | www.sick.com. | /W126 |
|------------------------------|---|---------------|-------|
| | | | |

Type
WL12G-302431

Detailed technical data

Features

us LISTED Ind. Con. Eq. 4R97

SIRIC®
optical ASIC invented by SICK

| Device type | Photoelectric sensors |
|-----------------------------|---------------------------------------|
| Functional principle | Photoelectric retro-reflective sensor |
| Functional principle detail | Autocollimation |
| Sensing range max. | 0 m 4 m ¹⁾ |
| Polarisation filters | Yes |
| Emitted beam | |
| Light source | LED ²⁾ |
| Type of light | Visible red light |
| Light spot size (distance) | Ø 25 mm (1.5 m) |
| Key LED figures | |
| Wave length | 640 nm |
| Adjustment | Potentiometer, 11 turns |
| Angle of dispersion | Approx. 1.5° |
| Special applications | Detecting transparent objects |
| Items supplied | 2 x clamps BEF-KH-W12, incl. screws |

¹⁾ Reflector PL80A.

Safety-related parameters

| MTTF _D | 823 years |
|-------------------|-----------|
| DC _{avg} | 0 % |

Part no.

1041457

 $^{^{2)}}$ Average service life: 100,000 h at T_U = +25 °C.

Electrical data

| Supply voltage U _B | 10 V DC 30 V DC ¹⁾ |
|----------------------------------|---|
| Ripple | < 5 V _{pp} ²⁾ |
| Current consumption | 30 mA ³⁾ |
| Protection class | III |
| Digital output | |
| Туре | PNP |
| Signal voltage NPN HIGH/LOW | Approx. Uv / < 3 V |
| Output current I _{max.} | ≤ 100 mA |
| Response time | ≤ 330 μs ⁴⁾ |
| Switching frequency | 1,500 Hz ⁵⁾ |
| Switching mode | Light/dark switching |
| Switching mode selector | Selectable via L/D control cable |
| Circuit protection | A ⁶⁾ C ⁷⁾ D ⁸⁾ |
| Special feature | Detecting transparent objects |

 $^{^{1)}\,\}mathrm{Limit}$ values when operated in short-circuit protected network: max. 8 A.

Mechanical data

| Housing | Rectangular |
|------------------------|---------------------------|
| Dimensions (W x H x D) | 15.6 mm x 48.5 mm x 42 mm |
| Connection | Male connector M12, 4-pin |
| Material | |
| Housing | Metal, zinc diecast |
| Front screen | Plastic, PMMA |
| Weight | 120 g |

Ambient data

| Enclosure rating | IP66 IP67 IP69K |
|-------------------------------|------------------------------|
| Ambient operating temperature | -40 °C +60 °C |
| Ambient temperature, storage | -40 °C +75 °C |
| UL File No. | NRKH.E181493 & NRKH7.E181493 |

Classifications

| eCl@ss 5.0 | 27270902 |
|--------------|----------|
| eCl@ss 5.1.4 | 27270902 |

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

³⁾ Without load.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

⁶⁾ A = V_S connections reverse-polarity protected.

 $^{^{7)}}$ C = interference suppression.

⁸⁾ D = outputs overcurrent and short-circuit protected.

WL12G-302431 | W12G

SMALL PHOTOELECTRIC SENSORS

| eCl@ss 6.0 | 27270902 |
|----------------|----------|
| eCl@ss 6.2 | 27270902 |
| eCl@ss 7.0 | 27270902 |
| eCl@ss 8.0 | 27270902 |
| eCl@ss 8.1 | 27270902 |
| eCl@ss 9.0 | 27270902 |
| eCl@ss 10.0 | 27270902 |
| eCl@ss 11.0 | 27270902 |
| eCl@ss 12.0 | 27270902 |
| ETIM 5.0 | EC002717 |
| ETIM 6.0 | EC002717 |
| ETIM 7.0 | EC002717 |
| ETIM 8.0 | EC002717 |
| UNSPSC 16.0901 | 39121528 |
| | |


Connection type



Connection diagram

Cd-087


Light spot size



All dimensions in mm (inch)

Sensing range diagram


WL12G-3



- Sensing range max.
- ① Reflector PL80A
- ② Reflector C110A
- ③ Reflector P250F
- 4 Reflector PL50A5 Reflector PL40A
- 6 Reflector PL30A
- ⑦ Reflector PL20A
- ® Reflective tape REF-IRF-56

Adjustments


WL12-3, WSE12-3



- ② LED indicator yellow: Status of received light beam
- 3 LED indicator green: Supply voltage active
- Sensitivity control: potentiometer

Dimensional drawing (Dimensions in mm (inch))

WL12-3, WSE12-3



- ① Optical axis
- ② LED indicator yellow: Status of received light beam
- 3 LED indicator green: Supply voltage active
- ④ M4 threaded mounting hole, 4 mm deep
- ⑤ Mounting hole, Ø 4.2 mm
- ® Sensitivity control: potentiometer
- ⑦ Connection

Recommended accessories

Other models and accessories → www.sick.com/W12G

| | Brief description | Туре | Part no. | |
|---------------|---|------------------------|----------|--|
| Mounting bra | ckets and plates | | | |
| | Universal mounting bracket for reflectors, steel, zinc coated | BEF-WN-REFX | 2064574 | |
| Plug connecto | Plug connectors and cables | | | |
| | Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m | YF2A14- 050VB3XLEAX | 2096235 | |
| | Head A: male connector, M12, 4-pin, straight Cable: unshielded | STE-1204-G | 6009932 | |
| Reflectors | | | | |
| | Fine triple reflector, screw connection, suitable for laser sensors, 52 mm x 62 mm, PM-MA/ABS, Screw-on, 2 hole mounting | P250F | 5308843 | |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

