



SIMATIC HMI TP700 Comfort INOX, Stainless steel front, Continuous decorative film, Degree of protection front IP66K, 7" widescreen TFT display, PROFINET interface, MPI/PROFIBUS DP interface, 12 MB configuration memory, Windows CE 6.0, (Microsoft Support included Security updates discontinued) configurable from WinCC Comfort V11

General information	
Product type designation	TP700 Comfort INOX
Display	
Design of display	TFT
Screen diagonal	7 in
Display width	152.4 mm
Display height	91.4 mm
Number of colors	16 777 216
Resolution (pixels)	
• Horizontal image resolution	800 pixel
• Vertical image resolution	480 pixel
Backlighting	
• MTBF backlighting (at 25 °C)	80 000 h
• Backlight dimmable	Yes; 0-100 %
Control elements	
Keyboard fonts	
• Function keys	
— Number of function keys	0
— Number of function keys with LEDs	0
• Keys with LED	No
• System keys	No
• Numeric keyboard	Yes; Onscreen keyboard
• alphanumeric keyboard	Yes; Onscreen keyboard
Touch operation	
• Design as touch screen	Yes; capacitive
Expansions for operator control of the process	
• DP direct LEDs (LEDs as S7 output I/O)	
— F1...Fx	0
• Direct keys (keys as S7 input I/O)	
— F1...Fx	0
• Direct keys (touch buttons as S7 input I/O)	32
Installation type/mounting	
Mounting position	vertical
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
maximum permissible angle of inclination without external ventilation	35°
Supply voltage	
Type of supply voltage	DC
Rated value (DC)	24 V

permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption (rated value)	0.5 A
Starting current inrush I ² t	0.5 A ² ·s
Power	
Active power input, typ.	12 W
Processor	
Processor type	X86
Memory	
Flash	Yes
RAM	Yes
Memory available for user data	12 Mbyte
Type of output	
Info LED	No
Power LED	No
Error LED	No
Acoustics	
• Buzzer	No
• Speaker	Yes
Time of day	
Clock	
• Hardware clock (real-time)	Yes
• Software clock	Yes
• retentive	Yes; Back-up duration typically 6 weeks
• synchronizable	Yes
Interfaces	
Number of industrial Ethernet interfaces	1; 2 ports (switch)
Number of RS 485 interfaces	1; RS 422 / 485 combined
Number of RS 422 interfaces	0; together with RS 485
Number of RS 232 interfaces	0
Number of USB interfaces	2; USB 2.0
• USB Mini B	1; 5-pole
Number of 20 mA interfaces (TTY)	0
Number of parallel interfaces	0
Number of other interfaces	0
Number of SD card slots	2
With software interfaces	No
Industrial Ethernet	
• Industrial Ethernet status LED	2
• Number of ports of the integrated switch	2
Protocols	
PROFINET	Yes
Supports protocol for PROFINET IO	Yes
IRT	Yes; As of WinCC V12
PROFIBUS	Yes
EtherNet/IP	Yes
MPI	Yes
Protocols (Ethernet)	
• TCP/IP	Yes
• DHCP	Yes
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
WEB characteristics	
• HTTP	Yes
• HTTPS	Yes
• HTML	Yes
• XML	Yes
• CSS	Yes

• Active X	Yes
• JavaScript	Yes
• Java VM	No
Redundancy mode	
Media redundancy	
— MRP	Yes; As of WinCC V12
Further protocols	
• CAN	No
• MODBUS	Yes
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class A, for use in industrial areas	Yes
• Limit class B, for use in residential areas	No
Degree and class of protection	
IP (at the front)	IP66K
IP (rear)	IP20
NEMA (front)	
• Enclosure Type 4 at the front	No
• Enclosure Type 4x at the front	Yes; indoor use only
Standards, approvals, certificates	
CE mark	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
EAC (formerly Gost-R)	Yes
Use in hazardous areas	
• ATEX Zone 2	Yes
• ATEX Zone 22	Yes
• IECEx Zone 2	Yes
• IECEx Zone 22	Yes
• cULus Class I Zone 1	No
• cULus Class I Zone 2, Division 2	Yes
• FM Class I Division 2	Yes
Marine approval	
• Germanischer Lloyd (GL)	No
• American Bureau of Shipping (ABS)	No
• Bureau Veritas (BV)	No
• Det Norske Veritas (DNV)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (Class NK)	No
• Polski Rejestr Statkow (PRS)	No
Ambient conditions	
Ambient temperature during operation	
Operation (vertical installation)	
— For vertical installation, min.	0 °C
— For vertical installation, max.	50 °C
Operation (max. tilt angle)	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, max.	40 °C
Operation (vertical installation, portrait format)	
— For vertical installation, min.	0 °C
— For vertical installation, max.	40 °C
Operation (max. tilt angle, portrait format)	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, max.	35 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	60 °C
Relative humidity	

• Operation, max.	90 %; no condensation
Operating systems	
proprietary	No
pre-installed operating system	
• Windows CE	Yes
configuration / header	
Message indicator	Yes
Alarm system (incl. buffer and acknowledgment)	Yes
Process value display (output)	Yes
Process value default (input) possible	Yes
Recipe management	Yes
Configuration software	
• STEP 7 Basic (TIA Portal)	No
• STEP 7 Professional (TIA Portal)	No
• WinCC flexible Compact	No
• WinCC flexible Standard	No
• WinCC flexible Advanced	No
• WinCC Basic (TIA Portal)	No
• WinCC Comfort (TIA Portal)	Yes; from V11
• WinCC Advanced (TIA Portal)	Yes; from V11
• WinCC Professional (TIA Portal)	Yes; from V11
Languages	
Online languages	
• Number of online/runtime languages	32
Project languages	
• Languages per project	32
Functionality under WinCC (TIA Portal)	
Libraries	Yes
Applications/options	
• Web browser	Yes
• Pocket Word	Yes
• Pocket Excel	Yes
• PDF Viewer	Yes
• Media Player	Yes
• SIMATIC WinCC Sm@rtServer	Yes
• SIMATIC WinCC Audit	Yes
Number of Visual Basic Scripts	Yes
Task planner	
• time-controlled	Yes
• task-controlled	Yes
Message system	
• Number of alarm classes	32
• Bit messages	
— Number of bit messages	4 000
• Analog messages	
— Number of analog messages	200
• S7 alarm number procedure	Yes
• System messages HMI	Yes
• System event, more (SIMATIC S7, SINUMERIK, SIMOTION, ...)	Yes
• Number of characters per message	80
• Number of process values per message	8
• Acknowledgment groups	Yes
• Message indicator	Yes
Recipe management	
• Number of recipes	300
• Data records per recipe	500
• Entries per data record	1 000
• Size of internal recipe memory	2 Mbyte
• Recipe memory expandable	Yes
Variables	

- Number of variables per device 2 048
- Number of variables per screen 400
- Limit values Yes
- Multiplexing Yes
- Structures Yes
- Arrays Yes

Images

- Number of configurable images 500
- Permanent window/default Yes
- Global image Yes
- Pop-up images Yes
- Slide-in images Yes
- Image selection by PLC Yes
- Image number in the PLC Yes

Image objects

- Number of objects per image 400
- Text fields Yes
- I/O fields Yes
- Graphic I/O fields (graphics list) Yes
- Symbolic I/O fields (text list) Yes
- Date/time fields Yes
- Switches Yes
- Buttons Yes
- Graphic display Yes
- Icons Yes
- Geometric objects Yes

Complex image objects

- Number of complex objects per screen 20
- Alarm view Yes
- Trend view Yes
- User view Yes
- Status/control Yes
- Sm@rtClient view Yes
- Recipe view Yes
- f(x) trend view Yes
- System diagnostics view Yes
- Media Player Yes
- HTML browser Yes
- PDF display Yes
- IP camera display Yes
- Bar graphs Yes
- Sliders Yes
- Pointer instruments Yes
- Analog/digital clock Yes

Lists

- Number of text lists per project 500
- Number of entries per text list 500
- Number of graphics lists per project 500
- Number of entries per graphics list 500

Archiving

- Number of archives per device 50
- Number of entries per archive 20 000
- Message archive Yes
- Process value archive Yes
- Archiving methods
 - Sequential archive Yes
 - Short-term archive Yes
- Memory location
 - Memory card Yes
 - USB memory Yes
 - Ethernet Yes

<ul style="list-style-type: none"> • Data storage format <ul style="list-style-type: none"> — CSV — TXT — RDB 	<p>Yes</p> <p>Yes</p> <p>Yes</p>
Security	
<ul style="list-style-type: none"> • Number of user groups • Number of user rights • Number of users • Password export/import • SIMATIC Logon 	<p>50</p> <p>32</p> <p>50</p> <p>Yes</p> <p>Yes</p>
Logging through printer	
<ul style="list-style-type: none"> • Alarms • Report (shift log) • Hardcopy • Electronic print to file 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes; PDF, HTML</p>
Character sets	
<ul style="list-style-type: none"> • Keyboard fonts <ul style="list-style-type: none"> — US English 	<p>Yes</p>
Transfer (upload/download)	
<ul style="list-style-type: none"> • MPI/PROFIBUS DP • USB • Ethernet • using external storage medium 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
Process coupling	
<ul style="list-style-type: none"> • S7-1200 • S7-1500 • S7-200 • S7-300/400 • LOGO! • WinAC • SINUMERIK • SIMOTION • Allen Bradley (EtherNet/IP) • Allen Bradley (DF1) • Mitsubishi (MC TCP/IP) • Mitsubishi (FX) • OMRON (FINS TCP) • OMRON (LINK/Multilink) • Modicon (Modbus TCP/IP) • Modicon (Modbus) • OPC UA Client • OPC UA Server 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes; with SINUMERIK option package</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>No</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
Service tools/configuration aids	
<ul style="list-style-type: none"> • Backup/Restore manually • Backup/Restore automatically • Simulation • Device switchover 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
Peripherals/Options	
Printer	Yes
SIMATIC HMI MM memory card: Multi Media Card	Yes; Up to 128 MB
SIMATIC HMI SD memory card: Secure Digital memory card	Yes; Up to 2 GB
SIMATIC HMI CF memory card Compact Flash Card	No
USB memory	Yes
SIMATIC IPC USB Flashdrive (USB stick)	Yes; Up to 16 GB
SIMATIC HMI USB stick	Yes; Up to 8 GB
Network camera	Yes
Mechanics/material	
Enclosure material (front) <ul style="list-style-type: none"> • Plastic • Aluminum • Stainless steel 	<p>No</p> <p>No</p> <p>Yes</p>

Dimensions	
Width of the housing front	214 mm
Height of housing front	158 mm
Mounting cutout, width	198 mm
Mounting cutout, height	142 mm
Overall depth	64.215 mm
Weights	
Weight (without packaging)	1.9 kg
Weight (with packaging)	2 kg

last modified: 8/1/2024 