

MLFB-Ordering data

6SL3210-5BB17-5BV1



Figure similar

Client order no.: Item no.:
Order no.: Consignment no.:
Offer no.: Project:
Remarks:

Rated data		General tech. specifications	
Input		Power factor λ	0.72
Number of phases	1 AC	Offset factor cos φ	0.95
Line voltage	200 240 V -15 % +10 %	Efficiency η	0.98
Line frequency	47 63 Hz	Ambient conditions	
Output		Cooling	convection cooling
Number of phases	3 AC	Installation altitude	1000 m (3281 ft)
Rated voltage	230 V	Ambient temperature	
Rated power (HO)	0.75 kW / 1.00 hp	Operation	-10 60 °C (14 140 °F)
Rated power (LO)	0.75 kW / 0.75 hp	Storage	-40 70 °C (-40 158 °F)
Rated current (HO)	4.20 A	Relative humidity	
Rated current (LO)	4.20 A	Max. operation	95 %
		Communication	
		Communication	USS, Modbus RTU
Pulse frequency Output frequency	8 kHz	Standards	
	0 550 Hz	Compliance with standards	CE, cULus, C-Tick (RCM), KC
		CE marking	EN 61800-5-1 /EN 60204-1 and EN 61800-3

Overload capability

Low Overload (LO)

110 % rated output current for 60 s, cycle time 300 s

High Overload (HO)

150 % rated output current for 60 s, cycle time 300 s



MLFB-Ordering data

6SL3210-5BB17-5BV1



Figure similar

				r	igure siiiiii
Mechanical data		Connections			
Mounting position	Wall mounting / side-by-side mounting		Max. motor cable length Shielded 25 m (33 ft)		
Degree of protection	protection IP20		Unshielded	50 m (164 ft)	
Size	FSAB		Onsineraca	50 III (1011t)	
Net weight	0.80 kg (1.76 lb)				
Width	68.0 mm (2.68 in)				
Height	142.0 mm	n (5.59 in)			
Depth	127.8 mm	າ (5.03 in)			
Inputs / outputs					
Standard digital input	S				
Number		4			
Digital outputs					
Number as relay changeo	ver contact	1			
Number as transistor		1			
Analog inputs					
Number		2 (Can be used as additional digital input)			
Analog outputs					
Number		1			