



SIMATIC S7-1500TF, CPU 1518TF-4 PN/DP, central processing unit with 9 MB work memory for program and 60 MB for data, 1st interface: PROFINET IRT with 2-port switch, 2nd interface: PROFINET RT, 3rd interface: PROFINET basic services, 4th interface: PROFIBUS, 1 ns bit performance, SIMATIC memory card required

General information	
Product type designation	CPU 1518TF-4 PN/DP
HW functional status	FS08
Firmware version	V2.9
Product function	
<ul style="list-style-type: none"> <li>I&amp;M data</li> </ul>	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> <li>Isochronous mode</li> </ul>	Yes; Distributed and central; with minimum OB 6x cycle of 125 µs (distributed) and 1 ms (central)
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated from version</li> </ul>	V17 (FW V2.9) / V17 (FW V2.9) or higher
Configuration control	
via dataset	Yes
Display	
Screen diagonal [cm]	6.1 cm
Control elements	
Number of keys	6
Mode selector switch	1
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Mains buffering	
<ul style="list-style-type: none"> <li>Mains/voltage failure stored energy time</li> </ul>	5 ms
<ul style="list-style-type: none"> <li>Repeat rate, min.</li> </ul>	1/s
Input current	
Current consumption (rated value)	1.55 A
Inrush current, max.	2.4 A; Rated value
$I^2t$	0.02 A <sup>2</sup> ·s
Power	
Infeed power to the backplane bus	12 W
Power consumption from the backplane bus (balanced)	30 W
Power loss	
Power loss, typ.	24 W
Memory	
Number of slots for SIMATIC memory card	1
SIMATIC memory card required	Yes
Work memory	

<ul style="list-style-type: none"> <li>integrated (for program)</li> </ul>	9 Mbyte
<ul style="list-style-type: none"> <li>integrated (for data)</li> </ul>	60 Mbyte
<b>Load memory</b>	
<ul style="list-style-type: none"> <li>Plug-in (SIMATIC Memory Card), max.</li> </ul>	32 Gbyte
<b>Backup</b>	
<ul style="list-style-type: none"> <li>maintenance-free</li> </ul>	Yes
<b>CPU processing times</b>	
for bit operations, typ.	1 ns
for word operations, typ.	2 ns
for fixed point arithmetic, typ.	2 ns
for floating point arithmetic, typ.	6 ns
<b>CPU-blocks</b>	
Number of elements (total)	20 000; Blocks (OB, FB, FC, DB) and UDTs
<b>DB</b>	
<ul style="list-style-type: none"> <li>Number range</li> </ul>	1 ... 60 999; subdivided into: number range that can be used by the user: 1 ... 59 999, and number range of DBs created via SFC 86: 60 000 ... 60 999
<ul style="list-style-type: none"> <li>Size, max.</li> </ul>	16 Mbyte; For DBs with absolute addressing, the max. size is 64 KB
<b>FB</b>	
<ul style="list-style-type: none"> <li>Number range</li> </ul>	0 ... 65 535
<ul style="list-style-type: none"> <li>Size, max.</li> </ul>	1 Mbyte
<b>FC</b>	
<ul style="list-style-type: none"> <li>Number range</li> </ul>	0 ... 65 535
<ul style="list-style-type: none"> <li>Size, max.</li> </ul>	1 Mbyte
<b>OB</b>	
<ul style="list-style-type: none"> <li>Size, max.</li> </ul>	1 Mbyte
<ul style="list-style-type: none"> <li>Number of free cycle OBs</li> </ul>	100
<ul style="list-style-type: none"> <li>Number of time alarm OBs</li> </ul>	20
<ul style="list-style-type: none"> <li>Number of delay alarm OBs</li> </ul>	20
<ul style="list-style-type: none"> <li>Number of cyclic interrupt OBs</li> </ul>	20; with minimum OB 3x cycle of 100 µs
<ul style="list-style-type: none"> <li>Number of process alarm OBs</li> </ul>	50
<ul style="list-style-type: none"> <li>Number of DPV1 alarm OBs</li> </ul>	3
<ul style="list-style-type: none"> <li>Number of isochronous mode OBs</li> </ul>	3
<ul style="list-style-type: none"> <li>Number of technology synchronous alarm OBs</li> </ul>	2
<ul style="list-style-type: none"> <li>Number of startup OBs</li> </ul>	100
<ul style="list-style-type: none"> <li>Number of asynchronous error OBs</li> </ul>	4
<ul style="list-style-type: none"> <li>Number of synchronous error OBs</li> </ul>	2
<ul style="list-style-type: none"> <li>Number of diagnostic alarm OBs</li> </ul>	1
<b>Nesting depth</b>	
<ul style="list-style-type: none"> <li>per priority class</li> </ul>	24; Up to 8 possible for F-blocks
<b>Counters, timers and their retentivity</b>	
<b>S7 counter</b>	
<ul style="list-style-type: none"> <li>Number</li> </ul>	2 048
<b>Retentivity</b>	
— adjustable	Yes
<b>IEC counter</b>	
<ul style="list-style-type: none"> <li>Number</li> </ul>	Any (only limited by the main memory)
<b>Retentivity</b>	
— adjustable	Yes
<b>S7 times</b>	
<ul style="list-style-type: none"> <li>Number</li> </ul>	2 048
<b>Retentivity</b>	
— adjustable	Yes
<b>IEC timer</b>	
<ul style="list-style-type: none"> <li>Number</li> </ul>	Any (only limited by the main memory)
<b>Retentivity</b>	
— adjustable	Yes
<b>Data areas and their retentivity</b>	
Retentive data area (incl. timers, counters, flags), max.	768 kbyte; In total; available retentive memory for bit memories, timers, counters, DBs, and technology data (axes): 700 KB

Extended retentive data area (incl. timers, counters, flags), max.	20 Mbyte; When using PS 6 0W 24/48/60 V DC HF
<b>Flag</b>	
<ul style="list-style-type: none"> <li>• Size, max.</li> <li>• Number of clock memories</li> </ul>	<p>16 kbyte</p> <p>8; 8 clock memory bit, grouped into one clock memory byte</p>
<b>Data blocks</b>	
<ul style="list-style-type: none"> <li>• Retentivity adjustable</li> <li>• Retentivity preset</li> </ul>	<p>Yes</p> <p>No</p>
<b>Local data</b>	
<ul style="list-style-type: none"> <li>• per priority class, max.</li> </ul>	64 kbyte; max. 16 KB per block
<b>Address area</b>	
Number of IO modules	16 384; max. number of modules / submodules
<b>I/O address area</b>	
<ul style="list-style-type: none"> <li>• Inputs</li> <li>• Outputs</li> </ul>	<p>32 kbyte; All inputs are in the process image</p> <p>32 kbyte; All outputs are in the process image</p>
per integrated IO subsystem	
— Inputs (volume)	32 kbyte; max. 32 KB via X1; max. 8 KB via X2 or X4
— Outputs (volume)	32 kbyte; max. 32 KB via X1; max. 8 KB via X2 or X4
per CM/CP	
— Inputs (volume)	8 kbyte
— Outputs (volume)	8 kbyte
<b>Subprocess images</b>	
<ul style="list-style-type: none"> <li>• Number of subprocess images, max.</li> </ul>	32
<b>Hardware configuration</b>	
Number of distributed IO systems	64; A distributed I/O system is characterized not only by the integration of distributed I/O via PROFINET or PROFIBUS communication modules, but also by the connection of I/O via AS-i master modules or links (e.g. IE/PB-Link)
<b>Number of DP masters</b>	
<ul style="list-style-type: none"> <li>• integrated</li> <li>• Via CM</li> </ul>	<p>1</p> <p>8; A maximum of 8 CMs/CPs (PROFIBUS, PROFINET, Ethernet) can be inserted in total</p>
<b>Number of IO Controllers</b>	
<ul style="list-style-type: none"> <li>• integrated</li> <li>• Via CM</li> </ul>	<p>2</p> <p>8; A maximum of 8 CMs/CPs (PROFIBUS, PROFINET, Ethernet) can be inserted in total</p>
<b>Rack</b>	
<ul style="list-style-type: none"> <li>• Modules per rack, max.</li> <li>• Number of lines, max.</li> </ul>	<p>32; CPU + 31 modules</p> <p>1</p>
<b>PtP CM</b>	
<ul style="list-style-type: none"> <li>• Number of PtP CMs</li> </ul>	the number of connectable PtP CMs is only limited by the number of available slots
<b>Time of day</b>	
<b>Clock</b>	
<ul style="list-style-type: none"> <li>• Type</li> <li>• Backup time</li> <li>• Deviation per day, max.</li> </ul>	<p>Hardware clock</p> <p>6 wk; At 40 °C ambient temperature, typically</p> <p>10 s; Typ.: 2 s</p>
<b>Operating hours counter</b>	
<ul style="list-style-type: none"> <li>• Number</li> </ul>	16
<b>Clock synchronization</b>	
<ul style="list-style-type: none"> <li>• supported</li> <li>• to DP, master</li> <li>• in AS, master</li> <li>• in AS, slave</li> <li>• on Ethernet via NTP</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
<b>Interfaces</b>	
Number of PROFINET interfaces	3
Number of PROFIBUS interfaces	1
<b>1. Interface</b>	
<b>Interface types</b>	
<ul style="list-style-type: none"> <li>• RJ 45 (Ethernet)</li> </ul>	Yes; X1

<ul style="list-style-type: none"> <li>• Number of ports</li> <li>• integrated switch</li> </ul>	<p>2</p> <p>Yes</p>
<b>Protocols</b>	
<ul style="list-style-type: none"> <li>• IP protocol</li> <li>• PROFINET IO Controller</li> <li>• PROFINET IO Device</li> <li>• SIMATIC communication</li> <li>• Open IE communication</li> <li>• Web server</li> <li>• Media redundancy</li> </ul>	<p>Yes; IPv4</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes; Optionally also encrypted</p> <p>Yes</p> <p>Yes</p>
<b>PROFINET IO Controller</b>	
<b>Services</b>	
<ul style="list-style-type: none"> <li>— PG/OP communication</li> <li>— Isochronous mode</li> <li>— Direct data exchange</li> <li>— IRT</li> <li>— PROFlenergy</li> <li>— Prioritized startup</li> <li>— Number of connectable IO Devices, max.</li> <li>— Of which IO devices with IRT, max.</li> <li>— Number of connectable IO Devices for RT, max.</li> <li>— of which in line, max.</li> <li>— Number of IO Devices that can be simultaneously activated/deactivated, max.</li> <li>— Number of IO Devices per tool, max.</li> <li>— Updating times</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes; Requirement: IRT and isochronous mode (MRPD optional)</p> <p>Yes</p> <p>Yes; per user program</p> <p>Yes; Max. 32 PROFINET devices</p> <p>512; In total, up to 1 000 distributed I/O devices can be connected via AS-i, PROFIBUS or PROFINET</p> <p>64</p> <p>512</p> <p>512</p> <p>8; in total across all interfaces</p> <p>8</p> <p>The minimum value of the update time also depends on communication share set for PROFINET IO, on the number of IO devices, and on the quantity of configured user data</p>
<b>Update time for IRT</b>	
<ul style="list-style-type: none"> <li>— for send cycle of 125 <math>\mu</math>s</li> <li>— for send cycle of 187.5 <math>\mu</math>s</li> <li>— for send cycle of 250 <math>\mu</math>s</li> <li>— for send cycle of 500 <math>\mu</math>s</li> <li>— for send cycle of 1 ms</li> <li>— for send cycle of 2 ms</li> <li>— for send cycle of 4 ms</li> <li>— With IRT and parameterization of "odd" send cycles</li> </ul>	<p>125 <math>\mu</math>s</p> <p>187.5 <math>\mu</math>s</p> <p>250 <math>\mu</math>s to 4 ms</p> <p>500 <math>\mu</math>s to 8 ms</p> <p>1 ms to 16 ms</p> <p>2 ms to 32 ms</p> <p>4 ms to 64 ms</p> <p>Update time = set "odd" send clock (any multiple of 125 <math>\mu</math>s: 375 <math>\mu</math>s, 625 <math>\mu</math>s ... 3 875 <math>\mu</math>s)</p>
<b>Update time for RT</b>	
<ul style="list-style-type: none"> <li>— for send cycle of 250 <math>\mu</math>s</li> <li>— for send cycle of 500 <math>\mu</math>s</li> <li>— for send cycle of 1 ms</li> <li>— for send cycle of 2 ms</li> <li>— for send cycle of 4 ms</li> </ul>	<p>250 <math>\mu</math>s to 128 ms</p> <p>500 <math>\mu</math>s to 256 ms</p> <p>1 ms to 512 ms</p> <p>2 ms to 512 ms</p> <p>4 ms to 512 ms</p>
<b>PROFINET IO Device</b>	
<b>Services</b>	
<ul style="list-style-type: none"> <li>— PG/OP communication</li> <li>— Isochronous mode</li> <li>— IRT</li> <li>— PROFlenergy</li> <li>— Shared device</li> <li>— Number of IO Controllers with shared device, max.</li> <li>— activation/deactivation of I-devices</li> <li>— Asset management record</li> </ul>	<p>Yes</p> <p>No</p> <p>Yes; Minimum send cycle of 250 <math>\mu</math>s</p> <p>Yes; per user program</p> <p>Yes</p> <p>4</p> <p>Yes; per user program</p> <p>Yes; per user program</p>
<b>2. Interface</b>	
<b>Interface types</b>	
<ul style="list-style-type: none"> <li>• RJ 45 (Ethernet)</li> <li>• Number of ports</li> <li>• integrated switch</li> </ul>	<p>Yes; X2</p> <p>1</p> <p>No</p>

Protocols	
• IP protocol	Yes; IPv4
• PROFINET IO Controller	Yes
• PROFINET IO Device	Yes
• SIMATIC communication	Yes
• Open IE communication	Yes; Optionally also encrypted
• Web server	Yes
• Media redundancy	No
PROFINET IO Controller	
Services	
— PG/OP communication	Yes
— Isochronous mode	No
— Direct data exchange	No
— IRT	No
— PROFIenergy	Yes; per user program
— Prioritized startup	No
— Number of connectable IO Devices, max.	128; In total, up to 1 000 distributed I/O devices can be connected via AS-i, PROFIBUS or PROFINET
— Number of connectable IO Devices for RT, max.	128
— of which in line, max.	128
— Number of IO Devices that can be simultaneously activated/deactivated, max.	8; in total across all interfaces
— Number of IO Devices per tool, max.	8
— Updating times	The minimum value of the update time also depends on communication share set for PROFINET IO, on the number of IO devices, and on the quantity of configured user data
Update time for RT	
— for send cycle of 1 ms	1 ms to 512 ms
PROFINET IO Device	
Services	
— PG/OP communication	Yes
— Isochronous mode	No
— IRT	No
— PROFIenergy	Yes; per user program
— Prioritized startup	No
— Shared device	Yes
— Number of IO Controllers with shared device, max.	4
— activation/deactivation of I-devices	Yes; per user program
— Asset management record	Yes; per user program
3. Interface	
Interface types	
• RJ 45 (Ethernet)	Yes; X3
• Number of ports	1
• integrated switch	No
Protocols	
• IP protocol	Yes; IPv4
• PROFINET IO Controller	No
• PROFINET IO Device	No
• SIMATIC communication	Yes
• Open IE communication	Yes
• Web server	Yes
4. Interface	
Interface types	
• RS 485	Yes; X4
• Number of ports	1
Protocols	
• PROFIBUS DP master	Yes
• PROFIBUS DP slave	No
• SIMATIC communication	Yes

<b>PROFIBUS DP master</b>	
<ul style="list-style-type: none"> <li>• Number of connections, max.</li> <li>• Number of DP slaves, max.</li> </ul>	<p>48; for the integrated PROFIBUS DP interface</p> <p>125; In total, up to 1 000 distributed I/O devices can be connected via AS-i, PROFIBUS or PROFINET</p>
<b>Services</b>	
<ul style="list-style-type: none"> <li>— PG/OP communication</li> <li>— Equidistance</li> <li>— Isochronous mode</li> <li>— Activation/deactivation of DP slaves</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
<b>Interface types</b>	
<b>RJ 45 (Ethernet)</b>	
<ul style="list-style-type: none"> <li>• 100 Mbps</li> <li>• 1000 Mbps</li> <li>• Autonegotiation</li> <li>• Autocrossing</li> <li>• Industrial Ethernet status LED</li> </ul>	<p>Yes</p> <p>Yes; Only possible at the X3 interface of the CPU 1518</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
<b>RS 485</b>	
<ul style="list-style-type: none"> <li>• Transmission rate, max.</li> </ul>	12 Mbit/s
<b>Protocols</b>	
PROFIsafe	Yes; V2.4 / V2.6
<b>Number of connections</b>	
<ul style="list-style-type: none"> <li>• Number of connections, max.</li> <li>• Number of connections reserved for ES/HMI/web</li> <li>• Number of connections via integrated interfaces</li> <li>• Number of S7 routing paths</li> </ul>	<p>384; via integrated interfaces of the CPU and connected CPs / CMs</p> <p>10</p> <p>320</p> <p>64; in total, only 16 S7-Routing connections are supported via PROFIBUS</p>
<b>Redundancy mode</b>	
<ul style="list-style-type: none"> <li>• H-Sync forwarding</li> </ul>	Yes
<b>Media redundancy</b>	
<ul style="list-style-type: none"> <li>— Media redundancy</li> <li>— MRP</li> <li>— MRP interconnection, supported</li> <li>— MRPD</li> <li>— Switchover time on line break, typ.</li> <li>— Number of stations in the ring, max.</li> </ul>	<p>only via 1st interface (X1)</p> <p>Yes; MRP Automanager according to IEC 62439-2 Edition 2.0, MRP Manager; MRP Client</p> <p>Yes; as MRP ring node according to IEC 62439-2 Edition 3.0</p> <p>Yes; Requirement: IRT</p> <p>200 ms; For MRP, bumpless for MRPD</p> <p>50</p>
<b>SIMATIC communication</b>	
<ul style="list-style-type: none"> <li>• PG/OP communication</li> <li>• S7 routing</li> <li>• Data record routing</li> <li>• S7 communication, as server</li> <li>• S7 communication, as client</li> <li>• User data per job, max.</li> </ul>	<p>Yes; encryption with TLS V1.3 pre-selected</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>See online help (S7 communication, user data size)</p>
<b>Open IE communication</b>	
<ul style="list-style-type: none"> <li>• TCP/IP <ul style="list-style-type: none"> <li>— Data length, max.</li> <li>— several passive connections per port, supported</li> </ul> </li> <li>• ISO-on-TCP (RFC1006) <ul style="list-style-type: none"> <li>— Data length, max.</li> </ul> </li> <li>• UDP <ul style="list-style-type: none"> <li>— Data length, max.</li> <li>— UDP multicast</li> </ul> </li> <li>• DHCP</li> <li>• DNS</li> <li>• SNMP</li> <li>• DCP</li> <li>• LLDP</li> <li>• Encryption</li> </ul>	<p>Yes</p> <p>64 kbyte</p> <p>Yes</p> <p>Yes</p> <p>64 kbyte</p> <p>Yes</p> <p>2 kbyte; 1 472 bytes for UDP broadcast</p> <p>Yes; 128 multicast circuits (of which max. 5 via X1)</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes; Optional</p>
<b>Web server</b>	
<ul style="list-style-type: none"> <li>• HTTP</li> </ul>	Yes; Standard and user pages

• HTTPS	Yes; Standard and user pages
<b>OPC UA</b>	
• Runtime license required	Yes; "Large" license required
• OPC UA Client	Yes
— Application authentication	Yes
— Security policies	Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256
— User authentication	"anonymous" or by user name & password
— Number of connections, max.	40
— Number of nodes of the client interfaces, max.	5 000
— Number of elements for one call of OPC-UA_NodeGetHandleList/OPC-UA_ReadList/C max.	300
— Number of elements for one call of OPC-UA_NameSpaceGetIndexList, max.	20
— Number of elements for one call of OPC-UA_MethodGetHandleList, max.	100
— Number of simultaneous calls of the client instructions per connection (except OPC-UA_ReadList, OPC-UA_WriteList, OPC-UA_M max.	1
— Number of simultaneous calls of the client instructions OPC-UA_ReadList, OPC-UA_WriteList and OPC-UA_MethodCall, max.	5
— Number of registerable nodes, max.	5 000
— Number of registerable method calls of OPC-UA_MethodCall, max.	100
— Number of inputs/outputs when calling OPC-UA_MethodCall, max.	20
• OPC UA Server	Yes; Data access (read, write, subscribe), method call, custom address space
— Application authentication	Yes
— Security policies	Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256
— User authentication	"anonymous" or by user name & password
— GDS support (certificate management)	Yes
— Number of sessions, max.	64
— Number of accessible variables, max.	200 000
— Number of registerable nodes, max.	50 000
— Number of subscriptions per session, max.	20
— Sampling interval, min.	10 ms
— Publishing interval, min.	10 ms
— Number of server methods, max.	100
— Number of inputs/outputs per server method, max.	20
— Number of monitored items, max.	10 000; for 1 s sampling interval and 1 s send interval
— Number of server interfaces, max.	10 of each "Server interfaces" / "Companion specification" type and 20 of the type "Reference namespace"
— Number of nodes for user-defined server interfaces, max.	30 000
• Alarms and Conditions	Yes
— Number of program alarms	400
— Number of alarms for system diagnostics	200
<b>Further protocols</b>	
• MODBUS	Yes; MODBUS TCP
<b>Isochronous mode</b>	
Equidistance	Yes
<b>S7 message functions</b>	
Number of login stations for message functions, max.	64
Program alarms	Yes
Number of configurable program messages, max.	10 000; Program messages are generated by the "Program_Alarm" block, ProDiag or GRAPH
Number of loadable program messages in RUN, max.	5 000

Number of simultaneously active program alarms	
<ul style="list-style-type: none"> <li>• Number of program alarms</li> <li>• Number of alarms for system diagnostics</li> <li>• Number of alarms for motion technology objects</li> </ul>	<p>4 000</p> <p>1 000</p> <p>480</p>
<b>Test commissioning functions</b>	
Joint commission (Team Engineering)	Yes; Parallel online access possible for up to 10 engineering systems
Status block	Yes; Up to 16 simultaneously (in total across all ES clients)
Single step	No
Number of breakpoints	20
<b>Status/control</b>	
<ul style="list-style-type: none"> <li>• Status/control variable</li> <li>• Variables</li> </ul>	Yes; without fail-safe inputs/outputs, bit memories, DBs, peripheral I/Os (without fail-safe), times, counters
<ul style="list-style-type: none"> <li>• Number of variables, max.</li> <li>— of which status variables, max.</li> <li>— of which control variables, max.</li> </ul>	<p>200; per job</p> <p>200; per job</p>
<b>Forcing</b>	
<ul style="list-style-type: none"> <li>• Forcing</li> <li>• Forcing, variables</li> <li>• Number of variables, max.</li> </ul>	<p>Yes; without fail-safe</p> <p>peripheral inputs/outputs (without fail-safe)</p> <p>200</p>
<b>Diagnostic buffer</b>	
<ul style="list-style-type: none"> <li>• present</li> <li>• Number of entries, max.</li> <li>— of which powerfail-proof</li> </ul>	<p>Yes</p> <p>3 200</p> <p>1 000</p>
<b>Traces</b>	
<ul style="list-style-type: none"> <li>• Number of configurable Traces</li> </ul>	8; Up to 512 KB of data per trace are possible
<b>Interrupts/diagnostics/status information</b>	
<b>Diagnostics indication LED</b>	
<ul style="list-style-type: none"> <li>• RUN/STOP LED</li> <li>• ERROR LED</li> <li>• MAINT LED</li> <li>• Connection display LINK TX/RX</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
<b>Supported technology objects</b>	
Motion Control	Yes; Note: The number of technology objects affects the cycle time of the PLC program; selection guide via the TIA Selection Tool
<ul style="list-style-type: none"> <li>• Number of available Motion Control resources for technology objects</li> <li>• Required Motion Control resources <ul style="list-style-type: none"> <li>— per speed-controlled axis</li> <li>— per positioning axis</li> <li>— per synchronous axis</li> <li>— per external encoder</li> <li>— per output cam</li> <li>— per cam track</li> <li>— per probe</li> </ul> </li> <li>• Number of available Extended Motion Control resources for technology objects</li> <li>• Required Extended Motion Control resources <ul style="list-style-type: none"> <li>— per cam (1 000 points and 50 segments)</li> <li>— per cam (10 000 points and 50 segments)</li> <li>— for each set of kinematics</li> <li>— Per leading axis proxy</li> </ul> </li> <li>• Positioning axis <ul style="list-style-type: none"> <li>— Number of positioning axes at motion control cycle of 4 ms (typical value)</li> <li>— Number of positioning axes at motion control cycle of 8 ms (typical value)</li> </ul> </li> </ul>	<p>15 360</p> <p>40</p> <p>80</p> <p>160</p> <p>80</p> <p>20</p> <p>160</p> <p>40</p> <p>512</p> <p>2</p> <p>20</p> <p>30</p> <p>3</p> <p>140</p> <p>192</p>
<b>Controller</b>	
<ul style="list-style-type: none"> <li>• PID_Compact</li> <li>• PID_3Step</li> <li>• PID-Temp</li> </ul>	<p>Yes; Universal PID controller with integrated optimization</p> <p>Yes; PID controller with integrated optimization for valves</p> <p>Yes; PID controller with integrated optimization for temperature</p>

Counting and measuring	
• High-speed counter	Yes
<b>Standards, approvals, certificates</b>	
Highest safety class achievable in safety mode	
• Performance level according to ISO 13849-1	PLe
• SIL acc. to IEC 61508	SIL 3
Probability of failure (for service life of 20 years and repair time of 100 hours)	
— Low demand mode: PFDavg in accordance with SIL3	< 2.00E-05
— High demand/continuous mode: PFH in accordance with SIL3	< 1.00E-09
<b>Ambient conditions</b>	
Ambient temperature during operation	
• horizontal installation, min.	0 °C
• horizontal installation, max.	60 °C; Display: 50 °C, at an operating temperature of typically 50 °C, the display is switched off
• vertical installation, min.	0 °C
• vertical installation, max.	40 °C; Display: 40 °C, at an operating temperature of typically 40 °C, the display is switched off
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	3 000 m; Restrictions for installation altitudes > 2 000 m, see manual
<b>configuration / header</b>	
configuration / programming / header	
Programming language	
— LAD	Yes; incl. failsafe
— FBD	Yes; incl. failsafe
— STL	Yes
— SCL	Yes
— GRAPH	Yes
Know-how protection	
• User program protection/password protection	Yes
• Copy protection	Yes
• Block protection	Yes
Access protection	
• protection of confidential configuration data	Yes
• Password for display	Yes
• Protection level: Write protection	Yes; Specific write protection both for Standard and for Failsafe
• Protection level: Read/write protection	Yes
• Protection level: Write protection for Failsafe	Yes
• Protection level: Complete protection	Yes
programming / cycle time monitoring / header	
• lower limit	adjustable minimum cycle time
• upper limit	adjustable maximum cycle time
<b>Dimensions</b>	
Width	175 mm
Height	147 mm
Depth	129 mm
<b>Weights</b>	
Weight, approx.	1 988 g
<b>last modified:</b>	11/10/2021 