

Heavy Duty 2-Post Rack - 16U

Product ID: 2POSTRACK16



This 2-post rack stands on your floor or desktop to provide 16U of storage space for EIA-310-D compliant 19" rack-mount devices, such as telecommunication and A/V equipment. The rack creates a robust storage solution, with support for a total load capacity of 160 kg (350 lb.).

This compact 2-post mounting solution offers a small footprint, and it's engineered to provide exceptional stability, with a total weight capacity of up to 160 kg (350 lb.). The rack fits in virtually any environment, and can be positioned on any surface, such as your floor, desk or table.

The 2-post server rack comes in a flat-packed box to reduce shipping volume, which also significantly reduces your costs in shipping. The rack is packaged efficiently, so you can easily store it for deployment at a later date.

To help make your equipment install easier, this rack includes tool-less clip nuts that seamlessly work with the punched round holes featured on this rack. The tool-less clip nuts provide an easy-to-install nut, unlike square cage nuts which can be a hassle.

The 2POSTRACK16 is backed by a lifetime StarTech.com warranty with free technical support.

Certifications, Reports and Compatibility

Applications

- Use this cabinet to house your A/V equipment in a restaurant or bar, where space may be limited
- Rack-mount the equipment in your repair center or technology shop
- · House equipment in audio-video editing rooms, or radio and television broadcast studios



Features

- Save space with a compact 2-post rack solution
- Get heavy-duty weight capacity up to 350 lb. (158 kg)
- Reduce your shipping costs with a flat-packed rack
- Easy equipment installation with tool-less clip nuts
- Maximize compatibility with EIA-310-D compliance
- 16U of rack space

Hardware		
	Warranty	Lifetime
	Wallmountable	No
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	16U
	Special Features	Easy Assembly
	Mounting Hole Types	Circle (For Clip Nut)
	Industry Standards	EIA/ECA-310-E
Physical Characteristics		
	Color	Black
	Construction Material	Steel
Product Measurements		
	Product Length	12.0 in [30.5 cm]
	Product Width	20.4 in [51.8 cm]
	Product Height	31.0 in [78.7 cm]
	Weight of Product	17.7 lb [8.0 kg]

Packaging Information



Flat Pack (Assembly

Required)

Yes

Package Length 35.7 in [90.7 cm]

Package Width 13.7 in [34.8 cm]

Package Height 2.9 in [73 mm]

Shipping (Package)

Weight

20.5 lb [9.3 kg]

What's in the Box

Included in Package Right Bracket

Left Bracket

Top Bracket

Bottom Bracket

Rubber Feet

10-32 Phillips Screws

10-32 Mounting Screws

Clip Nuts

User Manual

^{*}Product appearance and specifications are subject to change without notice.