

6U 19" Wall Mount Network Rack 19" Deep 2 Post Open Frame for Server Room Data/AV/IT/Communication/Computer Equipment/Patch Panel w/Cage Nuts/Screws Hook/Loop - Cisco 2960

## Product ID: RK619WALLO



This open-frame 6U wall mount rack provides 6U of storage, allowing you to save space and stay organized. The 19 inch equipment rack can hold up to 175 lb. (80 kg).

The wall mount open frame rack is 18 in. (45.7 cm) deep, so it's perfect for smaller spaces. It's easy to assemble and features mounting holes that are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common wall-frame stud spacing.

You can mount the wall mount open frame rack where space is limited, such as on a server room wall, office, or above a doorway, to expand your workspace and ensure your equipment is easy to access.

By having an open frame, the small wall mount network rack provides passive cooling to equipment. Additionally, the open frame provides easy access and configurability to your equipment, allowing you to maximize productivity.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The RK619WALLO is backed by a StarTech.com a lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## **Applications**

• Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore



- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mounting audio video broadcast or distribution components

## **Features**

- STURDY & CONVENIENT: 6U 19" Open Frame wall mount network rack with 19" mounting depth is EIA/ECA-310 compatible & supports like patch panels, shelves and unmanaged switches
- HEAVY DUTY: This heavy duty 2 post open frame rack supports unobstructed airflow & is easy to install with a durable design made from SPCC cold-rolled steel with support for up to 175lbs of equipment
- EASY ASSEMBLY: The rack ships flat packed with ISTA-6 certified packaging to ensure complete and undamaged delivery and also features comprehensive assembly instructions
- ACCESSORIES INCLUDED: The wall mount server room/ computer/communication/AV/IT equipment rack includes 24 M6 screws & cage nuts & hook & loop to securely mount all of your equipment in the rack
- LIFETIME WARRANTY: StarTech.com offers 24 hour technical support and has been the choice of IT professionals for 30 years, conducting thorough compatibility and performance testing on all our products

| Hardware    |                       | 177.0                 |
|-------------|-----------------------|-----------------------|
|             | Warranty              | Lifetime              |
|             | Wallmountable         | Yes                   |
|             | Rack Type             | 2-Post                |
|             | Frame Type            | Open Frame            |
|             | U Height              | 6U                    |
|             | Special Features      | Easy Assembly         |
|             |                       | Wall-Mountable        |
|             | Mounting Rail Profile | G-Shape               |
|             | Mounting Hole Types   | Square (For Cage Nut) |
|             | Industry Standards    | EIA/ECA-310-E         |
| Performance |                       |                       |
|             | Weight Capacity       | 176.8 lb [80 kg]      |

Physical Characteristics



|                          | Color                         | Black                                      |
|--------------------------|-------------------------------|--|
|                          | Construction Material         | Steel                                      |
| Product<br>Measurements  |                               |  |
|                          | Product Length                | 18.0 in [45.7 cm]                          |
|                          | Product Width                 | 21.9 in [55.5 cm]                          |
|                          | Product Height                | 16.0 in [40.7 cm]                          |
|                          | Weight of Product             | 23.2 lb [10.5 kg]                          |
|                          | Maximum Mounting Depth        | 18.0 in [45.7 cm]                          |
| Packaging<br>Information |                               |  |
|                          | Flat Pack (Assembly Required) | No   |
|                          | Package Length                | 20.7 in [52.5 cm]                          |
|                          | Package Width                 | 24.4 in [62.0 cm]                          |
|                          | Package Height                | 18.7 in [47.5 cm]                          |
|                          | Shipping (Package)<br>Weight  | 23.6 lb [10.7 kg]                          |
| What's in the Box        |                               |  |
|                          | Included in Package           | Rack                                       |
|                          |                               | M6 Screw                                   |
|                          |                               | M6 Cage Nuts                               |
|                          |                               | 10 Foot Length Roll of Black Hook and Loop |

<sup>\*</sup>Product appearance and specifications are subject to change without notice.