

4-Bay Mobile Rack Backplane for 2.5in SATA/SAS Drives

Product ID: SATSASBP425



Now it's easy to drive share and enhance the storage capabilities of your server or PC. This mobile rack backplane lets you install four 2.5in SATA or SAS solid-state or hard disk drives into a single 5.25in bay and quickly hot swap them between systems. It's ideal for systems integrators and administrators who are looking for flexible management of their data storage.

The mobile rack backplane is engineered to protect your valuable data and provide reliable performance. The aluminum housing is designed for enhanced heat dissipation, while two 40mm fans improve air flow to minimize heat build-up and ensure optimum operating temperature.

The backplane can be mounted either vertically or horizontally, for error-free tray insertion and maximum compatibility with servers or desktop computers. You can lock the removable steel trays in place, providing an enhanced level of drive protection. The Non-Scratch SATA (NSS) connector provides a high 50,000+ insertion rating, your assurance of long-lasting performance of both the drives and the bay.

Many fast-paced work environments require drives to be removed regularly. Hot swap between systems quickly, without shutting down, with the convenient backplane.

The included drive trays are interchangeable, working with both the 4-bay backplane and the single-bay backplane (SATSASBP125) so you can hot swap between systems for easy file access.

Designed for versatile use, the backplane supports an extensive range of both SATA or SAS based HDDs and SSDs, from 5 to 15mm in height.

To maximize the performance of your drives, the mobile rack supports SAS II and SATA III performance for transfer speeds up to 6 Gbps when paired with a compatible controller. The backplane also works with your preferred RAID controller or Hyper Duo controller to produce a high-performance or redundant storage solution.

The SATSASBP425 backplane is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Systems integrators and administrators looking for flexible storage management
- Build your incremental or off-site storage back-up plan by attaching hot-swappable drives to your server or computer
- Fast-paced work environments where drives need to be replaced or removed regularly

Features

- Build your storage system by adding four 2.5in SAS or SATA drives into one 5.25in bay
- Supports a wide range of SSDs and HDDs from 5-15mm
- Easy, error free insertion of tray with vertically or horizontally mounted backplane
- Lockable, removable trays provide drive protection
- NSS connector provides 50,000+ insertion rating for long-lasting performance
- Interchangeable drive trays also work with the 1-bay backplane (SATSASBP125)
- High-quality metal housing provides enhanced heat dissipation
- Two 40mm fans to optimize ventilation
- Flammability rating of UL 94 V-O
- Support for SAS II and SATA I, II and III with file transfer speeds of up to 6Gbps
- Works with your RAID or HyperDuo controller

Hardware		
	Warranty	2 Years
	Front Door Key Lock	Yes
	Fan(s)	Yes
	Fans	40 mm
	Interface	SATA
		SAS
	Number of Drives	4



Drive Size 2.5in

Compatible Drive Types SAS & SATA

Drive Installation Removable

Number of 2.5 inch bays 4

Supported Drive Height(s) 5mm

9.5mm

12.5mm

15mm

Fan Bearing Type Sleeve Bearing

Performance

Noise Level 20 dBA

Maximum Data Transfer

Rate

6 Gbps

Type and Rate SATA III (6 Gbps)

Port Multiplier No

Max Drive Capacity Tested with hard drives up to 2TB at 7200 RPM

Hot Swap Capability Yes

Insertion Rating 50,000

MTBF 30,000

Connector(s)

Drive Connectors SATA Data & Power Combo (7+15 pin)

Host Connectors SATA (7 pin, Data)

Other Interface(s) LP4 (4 pin; Large Drive Power)

Software

OS Compatibility OS independent; No software or drivers required

Special Notes / Requirements

Note Flammability rating: UL94 - V0



Indicators **LED Indicators** Drive power and activity LED Fan activity **Environmental Operating Temperature** 0C to 55C (23F to 95F) Storage Temperature -20C to 55C (-4F to 131F) 5%~65% RH Humidity **Physical** Characteristics Color Black Material Aluminum and Steel Max Drive Height 0.6 in [15 mm] Product Length 6.0 in [15.2 cm] **Product Width** 5.7 in [14.6 cm] Product Height 1.7 in [42.0 mm] Weight of Product 26.8 oz [760.0 g] **Packaging** Information Package Length 8.5 in [21.6 cm] Package Width 7.6 in [19.4 cm] Package Height 3.1 in [80.0 mm]

What's in the Box

Shipping (Package)

Weight

Included in Package 4-bay SATA/SAS hard drive backplane

drive tray keys

2.3 lb [1.0 kg]

2.5" drive trays

18" SATA data cables



SATA to Molex power adapters

drive mounting screws

backplane mounting screws

quick start guide

^{*}Product appearance and specifications are subject to change without notice.