

Composite and S-Video to VGA Video Scan Converter

## **Product ID:** VID2VGATV2



The VID2VGATV2 Composite and S-Video to VGA Video Scan Converter (with Scaler) provides a simple way to convert Composite or S-Video signals to VGA (or Component RCA) output, for use with computer monitors, projectors or HDTV sets.

Equipped with an On-Screen Display (OSD) menu and dip switches for simple configuration and selection of your video output settings, this compact video scaler installs quickly and easily for a true plug-and-play experience. An integrated scaler circuit dynamically converts the S-Video or Composite video input signal, giving you multiple output resolutions to choose from, to ensure compatibility with your display or projector.

Plus, the Component/S-Video-VGA Converter includes a VGA to Component (RCA) breakout cable, which enables you to connect to TV sets that are not equipped with a VGA port.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## **Applications**

- Perfect for displaying video from DVD players, VCRs or legacy Game Consoles on VGA projectors and HDTV sets
- Display camcorder output on televisions or monitors equipped with VGA input
- Monitor security cameras with S-Video or composite signaling using VGA monitors or televisions
- Adapt VHS video in the classroom to newer televisions
- Convert legacy Medical Imaging equipment for display on computer monitors



• Use in boardrooms for adapting legacy video equipment to work with new projectors

## **Features**

- Convert and scale Composite/S-Video input to VGA/Component output
- Accepts NTSC and PAL input
- On-Screen Display for simple output setting selection
- VGA to Component (YPbPr) RCA Adapter included
- 50 Hz to 60 Hz frame rate conversion
- Plug & Play installation no drivers or software required

Connector A

Hardware		
	Warranty	2 Years
	Active or Passive Adapter	Active
	AV Input	S-Video
		Composite
	AV Output	VGA
		Component
	Audio	No
Performance		
	Supported Resolutions	PC: 1600x1200, 1280x1024, 1024x768
		HDTV: 480p (50/60Hz), 576p (50Hz), 720p (50/60Hz), 1080p (50/60Hz)
	Signal Levels	Input
		Video @ 1V p-p, 75 ohm
		Y @ 1 V p-p, 75 ohm
		Color @ 0.7V p-p, 75 ohm

Composite Video (1 x RCA)

S-Video (4 pin, Mini-DIN)



	Connector B	VGA (15 pin, High Density D-Sub)
Indicators	LED Indicators	Composite (Yellow) / S-Video (Red) input indicator
Power	Power Source	AC Adapter Included
	Output Voltage	5 DC
	Output Current	1A
	Power Consumption (In Watts)	2.5
Environmental	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	0C to 60C (32F to 140F)
	Humidity	0~60% RH
Physical Characteristics		
	Color	Black
	Material	Plastic
	Product Length	4.4 in [11.2 cm]
	Product Width	2.5 in [64 mm]
	Product Height	1.0 in [26 mm]
	Weight of Product	3.0 oz [86 g]
Packaging Information		
	Package Length	4.6 in [11.8 cm]
	Package Width	8.2 in [20.9 cm]
	Package Height	2.4 in [61 mm]
	Shipping (Package) Weight	16.2 oz [459 g]

What's in the Box



Included in Package Video Converter/Scaler

VGA to Component (RCA) breakout cable

Universal Power Adapter

Instruction Manual

<sup>\*</sup>Product appearance and specifications are subject to change without notice.