

120x25mm Dual Ball Bearing Computer Case Fan w/ LP4 Connector

Product ID: FANBOX12



This versatile 12cm PC case fan is designed to fit a broad range of computer case designs, to circulate cool air into the case, or exhaust warm air out - preventing problems due to overheating components.

A quiet cooling solution, the 12cm dual ball-bearing case fan features a high efficiency blade design that's capable of moving 72.94 CFM throughout the computer case, helping to optimize system performance.

This broadly compatible PC cooling solution can be powered through a simple LP4 connection to the computer power supply, and is backed by StarTech.com's 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Replace a noisy or failed computer case fan
- Install into a computer to increase air flow and cooling

Features

- Dual ball bearing design
- Inline LP4 power connectors

Hardware

Warranty

2 Years



	Number of Conductors	2
	Fan Bearing Type	Ball Bearing
Performance		
	Air Flow Rate	72.94 CFM
	Noise Level	30 dBA
	Fan RPM	2000
Connector(s)	Connector Type(s)	LP4 (4 pin; Large Drive Power)
		LP4 (4 pin; Large Drive Power)
Power	Input Voltage	12V DC
Environmental	Operating Temperature	-10C to 80C
Physical Characteristics		
	Color	Black
	Material	Plastic
	Cable Length	12.0 in [30.5 cm]
	Product Length	4.7 in [12.0 cm]
	Product Width	1.0 in [25.0 mm]
	Product Height	4.7 in [12.0 cm]
	Weight of Product	4.4 oz [125.0 g]
Packaging Information		
	Package Length	8.0 in [20.3 cm]
	Package Width	5.8 in [14.7 cm]

1.2 in [30.0 mm]

Package Height



	Shipping (Package) Weight	6.2 oz [177.0 g]
What's in the Box	Included in Package	12cm Case Fan
		Mounting Screws

^{*}Product appearance and specifications are subject to change without notice.