

T4140012051-000 ✓ ACTIVE



M12 Connector

TE Internal #: T4140012051-000

Standard Circular Connectors, Wire-to-Panel, 5 Position, Sealable, Printed Circuit Board, Signal, Reverse Gender, Nickel, Brass, M12 Connector

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > M12 Panel Mount PCB



Connector System: **Wire-to-Panel**

Number of Positions: **5**

Sealable: **Yes**

Connector & Contact Terminates To: **Printed Circuit Board**

Contact Current Rating (Max): **4 A**

[All M12 Panel Mount PCB \(112\)](#)

Features

Product Type Features

Product Type	Connector
Accessory Color	Black
Assembly Type	Electrical Connector
Connector System	Wire-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board
Circular Connector Type	Plug
Shell Type	Metal

Configuration Features

Keying & Polarized Position Locations	A
Factory Installed Backshell	No
Keying	A
Number of Positions	5



Number of Power Positions	0
Number of Signal Positions	5
Contacts Preloaded	Yes

Electrical Characteristics

Operating Voltage	60 VAC
-------------------	--------

Body Features

Peripheral Seal Material	Silicone
Environmental Protection	IP67
O-Ring Material	Silicone
Environmental Protection Type	Elastomer Sealed
Shell Plating Material	Nickel
Shell Base Material	Brass
Circular Connector Insulation Material Type	Polyamide 66 GF25

Contact Features

Contact Current Rating (Max)	4 A
Reverse Gender	Yes
Circular Connector Contact Type	Pin

Mechanical Attachment

Polarization Code	A
-------------------	---

Housing Features

Circular Connector Shell Size	18
-------------------------------	----

Usage Conditions

IP Water Sealing Level	IP67
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	1
--------------------	---



Other

Field Serviceable	No
-------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T4110002051-000
M12,FEMALE,STRAIGHT,A CODE,5P, PG9,GOLD



TE Part # 1838892-3
M12 Mt FEMALE PNL CONN. PCB Front (Hex)



TE Part # TAA755A5501-A01
M12A5-MS-FS-PUR-3.0M



TE Part # TAA755A5501-A02
M12A5-MS-FS-PUR-4.5M




TE Part # TAA755A5501-A03
M12A5-MS-FS-PUR-6.0M



TE Part # TAA755A5501-A04
M12A5-MS-FS-PUR-7.5M



TE Part # TAA755A5501-A05
M12A5-MS-FS-PUR-10.0M



TE Part # TAA755A5501-A06
M12A5-MS-FS-PUR-15.0M



TE Part # TAA755A5501-A07
M12A5-MS-FS-PUR-18.0M



TE Part # TAA755A5501-A08
M12A5-MS-FS-PUR-20.0M



TE Part # TAA755A5501-A09
M12A5-MS-FS-PUR-25.0M



TE Part # TAA755A5501-A10
M12A5-MS-FS-PUR-35.0M



TE Part # TAA755A5501-A11
M12A5-MS-FS-PUR-45.0M



TE Part # TAA755A5501-A12
M12A5-MS-FS-PUR-60.0M




TE Part # TAA755A5501-A13
M12A5-MS-FS-PUR-75.0M

Also in the Series | **M12 Connector**



M8/M12 Cable Assemblies(230)




Standard Circular Connectors(520)

Customers Also Bought



TE Part #3-1734839-0
FPC CONN. 0.5MM PITCH T/C,30P




TE Part #T4041017041-000
M8 Panel Mount PCB



TE Part #1-770190-0
15P MINI-UMNL ASSY V0 SNNI*



TE Part #4-2176343-1
CRGCO 1206 22K 1%



Documents

Product Drawings

[M12,REAR MOUNTING,MALE,A CODE,5P](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_T4140012051-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T4140012051-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T4140012051-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Agency Approvals

[UL Report](#)

English