
KEMET Part Number: T494B106M016AT



T494, Tantalum, MnO2 Tantalum, 10 uF, 20%, 16 VDC, SMD, MnO2, Molded, Low ESR, 800 mOhms, 3528, Height Max = 2.1mm



Dimensions	
Footprint	3528
L	3.5mm +/-0.2mm
W	2.8mm +/-0.2mm
Н	1.9mm +/-0.2mm
Т	0.13mm REF
S	0.8mm +0.2/-0.3mm
F	2.2mm +/-0.1mm
Α	1.9mm MIN
В	0.4mm +/-0.15mm
E	2.2mm REF
G	1.8mm REF
Р	0.5mm REF
R	1mm REF
Х	0.1mm +/-0.1mm

Packaging Specifications		
Weight:	107.45 mg	
Packaging:	T&R, 178mm	
Packaging Quantity:	2000	

General Information		
Supplier:	KEMET	
Series:	T494	
Dielectric:	MnO2 Tantalum	
Style:	SMD Chip	
Description:	SMD, MnO2, Molded, Low ESR	
Features:	Low ESR	
RoHS:	Yes	
Termination:	Tin	
Shelf Life:	156 Weeks	
MSL:	1	

Specifications		
Capacitance:	10 uF	
Capacitance Tolerance:	20%	
Voltage DC:	16 VDC (85C), 10.72 VDC (125C)	
Temperature Range:	-55/+125C	
Rated Temperature:	85°C	
Dissipation Factor:	6.00% 120Hz 20C	
Failure Rate:	N/A	
Resistance:	0.8 Ohms (100kHz)	
Ripple Current:	326 mAmps (100kHz 25C), 293.4 mAmps (85C), 130.4 mAmps (125C)	
Leakage Current:	1.6 uA (5min 20C)	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

