
KEMET Part Number: T523H477M016APE070



T523, Tantalum, Polymer Tantalum, Reduced Volume, 470 uF, 20%, 16 VDC, SMD, Polymer, Molded, Face Down Terminals, 70 mOhms, 7360, Height Max = 2mm



Dimensions		
Footprint	7360	
L	7.3mm +/-0.3mm	
W	6mm +/-0.3mm	
Н	2mm MAX	
S	1.6mm +/-0.3mm	
F	4.45mm +/-0.1mm	

Packaging Specifications		
Packaging:	T&R, 178mm	
Packaging Quantity:	1000	

General Information	
Supplier:	KEMET
Series:	T523
Dielectric:	Polymer Tantalum
Style:	SMD Chip
Description:	SMD, Polymer, Molded, Face Down Terminals
Features:	Face Down
RoHS:	Yes
Termination:	Nickel Palladium Gold
Shelf Life:	52 Weeks
MSL:	3

Specifications	
Capacitance:	470 uF
Capacitance Tolerance:	20%
Voltage DC:	16 VDC (85C)
Temperature Range:	-55/+85C
Rated Temperature:	85°C
Humidity:	60C, 90% RH, no load, 500 Hours
Dissipation Factor:	10.00% 120Hz 25C
Failure Rate:	N/A
Resistance:	70 mOhms (100kHz 25C)
Ripple Current:	2510 mA (100kHz 45C), 1757 mA (85C)
Leakage Current:	752 uA (5min 25C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

