



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**  
 Die Sets Type: **Removable/Interchangeable**  
 Specification Type: **TE Product Specification (114-)**  
 TE Certification: **Cannot be Certified**  
 Power Technology Type: **Manual**

### Features

#### Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	SDE Crimp Die Set

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


### Compatible Parts



TE Part # 9-1478240-0  
 SDE SA PEW12 HAND TOOL FRAME-  
 NO DIES



TE Part # CAT-AM705-T273  
 AMP MCP, RECEPTACLE AND TAB



Was called  
 SDE PEW 12

Now renamed as:  
 SDE SA  
 (no other physical changes)

TE Part # 2063524-1  
 SDE MCP1.5 0.2-1.0mm2 ASSY



TE Part # 1241375-1  
 AMP MCP 1.5K, CONTACT, (LP)



TE Part # 1241381-1  
 AMP MCP 1.5K, CONTACT, SWS, (LP)



TE Part # 1241381-3  
 AMP MCP 1.5K, CONTACT, SWS, (LP)



TE Part # 1241381-2  
 AMP MCP 1.5K, CONTACT, SWS, (LP)



TE Part # 1241375-2  
 AMP MCP 1.5K, CONTACT, (LP)


TE Part # 1241375-3  
 AMP MCP 1.5K, CONTACT, (LP)

TE Part # 1241377-1  
 AMP MCP1.5K,CONTACT,(LP)



TE Part # 2362810-1  
 SDE CRIMP HAND TOOL FRAME

TE Part # 6-1241374-1  
 MCP1.5 SOCKET CONTACT



## Documents

### Datasheets & Catalog Pages

#### Bottoming Dies

English

---

### Instruction Sheets

#### Instruction Sheet (U.S.)

English