




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **White**

Primary Product Material: **Nylon**

Number of Positions: **19**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	19
---------------------	----

Body Features

Primary Product Color	White
Primary Product Material	Nylon

Mechanical Attachment

Strain Relief	With
---------------	------

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
--------------------	------------------

Usage Conditions

Compatible With IDC Installation Type Connector	Feed Thru
Operating Temperature (Max)	105 °C[221 °F]



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 4-640602-9
19P MTA156 CONN ASSY 24AWG LF



TE Part # 4-640599-9
19P MTA156 CONN ASSY 18AWG ORA



TE Part # 4-641119-9
19P MTA156 HDR ASSY FL/ST LF





TE Part # 1-1744194-9
19P MTA156 HDR ASSY FL/STR SN



 TE Part # 1-640385-9 19P MTA156 HDR ASSY SQ R/A	 TE Part # 4-641208-9 19P MTA156 HDR ASSY FL ST LF	 TE Part # 4-641120-9 19P MTA156 HDR ASSY FL/ST LF	 TE Part # 4-641207-9 19P MTA156 HDR ASSY FL RA LF
 TE Part # 1-644752-9 19P MTA156 HDR ASSY SQ STR F/L	 TE Part # 1-640383-9 19P MTA156 HDR ASSY STR SQ SN	 TE Part # 1-640251-9 19P SL156 HSG W/O LCK RAMP	 TE Part # 4-641209-9 19P MTA156 HDR ASSY FL ST LF
 TE Part # CAT-103156-WBHSM Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156	 TE Part # 1-640389-9 19P MTA156 HDR ASSY SQ R/A F/L	 TE Part # 1-640387-9 19P MTA156 HDR ASSY SQ R/A	 TE Part # 4-640433-9 19P MTA156 CONN ASSY 22AWG RED
 TE Part # 4-643817-9 19P MTA156 CONN ASSY 18AWG LF	 TE Part # 4-644769-9 19P MTA156 HDR ASSY R/A SQ LF	 TE Part # 1-644753-9 19P MTA156 HDR ASSY RN STR F/L	 TE Part # 4-641210-9 19P MTA156 HDR FLRA FB 30AU LF

Also in the Series | MTA 156

 Connector Caps & Covers(89)	 Connector Contacts(4)	 Connector Hardware(2)	 Insertion & Extraction Tools(1)
--	---	--	--



PCB Headers & Receptacles(677)



Power Contacts(3)




Rectangular Power Connectors(1178)




Wire-to-Board Headers & Receptacles (677)

Customers Also Bought



TE Part #880665-2
RING TONGUE




TE Part #5069856066
CGPT-9.5/4.8-0-30MM




TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #881016-2
RING TONGUE 6.0-10.0 MM2 1.00X22.7 TPBR



TE Part #962321-1
2X6P MOD4 BUCHS-GEH



TE Part #D812093001
ACW0219-0.50-61(NS)



TE Part #CAT-M8793-T273
MOS, RECEPTACLE AND TAB

Documents

Product Drawings

19P MTA156 FD-THRU COVER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-643071-9_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-643071-9_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-643071-9_M.3d_stp.zip

English

3D PDF



English

Customer View Model

[ENG_CVM_1-643071-9_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_1-643071-9_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-643071-9_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Application Specification

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

Japanese

Instruction Sheets

Instruction Sheet (U.S.)

English