### **AC/DC Industrial Power Supply**

- Slim profile, for DIN-rail mounting
- Alternative side-mounting for flat panels
- High power factor by active power correction
- Very high efficiency up to 95%
- Back power immunity
- 150% peak current for 4 s
- Operating temperature range: -40°C to +70°C max.
- Adjustable output voltage
- Short circuit and overload protection
- 3 year product warranty





UL 508 UL 60950-1 IEC 60950-1

This generation of DIN-rail power supplies combines the most efficient circuit topology with optimized cost/performance ratio for industrial environments and for electrical control cabinets. They have a very high efficiency of up to 95.0% which allows a very slim package design. The output voltage is adjustable from -2% to +17%. The case offers the potentially useful feature to fix the DIN-rail clip to the side wall for the mounting inside flat panels. Over a period of minimum 4 seconds they can operate with a boost power of 150%. The boost power facilitates the activation of stepper motors, solenoids or actuators. The units operate with a high power factor of up to 98% by active power factor correction which also keeps the input inrush current low. The TIB series are also available with other nominal power of 80, 120 or 480 Watt (+50% boost power). They come with the safety standard approvals for IEC/EN 60950-1, UL 60950-1 and UL 508.

Models					
Order Code	Output Power	Output Voltage	Output Current	Output Current	Efficiency
	max.	nom. (adjustable)	max.	peak	typ.
TIB 240-124	240 W	24 VDC (23.5 - 28.0 VDC)	10'000 mA	15'000 mA	95 %
TIB 240-148		<b>48 VDC</b> (47.0 - 56.0 VDC)	5'000 mA	7'500 mA	95 %

Input Specifications			
Input Voltage		85 - 264 VAC (Full Range)	
Input Frequency		45 - 65 Hz	
Power Consumption	- at no Load	2'300 mW typ.	
Input Inrush Current	- at 230 VAC	30 A max.	
	- at 115 VAC	15 A max.	
Power Factor	- at 230 VAC	0.92 min. (Active Power Factor Correction)	
	- at 115 VAC	0.98 min. (Active Power Factor Correction)	

<b>Output Specificati</b>	ons		
Output Voltage Adjustment		24 VDC model:	23.5 - 28.0 VDC
		48 VDC model:	47.0 - 56.0 VDC
			By trim potentiometer
			Output power must no exceed rated power!
Regulation	- Input Variation (Vmin - Vmax)		0.1% max.
	- Load Variation (10 - 90%)		0.5% max.
Output Current peak			Peak Power: 105 - 150% of lout max.
			Peak Operation Time: 4 s max. (switch off)
			Off Time: 10 s typ.
			In peak power mode, the unit continuously
			switches off the output voltage after 4 s and
			restarts after approx. 10 s.
Ripple and Noise			100 mVp-p max.
(20 MHz Bandwidth)		48 VDC model:	200 mVp-p max.
Capacitive Load			Infinite
Minimum Load			not required
Temperature Coefficient			±0.02 %/K max.
Hold-up Time	- at 230 VAC		20 ms min.
	- at 115 VAC		20 ms min.
Start-up Time	- at 230 VAC		2'000 ms max.
	- at 115 VAC		2'000 ms max.
Overload Protection			CC-Mode
Output Current Limitation			155% min. of lout max.
Short Circuit Protection			Switch off after 4 s delay, automatic restart
Overvoltage Protection			<b>117 - 146% of Vout nom.</b> (depending on model 32 - 35 VDC (24 VDC model) 56 - 60 VDC (48 VDC model) (In case of an internal error a second voltage reg- ulation loop keeps the output voltage at a save level, the power supply turnes off and tries to restart after 10 s.)
Transient Response	- Peak Variation		600 mV max. (10% to 90% Load Step)
	- Response Time		<b>2000 μs typ.</b> (10% to 90% Load Step)
Safety Specification			
Safety Standards	- IT / Multimedia Equipment		IEC 60950-1
cally clandards			EN 60950-1
			UL 60950-1
			CSA-C22.2, 60950-1-07
	- Industrial Control Equipment		UL 508
	- Certification Documents		www.tracopower.com/overview/tib240
Protection Class			Class   Prepared: Connection to PE

Continidation Decedition is	
Protection Class	Class I Prepared: Connection to PE
Pollution Degree	PD 2: Office or Laboratory Environments
Over Voltage Category	OVC II

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

\_\_\_\_

EMC Specificat	ions	
EMC Emissions		EN 61000-6-3 (Generic Residential) EN 61204-3 (Low Voltage Power Supplies) EN 50121-3-2 (EMC for Rolling Stock)
	- Conducted Emissions	EN 50121-4 (Railway Application Signalling) EN 55011 class B (internal filter) EN 55032 class B (internal filter)
	- Radiated Emissions	EN 55032 class B (internal filter) EN 55032 class B (internal filter) EN 55032 class B (internal filter)
	- Harmonic Current Emissions	EN 61000-3-2, class A
EMC Immunity		EN 50121-3-2 (EMC for Rolling Stock) EN 50121-4 (Railway Application Signalling) EN 61000-6-2 (Generic Industrial) EN 61204.3 (Law Voltage Rower Supplies)
	- Electrostatic Discharge	EN 61204-3 (Low Voltage Power Supplies) Air: EN 61000-4-2, ±8 kV, perf. criteria A
	- RF Electromagnetic Field	Contact: EN 61000-4-2, ±4 kV, perf. criteria A EN 61000-4-3, 10 V/m, perf. criteria A
	- EFT (Burst) - Surge	EN 61000-4-4, ±2 kV, perf. criteria B
	- Conducted RF Disturbances - PF Magnetic Field	L to PE: EN 61000-4-5, ±2 kV, perf. criteria B EN 61000-4-6, 10 Vrms, perf. criteria A EN 61000-4-8, 30 A/m, perf. criteria A
	- Voltage Dips & Interruptions	230 VAC / 50 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria C 60%, 10 periods, perf. criteria C >95%, 1 period, perf. criteria B >95%, 5 periods, perf. criteria C 20%, 250 periods, perf. criteria C
		115 VAC / 60 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria C 60%, 10 periods, perf. criteria C >95%, 1 period, perf. criteria B >95%, 5 periods, perf. criteria C 20%, 250 periods, perf. criteria C
	- Voltage Sag Immunity	SEMI F47, criteria A

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +70°C
Power Derating	- High Temperature	2 %/K above 60°C (at standard operation)
		3 %/K above 60°C (at peak power mode)
	- Low Input Voltage	3 %/V below 90 VAC (at standard operation)
		1.5 %/V below 100 VAC (at peak power mode)
Cooling System		Natural convection (no internal fan, 20 LFM)
Altitude During Operation	1	2000 m max.
Switching Frequency		<b>75 - 100 kHz</b> (PWM)
nsulation System		Reinforced Insulation
solation Test Voltage	- Input to Output, 60 s	4'250 VDC
	- Input to Case or PE, 60 s	1'500 VDC
	- Output to Case or PE, 60 s	750 VDC
Creepage	- Input to Output	8 mm min.
	- Input to Case or PE	4 mm min.
	- Output to Case or PE	1.5 mm min.
Clearance	- Input to Output	8 mm min.
	- Input to Case or PE	4 mm min.
	- Output to Case or PE	1.5 mm min.

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Leakage Current	0		3500 μA max. 310 μA max.	
Reliability	- Calculated MTBF		1'300'000 h (IEC 61709)	
Environment	- Vibration		EN 61373	
			IEC 60068-2-6	
			3 axis, sine sweep, 10 - 55 Hz, 2 g, 11 oct/min	
	- Mechanical Shock		EN 61373	
			IEC 60068-2-27	
			3 axis, 25 g half sine, 11 ms shock	
Housing Material			Aluminium (Chassis)	
			Stainless Steel (Cover)	
Connection Type			Screw Terminal	
Mounting	- DIN Rail		For DIN-rails as per EN 50022-35×15/7.5	
Weight			643 g	
Thermal Impedance			0.95 K/W	
Power Back Immunity		24 VDC model:	35 V max.	
		48 VDC model:	60 V max.	
			When external voltage is supplied above set out-	
			put voltage and below OVP threshold, the power	
			supply will function normally without switch off or	
			destruction, even if external voltage is applied	
			continuously.	
Power OK Signal			Relay Output	
	- Trigger Threshold	24 VDC model:	OK: 22.5 VDC, Off: 21.5 VDC	
		48 VDC model:	OK: 45 VDC, Off: 43 VDC	
	- Power OK		Relay contact closed	
	- Power Off		Relay contact open	
	- Pin Specifications		30 VDC / 1 A max.	
Status Indicator			Also indicated by green LEDs: front and side	
Environmental Compliance	- Reach		www.tracopower.com/info/reach-declaration.pdf	
	- RoHS		www.tracopower.com/info/rohs-declaration.pdf	


#### Supporting Documents

Overview Link (for additional Documents)


www.tracopower.com/overview/tib240

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

### Blockdiagram




### **Outline Dimensions**



All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.



#### Alternative side mounting



© Copyright 2019 Traco Electronic AG



Specifications can be changed without notice.