



8/16/24-Port Gigabit Switch

TL-SG1008 / TL-SG1016D / TL-SG1024D

Overview

The TL-SG1008/TL-SG1016D/TL-SG1024D Gigabit Ethernet Switch provides you with a high-performance, low-cost, easy-to-use, seamless and standard upgrade to improve old network to 1000Mbps network. All 8/16/24 ports support auto MDI/MDIX, no need to worry about the cable type, simply plug and play. Moreover, with the innovative energy-efficient technology, the TL-SG1008/TL-SG1016D/TL-SG1024D can save up to 75%/40%/20%* of the power consumption and 80% of the packaging material can be recycled, making it an eco-friendly solution for your business network.

Green Technology

- Saving power 75%/70%/60%
- Recyclable packaging material

High Performance

- IEEE 802.3x flow control
- Non-blocking switching architecture
- 16/32/48 Gbps Switching Capacity
- Store and forward
- Auto-MDI/MDIX
- Auto-negotiation
- MAC address auto-learning and auto-aging
- 10KB Jumbo frame

Easy to use

- Plug and Play design
- Quiet/Fanless design



8/16/24-Port Gigabit Switch

TL-SG1008 / TL-SG1016D / TL-SG1024D

TP-LINK Green Technology

This new generation TL-SG1008/TL-SG1016D/TL-SG1024D Gigabit Switch features the latest innovative energy-efficient technologies that can greatly expand your network capacity with much less power. It automatically adjusts power consumption according to the link status and cable length to limit the carbon footprint of your network. It also complies with the EU'S RoHS, prohibiting the use of certain hazardous materials. Besides, 80% of the packaging material can be recycled.

High Performance

All 8/16/24 ports are Gigabit RJ-45 ports which can provide large file transferring and also be compatible with 10Mbps and 100Mbps Ethernet devices. Featuring non-blocking switching architecture, TL-SG1008/TL-SG1016D/TL-SG1024D forwards and filters packets at full wire-speed for maximum throughput. With 10KB Jumbo frame, the performance of large files transfers is improved significantly. And IEEE 802.3x flow control for Full Duplex mode and backpressure for Half Duplex mode alleviate the traffic congestion and make The TL-SG1008/TL-SG1016D/TL-SG1024D work reliably. It's a perfect choice to update your network to Gigabit while protecting your previous investment properly.




Easy to Use

The auto features of this gigabit switch make installation plug and play and hassle-free. No configuring is required. Auto MDI/MDIX eliminates the need for crossover cables. Auto-negotiation on each port senses the link speed of a network device (10, 100, or 1000 Mbps) and intelligently adjusts for compatibility and optimal performance.



- Details:<http://www.tp-link.com/support/Localesupport.asp>
- German/Austrian/Swiss users are not included

Specifications:

| Product Picture |  |  |  |
|------------------------------|---|---|---|
| Model | TL-SG1008 | TL-SG1016D | TL-SG1024D |
| Standards | IEEE 802.3, IEEE 802.3u, IEEE 802.3x | IEEE 802.3, IEEE 802.3u, IEEE 802.3x | IEEE 802.3, IEEE 802.3u, IEEE 802.3x |
| Network Ports | 8*10/100/1000Mbps RJ45 ports | 16*10/100/1000Mbps RJ45 ports | 24*10/100/1000Mbps RJ45 ports |
| Auto Negotiation | YES | YES | YES |
| Auto MDI/MDIX | YES | YES | YES |
| Systems | Windows 2000/XP/Vista/7 Linux/MAC OS | Windows 2000/XP/Vista/7 Linux/MAC OS | Windows 2000/XP/Vista/7 Linux/MAC OS |
| Forwarding Mode | Store and Forward | Store and Forward | Store and Forward |
| Switch Capacity | 16 Gbps | 32 Gbps | 48 Gbps |
| MAC Address Table | 8 K | 8 K | 8 K |
| Jumbo Frame | 10 KB | 10 KB | 10 KB |
| Flow Control | YES | YES | YES |
| Fanless | YES | YES | No |
| Power Saving | Up to 75% | Up to 40% | Up to 20% |
| LED | Power、1000Mbps、Link/Act | Power、1000Mbps、Link/Act | Power、1000Mbps、Link/Act |
| Dimensions | 294*180*44 mm | 294*180*44 mm | 294*180*44 mm |
| Operating Temperature | 0°C~40°C (32°F~104°F) | 0°C~40°C (32°F~104°F) | 0°C~40°C (32°F~104°F) |
| Storage Temperature | -40°C~70°C (-40°F~158°F) | -40°C~70°C (-40°F~158°F) | -40°C~70°C (-40°F~158°F) |
| Operating Humidity | 10%~90% non-condensing | 10%~90% non-condensing | 10%~90% non-condensing |
| Storage Humidity | 5%~90% non-condensing | 5%~90% non-condensing | 5%~90% non-condensing |
| Ordering Information | 8-Port Gigabit switch | 16-Port Gigabit switch | 24-Port Gigabit switch |

* Maximum power savings when compared to a TP-LINK conventional switch, the real saving rate may vary based on the usage condition. Currently TL-SG1024D is not for our quiet design, but soon we will escalate it.