# TP-LINK®

# 150Mbps Wireless N PCI Express Adapter

## TL-WN781ND

### • Features:

- · Wireless N speed up to 150Mbps
- PCI Express(x1) connector, compatible with other standard PCI Express slot, x1, x2, x8, or x16
- Easily setup an encrypted security network at a push the WPS (Wi-Fi Protected Setup) button
- Detachable antennas allow for better alignment and stronger antenna upgrades
- Supports 64/128-bit WEP, WPA/WPA2, WPA-PSK/WPA2-PSK (TKIP/AES), IEEE 802.1X
- Supports Roaming technology, guaranteeing the client wireless connections
- Supports Windows 7(32/64bits), Windows Vista (32/64bits), Window XP(32/64bits)




### • Description:

The TP-LINK 150Mbps Wireless N PCI Express Adapter TL-WN781ND is designed to connect a desktop to a wireless network, enabling users to access a high-speed Internet connection. Featuring a wireless N speed up to 150Mbps, it allows users to get a better Internet experience, such as downloading, online gaming, video streaming and so on. Furthermore, the 150Mbps Wireless N PCI Express(x1) Adapter provides a wider compatibility, fitting with any standard PCI Express slot, x1, x2, x8, or x16.

# • Specifications:

| IARDWARE FEATURES     |  |
|-----------------------|--|
| nterface              | PCI Express  |
| Dimensions (Wx Dx H)  | 4.8x 3.1x 0.8in. (120.8x 78.5x 21.5mm)                       |
| Antenna Type          | Detachable Omni Directional (RP-SMA)                         |
| Antenna Gain          | 2dBi   |
| WIRELESS FEATURES     |  |
| Wireless Standards    | IEEE 802.11n, IEEE 802.11g, IEEE 802.11b                     |
| requency              | 2.4-2.4835GHz  |
| Wireless Signal Rate  | 11n: Up to 150Mbps(dynamic)                                  |
|                       | 11g: Up to 54Mbps(dynamic)                                   |
|                       | 11b: Up to 11Mbps(dynamic)                                   |
| EIRP                  | <20dBm(EIRP)   |
| Reception Sensitivity | 130M: -68dBm@10% PER   |
|                       | 108M: -68dBm@10% PER   |
|                       | 54M: -68dBm@10% PER  |
|                       | 11M: -85dBm@8% PER   |
|                       | 6M: -88dBm@10% PER   |
|                       | 1M: -90dBm@8% PER  |
| Wireless Modes        | Ad-Hoc / Infrastructure mode                                 |
| Wireless Security     | 64/128-bit WEP, WPA/WPA2, WPA-PSK/WPA2-PSK (TKIP/AES),       |
| Wheless Security      | Wireless MAC Filtering                                       |
| Modulation Technology | DBPSK, DQPSK, CCK, OFDM, 16-QAM, 64-QAM                      |
| OTHERS                |  |
| Certification         | CE, FCC, RoHS  |
| System Requirements   | Windows 7 (32/64bits), Windows Vista (32/64bits), Windows XP |
| , sterr requirements  | (32/64bits)  |
|                       | Operating Temperature: 0°C ~40°C (32°F~104°F)                |
| Environment           | Storage Temperature: -40 °C ~70 °C (-40°F~158°F)             |
|                       | Operating Humidity: 10%~90% non-condensing                   |
|                       | Storage Humidity: 5%~90% non-condensing                      |

## • Diagram:



#### Package:

- 150Mbps Wireless N PCI Express Adapter TI -WN781ND
- One Detachable Omni Directional Antenna
- Quick Installation Guide
- Resource CD

#### **Related Products:**

- 150Mbps Wireless N Router TL-WR741ND
- 150Mbps Wireless N Router TL-WR740N
- 150Mbps Wireless N USB Adapter TL-WN721N