



### LAN Transformer 10-100 Base-T

Part No: TM42430ANL

#### **Description:**

10/100 Base-T transformer Single Port and 24pin SMT

#### **Features:**

3Wire/Cable
Industrial grade
RoHS & REACH Compliant



1.	Introduction	3
2.	Specifications	4
3.	Mechanical	5
4.	Electrical	6
5.	Packaging & Storage	7
	Changelog	8

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

















Featuring a compatible footprint with industry LAN transformers, and designed to work in demanding industrial environmental conditions, the Taoglas TM42430ANL is a 10/100 Base-T Single Port of 24pin with 3 wire Common Mode Choke on the cable side to offer better EMI performance.

Typical applications for this cost-effective part are:

- Industrial Automation
- Hubs
- Routers
- Switches
- Wireless Access Points

The Taoglas Magnetics Product Team have over fifteen years of LAN magnetics design and high-quality manufacturing. With an ever-expanding portfolio, we provide trusted products and services to customers within a wide range of applications such as: Networking and Interconnect Devices, Servers, Switches, Router, Communication systems and any Digital Consumer electronics.

The Taoglas Exos Series offer an extensive product line of LAN Transformers designed for commercial and industrial grade applications, supporting 10/100 Base-T (Exos100 Series), 1G Base-T (Exos1G Series) and 10G Base-T (Exos10G Series). These products include Single, Dual, and Quad configurations not only for standard applications but also for Power over Ethernet (PoE, PoE+, PoE++).

For more information on the range of products or for assistance with integration, contact your regional Taoglas customer support team.



# 2. Specifications

Electrical Performance @25°C				
Inductance OCL	350μH MIN @ 100K	Hz 0.1V 8mA DC Bias		
Turns Ratio (±2%)	TX=1CT: 1CT	RX=1CT: 1CT		
Primary Leakage	0.35uH Max @ 100Khz, 0.1Vrms			
Cw/w	35pF Max. Primary to Secondary			
DCR	Primary: $0.9\Omega$ Max, Secondary: $1.4\Omega$ Max			
	-1.0dB MAX	@ 0.3-80KHz		
Insertion Loss	-1.4dB MAX	( @ 100MHz		
	-3.0dB MAX	X @125MHz		
	-18dB MIN @	<u>ම</u> 0.5-15MHz		
Return Loss	-14dB MIN (	@ 30-45MHz		
	-10dB MIN @ 45-60MHz			
	-6dB MIN @	9 60-80MHz		
Crosstalk	-40dB MII	N @ 1MHz		
	-55-24log(f/10MHz) o	dB MIN @ 30-100MHz		
DCMR	-50dB MII	N @ 2MHz		
	-43+22log(f/30) dB	MIN @ 30-100MHz		
Hi-Pot	4000V	rms 60S		

Environmental Specifications				
Operating Temperature	-40°C TO +85°C			


Compliance		
UL recognized - FILE NO. E528697		
RoHs compliant		

Storage requirements				
Humidity	Storage Temperature			
MSL - 1	-40°C TO +85°C			



## 3. Mechanical


### 3.1 Mechanical Drawings



Mechanical Specifications				
Length	13.6 mm			
Width	15.2 mm			
Height	5.7 mm			
Mounting Style	Surface Mount (SMT)			

Dimensions are in millimeters with the following tolerances:  $X.XX = \pm 0.25$ 

### 3.2 Pad Layout




Suggested Pad Layout

Dimensions are in millimeters with the following tolerances: X.XX =  $\pm 0.10$ 




## 4. Electrical

### 4.1 Electrical Drawings



#### 4.2 Profile of Reflow Solder





## 5. Packaging and Storage

### **5.1** SPQ


400 pcs/reel

A (Carrier Tape Width): 24±0.3 mm

B (Sprocket hole to Cavity center): 11.5±0.2 mm

C (Cavity width): 15.9±0.2 mm


Reel weight: 760 g



1CTN = 4 reels = 1600 pcs


Carton dimensions: 370\*370\*250mm

Carton Weight: 6 kg





# Changelog







www.taoglas.com

