





Conductive Polymer Tantalum Solid Capacitors


Surface Mount Type **TPE** series **B** size

Features


- Small size (L 3.5 × W 2.8 × H 1.9 mm)
- Low ESR (15 mΩ max.)
- RoHS compliance, Halogen free

Specifications								
Size code	B2							
Category temp. range	–55 ℃ to +105 ℃							
Rated volt. range		2.0 V to 10 V						
Category volt. range		1.8 V to 8 V						
Rated cap. range	47 μF to 470 μF							
Capacitance tolerance	±20 % (120 Hz / +20 ℃)							
Leakage current	Please see the attached characteristics list							
Dissipation factor(tan δ)	Please see the attached characteristics list							
Surge voltage (V)	Rated voltage × 1.15							
Endurance	Capacitance change Dissipation factor(tan δ) Leakage current	cts : +85 ℃ 1000 h, rated voltage applied Within ±20 % of the initial value ≦ 1.5 times of the initial limit Within the initial limit						
Damp heat (Steady State)	+60 ℃, 90 % to 95 % RH, 5 Capacitance change	500 h, No-applied voltage Within +50 %, -20 % of the initial value (2R5TPE220MAZB (MAPB, MAFB), 2R5TPE330MAZB, 2TPE330MAFB (MADGB), 2TPE470MAJGB (MAFB), 2TPE330MFB, ETPE330MAFB (MA9GB)) Within +40 %, -20 % of the initial value (Except for above model)						
	Dissipation factor(tan δ) Leakage current	≤ 1.5 times of the initial limit ≤ 3 times of the initial limit						

Marking



Dimensions (not to scale)



TPE (B size) series

	racte	101100				200.0	70								Elas	or lif-
	Rated	Cate- Cate- (mm)							Specifi	cations		Standard			or life vel	
Rated voltage (V)	temper- ature (°C)	Cate- gory voltage (V)	gory temper- ature (℃)	Rated capaci- tance (µF)	L	W	Н	Size code	Ripple ^{*1} current (mA rms)	ESR ^{*2} (mΩ max.)	tan δ ^{*3}	LC ^{*4} (μΑ)	Part number	Min. packaging q'ty (pcs)	Reflow temp ≤260°C	Reflo
NRF	FND 105	2.0	105		3.5	2.8	1.9		2000	15	0.08	132.0	2TPE330MFB	2000		
NRF	FND 85	1.8	105	330	3.5	2.8	1.9	В2	2000	15	0.08	132.0	2TPE330MAFB	2000	3	3
2.0 NR	FND 85	1.8	105		3.5	2.8	1.9		2000	13/300kHz	0.10	132.0	2TPE330MADGB	2000		
	85	1.8	105	470	3.5	2.8	1.9		2300	15	0.10	188.0	2TPE470MAFB	2000		
	85	1.8	105		3.5	2.8	1.9		2300	11/300kHz	0.08	188.0	2TPE470MAJGB	2000		
	85	2.0	105		3.5	2.8	1.9		2000	15	0.08	110.0	2R5TPE220MAFB	2000		
	105	2.5	105		3.5	2.8	1.9		1800	15/300kHz	0.08	110.0	2R5TPE220MFGB	2000		
	105	2.5	105		3.5	2.8	1.9		1700	21	0.08	55.0	2R5TPE220MLB	2000		
	85	2.0	105	220	3.5	2.8	1.9	B2	1600	25	0.08	55.0	2R5TPE220MAPB	2000	3	3
	105	2.5	105		3.5	2.8	1.9	DZ	1400	35	0.08	55.0	2R5TPE220MZB	2000		
	85	2.0	105		3.5	2.8	1.9		1400	35	0.08	55.0	2R5TPE220MAZB	2000	_	
2.5	105	2.5	105		3.5	2.8	1.9		1400	30	0.08	55.0	2R5TPE220MUB	2000		
	85	2.0	105		3.5	2.8	1.9		1400	35	0.08	82.5	2R5TPE330MAZB	2000		
	85	2.0	105	330	3.5	2.8	1.9		3200	9/300kHz	0.08	165.0	ETPE330MA9GB	2000		
NRF	105	2.5	105		3.5	2.8	1.9		3200	9/300kHz	0.08	165.0	ETPE330M9GB	2000		
	ND 85	2.0	105	330	3.5	2.8	1.9	B2	2700	15	0.08	165.0	ETPE330MAFB	2000	3	3
	105	2.5	105	330	3.5	2.8	1.9		2700	15	0.08	165.0	ETPE330MFB	2000		
	105	2.5	105	330	3.5	2.8	1.9		2450	18	0.08	165.0	ETPE330MIB	2000		
	105	4.0	105		3.5	2.8	1.9		1400	35	0.08	40.0	4TPE100MZB	2000		
	105	4.0	105	100	3.5	2.8	1.9		950	70	0.08	40.0	4TPE100MBB	2000		
	105	4.0	105		3.5	2.8	1.9		1300	40	0.08	40.0	4TPE100MWB	2000		
4.0	85	3.2	105	150	3.5	2.8	1.9		1400	35	0.08	60.0	4TPE150MAZB	2000		
4.0	85	3.2	105	220	3.5	2.8	1.9		1400	35	0.08	88.0	4TPE220MAZB	2000		
	105	4.0	105		3.5	2.8	1.9		1350	35	0.10	88.0	4TPE220MZB	2000		
	105	4.0	105		3.5	2.8	1.9		1150	45	0.10	88.0	4TPE220MVB	2000		
	105	4.0	105		3.5	2.8	1.9		950	70	0.10	88.0	4TPE220MBB	2000		
	105	6.3	105	100	3.5	2.8	1.9		1600	25	0.08	63.0	6TPE100MPB	2000		
	85	5.0	105		3.5	2.8	1.9	9 B2	1400	35	0.08	63.0	6TPE100MAZB	2000		
	105	6.3	105		3.5 2.8		1.9		1400	35	0.08	63.0	6TPE100MZB	2000	3	3
	105	6.3	105		3.5	2.8	1.9		950	70	0.08	63.0	6TPE100MBB	2000		
	105	6.3	105		3.5	2.8	1.9		1300	40	0.08	63.0	6TPE100MWB	2000		
	105	6.3	105		3.5	2.8	1.9		1200	45	0.08	63.0	6TPE100MVB	2000		
6.3	85	5.0	105	120	3.5	2.8	1.9		1400	35	0.08	75.6	6TPE120MAZB	2000		
0.0	85	5.0	105	150	3.5	2.8	1.9		1600	25	0.08	94.5	6TPE150MAPB	2000		
	85	5.0	105		3.5	2.8	1.9		1400	35	0.08	94.5	6TPE150MAZB	2000		
	85	5.0	105		3.5	2.8	1.9		1400	35	0.10	138.6	6TPE220MAZB	2000	-	
	85	5.0	105		3.5	2.8	1.9		1600	25	0.10	138.6	6TPE220MAPB	2000	-	
	105	6.3	105	220	3.5	2.8	1.9		1150	45	0.10	138.6	6TPE220MVB	2000	-	
	105	6.3	105		3.5	2.8	1.9		950	70	0.10	138.6	6TPE220MBB	2000	-	
	105	6.3	105		3.5	2.8	1.9		1350	35	0.10	138.6	6TPE220MZB	2000		
8.0	85	6.3	105	100	3.5	2.8	1.9		1400	35	0.08	80.0	8TPE100MAZB	2000		
10	85	8.0	105	47	3.5	2.8	1.9		1400	35	0.08	47.0	10TPE47MAZB	2000		L

^{*1:} Ripple current (100 kHz / +45 ℃)

Not recommended for new design

^{*2:} ESR (100 kHz / +20 °C)


^{*3:} tan δ (120 Hz / +20 °C)

^{*4:} After 5 minutes

[♦] Please refer to each page in this catarog for "Reflow conditions", "Taping specifications" and "Floor life level".

[◆] Small order quantity (500 pcs/reel) is available with TPE series. Please contact our sales representative if you prefer it.









Surface Mount Type

TPE series D size




Features


- Low profile (Height 1.5 mm max.)
- Low ESR (7 mΩ max.)
- Large capacitance (1500 µF max.)
- RoHS compliance, Halogen free

Specifications										
Size code	D15E	D2E	D3L	D4						
Category temp. range	–55 °C to +105 °C									
Rated volt. range	6.3 V	2.5 V to 10 V								
Category volt. range	5.0 V	2.5 V to 10 V								
Rated cap. range	470 µF	68 μF to 470 μF	68 μF to 470 μF							
Capacitance tolerance	±20 % (120 Hz / +20 ℃)									
Leakage current	Please see the attached characteristics list									
Dissipation factor(tan δ)	Please see the attached characteristics list									
Surge voltage (V)	Rated voltage × 1.15									
Endurance	(6TPE330MAP, 6TPE470 Capacitance change Dissipation factor(tan δ) Leakage current	ucts: +85 °C 1000 h, rated MAZU: +85 °C 2000 h, ra Within ±20 % of the initial Within the initial limit	ts: +85 ℃ 1000 h, rated voltage applied AZU: +85 ℃ 2000 h, rated voltage applied) Within ±20 % of the initial value ≤ 1.5 times of the initial limit							
	+60 ℃, 90 % to 95 % RH,									
Damp heat (Steady State)	Capacitance change	(2R5TPE220M (I, F, 9), 2R5TPE470M (I, F, C, 9	Within +50 %, -20 % of the initial value (2R5TPE220M (I, F, 9), 2R5TPE330M (I, F, C, 9, 7), 2R5TPE470M (I, F, C, 9, 7), 2R5TPE1000MF, 2R5TPE1500M (F, C)) Within +40 %, -20 % of the initial value (Except for above model)							
	Dissipation factor(tan δ)		, , ,	,						
	Leakage current	eakage current ≤ 3 times of the initial limit								

Marking



Dimensions (not to scale)



TPE (D size) series

		ristics			<u> </u>	200.0	70								Elas	or D
	Rated	Cate-	Cate-	Poted	Ca	ase si (mm)	ze			Specifi	cations		Standard		Floo	or III evel
Rated	temper-	gory	gory	Rated capaci-		()		Size						Min.		
oltage	ature	voltage	temper-	tance		W	Н	code	Ripple*1	ESR*2	- *3	LC^{*4}	Dort number	packaging	Reflow temp	Ref
(V)	(℃)	(V)	ature	(µF)	L	VV	п		(mA rms)	(mΩ max.)	tan δ ^{*3}	(µA)	Part number	q'ty	≤260°C	
			(℃)						(IIIA IIIIS)					(pcs)		
	105	2.5	105		7.3	4.3	1.8		3900	9	0.10	55.0	2R5TPE220M9	3000		
	105	2.5	105	220	7.3	4.3	1.8		3100	15	0.10	55.0	2R5TPE220MF	3000		
_	105	2.5	105		7.3	4.3	1.8		2800	18	0.10	55.0	2R5TPE220MI	3000		
NRF	105 105	2.5 2.5	105 105		7.3	4.3	1.8		2400 4400	25 7	0.10	55.0 82.5	2R5TPE220M 2R5TPE330M7	3000 3000		
	105	2.5	105	1	7.3	4.3	1.8		3900	9	0.10	82.5	2R5TPE330M7 2R5TPE330M9	3000		
	105	2.5	105		7.3	4.3	1.8		3500	12	0.10	82.5	2R5TPE330MC	3000		
	105	2.5	105	330	7.3	4.3	1.8	D2E	3100	15	0.10	82.5	2R5TPE330MF	3000		
	105	2.5	105		7.3	4.3	1.8		2800	18	0.10	82.5	2R5TPE330MI	3000		
NRF	ND 105	2.5	105		7.3	4.3	1.8		2400	25	0.10	82.5	2R5TPE330M	3000	3	
2.5	105	2.5	105		7.3	4.3	1.8		4400	7	0.10	117.5	2R5TPE470M7	3000		
	105	2.5	105		7.3	4.3	1.8		3900	9	0.10	117.5	2R5TPE470M9	3000		
	105	2.5	105	470	7.3	4.3	1.8		3500	12	0.10	117.5	2R5TPE470MC	3000		
	105	2.5	105		7.3	4.3	1.8		3100	15	0.10	117.5 117.5	2R5TPE470MF	3000		
	105 105	2.5 2.5	105 105		7.3	4.3	1.8		2800 3500	18 12	0.10 0.10	170.0	2R5TPE470MI 2R5TPE680MCL	3000 2500		
	105	2.5	105	680	7.3	4.3	2.8	D3L	3100	15	0.10	170.0	2R5TPE680MFL	2500		
	105	2.5	105	000	7.3	4.3	2.8	DOL	1850	40	0.10	170.0	2R5TPE680MWL	2500		
	105	2.5	105	1000	7.3	4.3	3.8		3900	15	0.15	250.0	2R5TPE1000MF	2000		
	105	2.5	105		7.3	4.3	3.8	D4	4400	12	0.15	375.0	2R5TPE1500MC	2000		1
	105	2.5	105	1500	7.3	4.3	3.8		3900	15	0.15	375.0	2R5TPE1500MF	2000	_	
	105	4.0	105	150	7.3	4.3	1.8		2800	18	0.10	60.0	4TPE150MI	3000		1
	105	4.0	105		7.3	4.3	1.8		3100	15	0.10	88.0	4TPE220MF	3000		
	105	4.0	105	220	7.3	4.3	1.8		2800	18	0.10	88.0	4TPE220MI	3000		
	105	4.0	105	330	7.3	4.3	1.8	D2E	2400	25	0.10	88.0	4TPE220M	3000		
4.0	105	4.0	105		7.3	4.3	1.8	-	1750 2800	45	0.10	88.0	4TPE220MV	3000		
	105 105	4.0 4.0	105 105		7.3	4.3	1.8		2400	18 25	0.10 0.10	132.0 132.0	4TPE330MI 4TPE330M	3000		
	105	4.0	105	330	7.3	4.3	1.8		1850	40	0.10	132.0	4TPE330MW	3000		
	105	4.0	105		7.3	4.3	2.8		3500	12	0.10	188.0	4TPE470MCL	2500		
	105	4.0	105	1	7.3	4.3	2.8	-	3100	15	0.10	188.0	4TPE470MFL	2500		
	105	4.0	105	470	7.3	4.3	2.8	D3L	2800	18	0.10	188.0	4TPE470MIL	2500		
	105	4.0	105]	7.3	4.3	2.8		2400	25	0.10	188.0	4TPE470ML	2500	3	
	105	4.0	105		7.3	4.3	2.8		1850	40	0.10	188.0	4TPE470MWL	2500		
	105	6.3	105		7.3	4.3	1.8		2800	18	0.10	63.0	6TPE100MI	3000		
	105	6.3	105	100	7.3	4.3	1.8		2400	25	0.10	63.0	6TPE100M	3000		
	105 105	6.3 6.3	105 105		7.3 7.3	4.3	1.8		1850 3100	40 15	0.10 0.10	63.0 94.5	6TPE100MW	3000		
	105	6.3	105	150	7.3	4.3	1.8		2800	18	0.10	94.5	6TPE150MF 6TPE150MI	3000		
	105	6.3	105	130	7.3	4.3	1.8	D2E	2400	25	0.10	94.5	6TPE150M	3000	-	
	105	6.3	105		7.3	4.3	1.8		2800	18	0.10	138.6	6TPE220MI	3000		
	105	6.3	105	220	7.3	4.3	1.8		2400	25	0.10	138.6	6TPE220M	3000		
	85	5.0	105		7.3	4.3	1.8		2400	25	0.10	138.6	6TPE220MAP	3000		
	105	6.3	105		7.3	4.3	1.8		1850	40	0.10	138.6	6TPE220MW	3000		
	105	6.3	105	200	7.3	4.3	2.8	D3L	2800	18	0.10	138.6	6TPE220MIL	2500	-	1
	85	5.0	105	330	7.3	4.3	1.8	D2E	2400	25	0.10	207.9	6TPE330MAP	3000	3	4
5.3 NRE	FND 85	5.0 5.0	105 105	330	7.3	4.3	2.8	D3L	2400 3900	25 9/500kHz	0.10	207.9	6TPE330MAL 6TPE330MA9EL	2500 2500	3	
NR	105	6.3	105		7.3	4.3	2.8	-	3100	9/500KHZ	0.10	207.9	6TPE330MFL	2500	-	
	105	6.3	105	330	7.3	4.3	2.8	D3L	2800	18	0.10	207.9	6TPE330MIL	2500	-	
	105	6.3	105	330	7.3	4.3	2.8	1	2400	25	0.10	207.9	6TPE330ML	2500	-	
	85	5.0	105		7.3	4.3	3.8	D4	4400	10	0.10	207.9	6TPE330MAA	2000		
NRF	ND 85	5.0	105		7.3	4.3	1.4	D4 D15E	1700	35	0.10	296.1	6TPE470MAZU	4000		
	105	6.3	105		7.3	4.3	3.8		3500	18	0.15	296.1	6TPE470MI	2000		
	105	6.3	105	470	7.3	4.3	3.8		3000	25	0.15	296.1	6TPE470M	2000	3	
	105	6.3	105		7.3	4.3	3.8	D4	2500	35	0.15	296.1	6TPE470MZ	2000	٦	
	105	6.3	105		7.3	4.3	3.8	7-	2350	40	0.15	296.1	6TPE470MW	2000		
	105	6.3	105	680	7.3	4.3	3.8		3500	18	0.15	428.4	6TPE680MI	2000		
	105	6.3	105		7.3	4.3	3.8		3000	25	0.15	428.4	6TPE680M	2000		
	105 105	10 10	105 105	68	7.3	4.3	1.8	D2E	2400 1850	25 40	0.10	68.0 68.0	10TPE68M	3000	-	
	105	10	105	150	7.3	4.3	1.8 2.8		2400	25	0.10 0.10	150.0	10TPE68MW 10TPE150MPL	2500	-	H
10	105	10	105		7.3	4.3	2.8	D3L	2800	25 18	0.10	220.0	10TPE150MPL	2500	-	\vdash
	105	10	105	220	7.3	4.3	2.8	JUL	2400	25	0.10	220.0	10TPE220ML	2500		1
-	105	10	105	330	7.3	4.3	3.8	D4	3000	25	0.10	330.0	10TPE330M	2000		1.

^{*1:} Ripple current (100 kHz / +45 °C)

Not recommended for new design

^{*2:} ESR (100 kHz / +20 ℃)

^{*3:} tan δ (120 Hz / +20 ℃)

^{*4:} After 5 minutes

[♦] Please refer to each page in this catarog for "Reflow conditions", "Taping specifications" and "Floor life level".

[◆] Small order quantity (500 pcs/reel) is available with TPE series. Please contact our sales representative if you prefer it.



Guidelines and precautions regarding the technical information and use of our products described in this online catalog.

- If you want to use our products described in this online catalog for applications requiring special qualities or reliability, or for applications where the failure or malfunction of the products may directly jeopardize human life or potentially cause personal injury (e.g. aircraft and aerospace equipment, traffic and transportation equipment, combustion equipment, medical equipment, accident prevention, anti-crime equipment, and/or safety equipment), it is necessary to verify whether the specifications of our products fit to such applications. Please ensure that you will ask and check with our inquiry desk as to whether the specifications of our products fit to such applications use before you use our products.
- The quality and performance of our products as described in this online catalog only apply to our products when used in isolation. Therefore, please ensure you evaluate and verify our products under the specific circumstances in which our products are assembled in your own products and in which our products will actually be used.
- Please ensure the safety by means of protection circuit, redundant circuit etc. in your system design in order to prevent the occurrence of life crisis and other serious damages due to the failure of our products.
- The products and product specifications described in this online catalog are subject to change for improvement without prior notice. Therefore, please be sure to request and confirm the latest product specifications which explain the specifications of our products in detail, before you finalize the design of your applications, purchase, or use our products.
- The technical information in this online catalog provides examples of our products' typical operations and application circuits. We do not guarantee the non-infringement of third party's intellectual property rights and we do not grant any license, right, or interest in our intellectual property.
- If any of our products, product specifications and/or technical information in this catalog is to be exported, the laws and regulations of the exporting country, especially with regard to security and export control, shall be observed.

<Regarding the Certificate of Compliance with the EU RoHS Directive/REACH Regulations>

- The switchover date for compliance with the RoHS Directive/REACH Regulations varies depending on the part number or series of our products.
- When you use the inventory of our products for which it is unclear whether those products are compliant with the RoHS Directive/REACH Regulation, please select "Sales Inquiry" in the website inquiry form and contact us.

Please note that we do not owe any liability and responsibility if our products are used beyond the description of this catalog or without complying with precautions in this catalog.



Notices

Applicable laws and regulations

- This product complies with the RoHS Directive (Restriction of the use of certain hazardous substances in electrical and electronic equipment (DIRECTIVE 2011/65/EU and (EU)2015/863)).
- No Ozone Depleting Chemicals(ODC's), controlled under the Montreal Protocol Agreement, are used in producing this product. We do not use PBBs or PBDEs as brominated flame retardants.
- Follow export procedures in accordance with the Foreign Exchange and Foreign Trade Law and other export-related laws and regulations when exporting this product.
- These products are not dangerous goods on the transportation as identified by UN(United Nations) numbers or UN classification.

■ Limited applications

- This capacitor is designed to be used for electronics circuits such as audio/visual equipment, home appliances, computers and other office equipment, optical equipment, measuring equipment.
- An advanced specification must be signed individually for high-reliability use that might threaten human life or property due to a malfunction of the capacitor.

■ Intellectual property rights and licenses

• The technical information in this specification provides examples of our products' typical operations and application circuits. We do not guarantee the non-infringement of third party's intellectual property rights and we do not grant any license, right, or interest in our intellectual property.

Items to be observed

■ For specification

- This specification guarantees the quality and performance of the product as individual components.
 - The durability differs depending on the environment and the conditions of usage.
 - Before use, check and evaluate their compatibility with actual conditions when installed in the products.
 - When safety requirements cannot be satisfied in your technical examination, inform us immediately.
- · Do not use the products beyond the specifications described in this document.

■ Upon application to products where safety is regarded as important

If a malfunction of this product may result in the loss of human life or other serious damage, in traffic transportation equipment (trains, automobiles, traffic signals, etc.), medical equipment, aerospace equipment, electric heating equipment, combustion and gas equipment, rotating equipment, disaster prevention and security equipment, etc., ensure safety by giving sufficient consideration to a fail-safe design, for example, by considering the following items.

- (1) The system is equipped with a protection circuit and protection device.
- (2) The system is equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault.

■ Conditions of use

- Before using the products, carefully check the effects on their quality and performance, and determined whether or not they can be used. These products are designed and manufactured for general-purpose and standard use in general electronic equipment. These products are not intended for use in the following special conditions.
 - (1) In liquid, such as Water, Oil, Chemicals, or Organic solvent.
 - (2) In direct sunlight, outdoors, or in dust.
 - (3) In vapor, such as dew condensation water of resistive element, or water leakage, salty air, or air with a high concentration corrosive gas, such as Cl₂, H₂S, NH₃, SO₂, or NOx.
 - (4) In an environment where strong static electricity or electromagnetic waves exist.
 - (5) Mounting or placing heat-generating components or inflammables, such as vinyl-coated wires, near these products.
 - (6) Sealing or coating of these products or a printed circuit board on which these products are mounted, with resin and other material.
 - (7) Using resolvent, water or water-soluble cleaner for flux cleaning agent after soldering. (In particular, when using water or a water-soluble cleaning agent, be careful not to leave water residues)
 - (8) Using in the atmosphere where strays acid or alkaline.
 - (9) Using in the atmosphere where there are excessive vibration and shock.
 - (10) Using in the atmosphere where there are low pressure or decompression.
- Please arrange circuit design for preventing impulse or transitional voltage.
 Ensure that the voltage is lower than the rated voltage in the following condition: shock voltage circuits, transient phenomena in which excessive high voltage is applied in a short period of time, or when pulse high voltage is applied.
- Our products there is a product are using an electrolyte solution. Therefore, misuse can result in rapid deterioration of characteristics and functions of each product. Electrolyte leakage damages printed circuit and affects performance, characteristics, and functions of customer system.



1

Application Guidelines (POSCAP)

1. Circuit design

1.1 Prohibited circuits

Since problems can be expected, POSCAP cannot be used on the following circuits.

- (1) High impedance voltage retention circuits
- (2) Coupling circuit
- (3) Time constant circuits
- (4) Circuits greatly affected by leakage current
- (5) The circuit in which two or more POSCAP are connected in a series so as to raise the endurance voltage.

1.2 Failure and life-span

The failure rate is 0.5 %* / 1000 h (Confidence level: 60 %) based on JIS C 5003.

The mainly failure modes are as follows.

 * B2 size or less : 1.0 %

1.2-1 Contingency failure

The main causes of failure are thermal stresses cause by the soldering or thermal use environment, along with heat stresses, electrical stresses or mechanical stresses. The most common failure mode is a short circuit. In case a short circuit occurs, ensure safety by fully considering the followings.

- (a) If POSCAP emit smoke, turn off the main power of the equipment. In this case, keep your face and hands away from the area.
- (b) It may take a few seconds to a few minutes before POSCAP emits smoke by the situation. When using a protection circuit, design the product so that it operates during this period.
- (c) If the smoke comes into eyes, rinse immediately. If the smoke is inhaled, gargle immediately.
- (d) In case a large current continues to flow after a short circuit, in the worst case, the shorted-out section may ignite. Consider safety designs such as redundant design and protection circuits.

1.2-2 Wear-out failure (lifetime)

When lifetime exceeded the specified guarantee time of Endurance and Damp heat, electrolyte might insulate and cause electric characteristic changed. This is called an open circuit. The rated capacitance values and the electrical characteristics values such as ESR specified in the characteristics list are factory default values. Please carefully design a circuit since rated capacitance values and the electrical characteristics values may change (increase) beyond the specified values under the conditions of rated voltage/temperature and electrical/mechanical performances.

1.3 Reduction of failure stress

When POSCAP is used within the rated voltage, it shows a stable characteristic, but it may be damaged in a short circuit when an overvoltage, for instance, is applied. The time to reach the failure mode can be extended by using POSCAP with reduced environment temperature, ripple current and applied voltage.

Failure rate

- In the case of the endurance which is 105 °C 2000 h.
 0.5 %/1000 h (Environment temp. : 105 °C, Rated voltage or Category voltage applied)
- \cdot In the case of the endurance which is 105 °C 1000 h or 125 °C 1000 h.
 - 1.0 %/1000 h (Environment temp. : 105 $^{\circ}$ C, Rated voltage or Category voltage applied)
- In the case of the endurance which is 85 °C 1000 h.
 - 1.0 %/1000 h (Environment temp. : 85 °C, Rated voltage applied)

1.4 Check the rated performance

After checking the operation and installation environments, design the circuit so that it falls within the rated performance range stipulated in this delivery specification.

1.5 Operating temperature and ripple current

- (1) Set the operating temperature so that it falls within the range stipulated in this delivery specification.
- (2) Do not apply current that exceeds the allowable ripple current. Ripple current should be controlled so that surface temperature of a capacitor do not exceed the rated temperature.

(For questions regarding TQC series, please contact us.)

(3) The ESR values specified in the characteristics list are factory default values.

ESR values may change (increase) beyond the specified values depending on the customer's use conditions.



1.6 Leakage current

Even when the soldering conditions fall within the range of this delivery specifications, leakage current increases a little on occasion. It also increases a little during high temperature storage, high humidity storage Zand temperature cycling with no voltage applied. In cases such as these, leakage current will decrease by applying voltage under the condition of below the POSCAP's maximum operating temperature.

The speed at which the leakage current is restored is increased by applying voltage when the POSCAP's temperature is close to the maximum operating temperature.

1.7 Rapid charge and discharge limitation

Rapid charge and discharge are restricted (for maintainance of high-proof reliability).

A protective circuit is recommended for when a rapid charge or discharge causes excessive rush current since this is main cause of short circuit and large leakage current. Use a protective circuits in case the rush current value exceeds 20 A*.

Be sure to insert a protection resistor of about 1 $k\Omega$ for charge and discharge when measuring the leakage current.

* When TH series use under the ambient temperature more than 105 °C: 10 A, TPU series: 10 A

2. Mounting

2.1 Protect circuit

The failure mode of POSCAP is the short mode. When it breaks down, short electric current flows to it. POSCAP gives off heat by this short current.

Do the following consideration in design fully for the safety because it has a bad influence on the part around POSCAP due to this heat.

- · A protective circuit and a protective device are set up, so as to make the system safer.
- A diffuse circuit and so on is set up, so as to make the system safer such as that a machine may not break down as to the single trouble.

2.2 Considerations when soldering

The soldering conditions are to be within the range prescribed in this delivery specification.

If the specifications are not followed, there is the possibility of degradation of electric characteristic and lifetime when soldering is conducted under conditions that are harsher that those stipulated.

2.3 Others

POSCAP's Electrical characteristics are affected by temperature and frequency fluctuations.

Design circuits after checking the amount of fluctuation.

3. Storage

It is necessary to set an environment to prevent a trouble at the time of soldering by the degradation of solder ability or moisture's getting into the molding resin when POSCAP are stored.

- Please make storage of POSCAP sealing up in the reel and the moisture proof bag at the time of delivery in the following environment. Also, set storage period of unopened as 18 months or shorter after shipment from factory.
 - Room temperature and room humidity (generally: 15 to 35 °C, 45 to 75% RH) are desirable.
 - · Place where POSCAP is not exposed by direct sunshine.
- Please unseal the moisture proof bag just before mounting and use up POSCAP in the moisture proof bag.
 Storage conditions after opening the moisture proof bag are as follows.

Floor life								
Level	Time	Conditions						
2a	4 weeks	≦ 30 °C / 60 %RH						
3	168 hours	≦ 30 °C / 60 %RH						
5	48 hours	≦ 30 °C / 60 %RH						

POSCAP is not compatible with JEDEC J-STD-020, J-STD-033

* Intellectual property right

We, Panasonic Group are providing the product and service that customers can use without anxiety, and are working positively on the protection of our products under intellectual property rights.

Representative patents relating to POSCAP are as follows:

US Patent No.6508800, No.6891717, No.7158368, No.7326260号, No.8081421, No.8149569,

No.8456804, No.8559166