TSM500P02CX

20V P-Channel Power MOSFET

SOT-23



Pin Definition:
1. Gate
2. Source
3. Drain

Key Parameter Performance

Parameter		Value	Unit
V_{DS}		-20	V
$R_{DS(on)}$ (max)	V_{GS} = -4.5V	50	mΩ
	V_{GS} = -2.5V	65	
	V_{GS} = -1.8V	85	
Q_g		9.6	nC

Features

- Fast Switching
- Suited for -1.8V Gate Drive Applications
- Halogen-free

Ordering Information

Part No.	Package	Packing
TSM500P02CX RFG	SOT-23	3Kpcs / 7" Reel

Note: "G" denotes for Halogen- and Antimony-free as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds

Block Diagram



P-Channel MOSFET

Absolute Maximum Ratings (T_C = 25°C unless otherwise noted)

Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V_{DS}	-20	V
Gate-Source Voltage		V_{GS}	±10	V
Continuous Drain Current	T_C = 25°C	I_D	-4.7	A
	T_C = 100°C		-3	A
Pulsed Drain Current (Note 1)		I_{DM}	-18.8	A
Power Dissipation @ T_C = 25°C		P_D	1.56	W
Operating Junction Temperature		T_J	150	°C
Storage Temperature Range		T_{STG}	-55 to +150	°C

Thermal Performance

Parameter	Symbol	Limit	Unit
Thermal Resistance - Junction to Ambient	$R_{\theta JA}$	80	°C/W

Pb-Free RoHS COMPLIANT

Electrical Specifications (T_C = 25°C unless otherwise noted)

Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Static						
Drain-Source Breakdown Voltage	V_{GS} = 0V, I_D = -250μA	BV_{DSS}	-20	--	--	V
Drain-Source On-State Resistance	V_{GS} = -4.5V, I_D = -3A	$R_{DS(ON)}$	--	42	50	mq
	V_{GS} = -2.5V, I_D = -2A		--	57	65	
	V_{GS} = -1.8V, I_D = -1A		--	75	85	
Gate Threshold Voltage	V_{DS} = V_{GS}, I_D = -250μA	$V_{GS(TH)}$	-0.3	-0.6	-0.8	V
Zero Gate Voltage Drain Current	V_{DS} = -20V, V_{GS} = 0V	I_{DSS}	--	--	-1	μA
	V_{DS} = -16V, T_J = 125°C		--	--	-10	
Gate Body Leakage	V_{GS} = ±10V, V_{DS} = 0V	I_{GSS}	--	--	±100	nA
Forward Transconductance (Note 2)	V_{DS} = -10V, I_D = -3A	g_{fs}	--	7	--	S
Dynamic						
Total Gate Charge (Note 2,3)	V_{DS} = -10V, I_D = -3A, V_{GS} = -4.5V	Q_g	--	9.6	--	nC
Gate-Source Charge (Note 2,3)		Q_{gs}	--	1.6	--	
Gate-Drain Charge (Note 2,3)		Q_{gd}	--	2	--	
Input Capacitance	V_{DS} = -10V, V_{GS} = 0V, f = 1.0MHz	C_{iss}	--	850	--	pF
Output Capacitance		C_{oss}	--	70	--	
Reverse Transfer Capacitance		C_{rss}	--	55	--	
Switching						
Turn-On Delay Time (Note 2,3)	V_{DD} = -10V, I_D = -1A, V_{GS} = -4.5V, R_{GEN} =25q	$t_{d(on)}$	--	6	--	ns
Turn-On Rise Time (Note 2,3)		t_r	--	21.6	--	
Turn-Off Delay Time (Note 2,3)		$t_{d(off)}$	--	51	--	
Turn-Off Fall Time (Note 2,3)		t_f	--	13.8	--	
Source-Drain Diode Ratings and Characteristic						
Maximum Continuous Drain-Source Diode Forward Current	Integral reverse diode in the MOSFET	I_S	--	--	-4.7	A
Maximum Pulse Drain-Source Diode Forward Current		I_{SM}	--	--	-18.8	A
Diode-Source Forward Voltage	V_{GS} = 0V, I_S = -1A	V_{SD}	--	--	-1	V

Note:

1. Pulse width limited by safe operating area
2. Pulse test: pulse width Ò300μs, duty cycle Ò2%
3. Switching time is essentially independent of operating temperature.

Pb-Free RoHS COMPLIANT

Electrical Characteristics Curves

Continuous Drain Current vs. Tc



Normalized RDSON vs. T_J



Normalized V_{th} vs. T_J



Gate Charge Waveform



Normalized Transient Impedance



Maximum Safe Operation Area



Pb-Free RoHS COMPLIANT

SOT-23 Mechanical Drawing



Unit: Millimeters

Marking Diagram



50 = Device Code
Y = Year Code
M = Month Code for Halogen Free Product
(**O**=Jan, **P**=Feb, **Q**=Mar, **R**=Apl, **S**=May, **T**=Jun, **U**=Jul, **V**=Aug, **W**=Sep, **X**=Oct, **Y**=Nov, **Z**=Dec)
L = Lot Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.