

General Information

Extended Product Type:	TS 16/4-8-12
Product ID:	2CSM161021R0811
EAN:	8012542369202
Catalog Description:	TS 16/4-8-12 Non-inherently short-circuit proof bell transformers
Long Description:	These transformers with secondary in very low safety voltage for feeding bells are available in 3 series: non-inherently short-circuit proof (TS8), non-inherently short-circuit proof with switch (TS8/SW), non-inherently short-circuit proof (TS16/TS24). No Switch 0-1.

Additional Information

Country of Origin:	Romania (RO)
Customs Tariff Number:	85043121
Data Sheet, Technical Information:	2CSC400002D0209
Declaration of Conformity - CE:	2CSC446002D2701
EAN:	8012542369202
ETIM 4:	EC001547 - Bell transformer
ETIM 5:	EC001547 - Bell transformer
ETIM 6:	EC001547 - Bell transformer
Environmental Information:	See RoHS Information
Instructions and Manuals:	On the product's body
Invoice Description:	TS 16/4-8-12 Non-inherently short-circuit proof bell transformers
Minimum Order Quantity:	1 piece
Object Classification Code:	T
Package Level 1 EAN:	8012542369202
Package Level 1 Gross Weight:	2.2 kg
Package Level 1 Height:	0.077 m
Package Level 1 Length:	0.216 m
Package Level 1 Units:	1 piece
Package Level 1 Width:	0.095 m
Power Supply:	16 V·A
Product Main Type:	TS
Product Name:	Non-inherently short-circuit proof bell transformer
Product Net Depth:	0.065 m
Product Net Height:	0.085 m
Product Net Weight:	0.340 kg
Product Net Width:	0.035 m
Rated Operational Voltage:	230 V AC
RoHS Date:	25/06/2009 0.00.00
RoHS Information:	2CSC446004K0201
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Secondary Voltage:	4-8-12 V AC
Selling Unit of Measure:	piece

