

Identification tags for cable bundle, thermal transfer

The Tiptag PU cable markers consist of a robust and flexible polyurethane material. It is especially suited for harsh environments where the material is exposed to chemical, fluids or abrasion. Tiptag PU's are presented in a special perforated format which include fastening slots for easy fitting with cable ties. They are also suitable for retrofit purposes.

Print from the reel with HellermannTyton's premium range of thermal transfer printers.

A special ribbon has been developed for Tiptag PU to create a "tattoo" effect so that the marking cannot be rubbed off and is particularly durable and resistant to harsh abrasion.

Features and benefits

- Durable and robust polyurethane material
- For large cable bundles and wires
- Flame retardant
- Weather resistant
- Abrasion resistant
- Good resistance to chemicals
- Available in white and yellow as standard
- Perforated format with fastening slots for cable ties




TIPTAG PU – printed mark has a tattoo-like permanency.

| | |
|---------------------------------|--|
| MATERIAL | Polyurethane (PUR) |
| Operating Temperature | -65 °C to +120 °C, intermittent 150 °C |
| Flammability | self-extinguishing, UL 94 V0 (3 mm) |
| Recommended Ribbon Type | TTRC+ |
| Thermal Transfer Printer | TT431, TT4030 |



TIPTAG PU - UV-stabilised Tiptags, Polyurethane



| TYPE | Length (L) | Width (W) | Pack Cont. | Colour | Article-No. |
|----------------|------------|-----------|------------|-------------|-------------|
| TTAGPU11X65WH | 65.0 | 11.0 | 190 pcs. | White (WH) | 556-25012 |
| TTAGPU11X65YE | 65.0 | 11.0 | 190 pcs. | Yellow (YE) | 556-25019 |
| TTAGPU15X65WH | 65.0 | 15.0 | 190 pcs. | White (WH) | 556-25007 |
| TTAGPU15X65YE | 65.0 | 15.0 | 190 pcs. | Yellow (YE) | 556-25011 |
| TTAGPU11X100WH | 100.0 | 11.0 | 125 pcs. | White (WH) | 556-25021 |
| TTAGPU11X100YE | 100.0 | 11.0 | 125 pcs. | Yellow (YE) | 556-25020 |
| TTAGPU15X100WH | 100.0 | 15.0 | 125 pcs. | White (WH) | 556-25006 |
| TTAGPU15X100YE | 100.0 | 15.0 | 125 pcs. | Yellow (YE) | 556-25010 |

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available. More colours on request.

