

Product Information

2470PJP075P30

EAN 4031582010459

Swivel castor, housing made of pressed steel, zinc-chromatised, double ball bearing swivel head.

Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, precision ball bearing, with threadguards, bolt hole

Castors can be mounted with standard screws; various length screws can be used..

Wheel diameter	75 mm
Width of Tread	25 mm
Centre hole	11 mm
Offset	24 mm
Swivel Interference	123 mm
Overall height	100 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.256 kg
Dynamic Load capacity	75 kg
Static Load capacity	150 kg
Swivel Radius	61.5 mm
Hardness of tread	A 87 Shore



Versions:

