

overview

- Most reliable object detection through barrier principle
- Acquisition of two independent limit values
- Detection of double sheets
- High performance in compact housing



Picture similar



Technical data

general data

emitter / receiver	receiver
scanning range Sd	0 ... 1000 mm
scanning range far limit Sde	0 ... 1000 mm
version	IO-Link
object size (at Sd = 50 mm)	> 4 cm ²
hysteresis typ.	5 % Sde
repeat accuracy	< 1 mm
temperature drift	< 2 % Sde
response time ton	< 2 ms
release time toff	< 2 ms
adjustment	qTeach, line-Teach, IO-Link
sonic frequency	290 kHz
alignment aid	target indication flashing
output indicator	LED yellow
power on indication	LED green

electrical data

voltage supply range +Vs	12 ... 30 VDC
current consumption max. (no load)	35 mA
output circuit	push-pull
output current	< 100 mA
voltage drop Vd	< 3 VDC
residual ripple	< 10 % Vs
short circuit protection	yes
reverse polarity protection	yes, Vs to GND

communication interface

interface	IO-Link V1.1
baud rate	230,4 kBaud (COM 3)
cycle time	≥ 0.8 ms

communication interface

process data length	32 Bit
process data structure	Bit 0 = SSC1 Bit 1 = SSC2 Bit 3 = alarm Bit 16-31 = 16 Bit measurement
IO-Link port type	Class A

additional data

excess gain
operating cycles
operating hours
boot cycles
operating voltage
device temperature
histograms

adjustable parameters

time filters
LED status indicators
output logic
output circuit
counter
deactivate the sensor element
Find Me function


mechanical data

type	rectangular
housing material	plastic (ASA, PMMA)
width / diameter	12,9 mm
height / length	32,2 mm
depth	23 mm
connection types	connector M8 4 pin


ambient conditions

operating temperature	-25 ... +65 °C
storage temperature	-40 ... +75 °C
protection class	IP 67

dimension drawing



connection diagram



pin assignment

