

# Keysight Technologies TrueIR Series Thermal Imager

Data Sheet



See MORE. Accomplish MORE. Expect MORE.



## Introduction


Reap the benefits of a high resolution thermal imager that fits within your available budget. With the Fine Resolution capability, you can achieve effective resolution of 320 x 240 pixels from a 160 x 120 pixels detector – four times more resolution, four times more details.

- Four times more pixels with Fine Resolution capability
- View finer object details with 4x digital zoom
- Quick access buttons to easily change settings or functions
- Long product warranty – 3 years
- Ergonomically designed with evenly distributed weight
- In-camera monitoring for temperature trending
- Ability to focus on objects, as close as 10 cm away

# See More with U5855A True/IR Series Thermal Imager

## Get more details with Fine Resolution

Fine Resolution is a technology that restores the details originally inherent to the object while enhancing the resolution, at the same time minimizing fuzziness and noise. It is accomplished by performing sophisticated calculations on continuous multi-frames of the image – evaluated for misalignment caused mainly by hand tremor. The firmware then detects and corrects the information between images through one feature pixel.



Continuous multi-frames of low resolution images

Four times more resolution, noise eliminated

With Fine Resolution,

- Get an effective 320 x 240 pixels of radiometric JPEG IR image which is clearer and sharper.
- See fine details on objects as close as 10cm, especially when measuring temperature on small components which are close to each other.
- With 4x digital zoom, magnify a thermal image of a far-away objects quickly to identify anomalies and to reveal even finer details.
- These are essential for industrial, building inspection, electronics, as well as medical research.




Figure 1. Samples of IR images

## Perform more in-camera measurements and analysis

Capture thermal images effectively with its intuitive and easy to use tools:

- Configurable quick access buttons that are able to change functions based on user preference.
- Monitor temperature trends over time for quality checks when monitoring process parameters in industrial plant automation.
- Perform analysis using its extensive range of measurement tools.
- Coupled with the U5855A's high sensitivity of 0.07 °C, it can detect the slightest temperature difference to provide more accurate temperature readings.




Figure 2. Center spot, min and max tracking, three moveable spots.




Figure 3. Three moveable boxes with statistics




Figure 4. Delta temperature

## Ergonomically designed for comfort

The ergonomically built TrueIR thermal imager is designed to let you carry out daily tasks comfortably. With its evenly distributed weight of only 746 grams and good stability, it fits comfortably in your palm




Figure 5. Ergonomically designed to have distributed weight. It can even stand on its own!

without straining your hands, even when used over a long period of time. With a stable grip, it allows you to single-handedly capture more images and to work more efficiently.



Figure 6. Good grip with belt support

## TrueIR Analysis and Reporting Tool

Import, analyze, edit and present your thermal images to your clients swiftly with TrueIR analysis and reporting tool. With this PC software, you could change color settings and corrective parameters, add color alarm, or pick and choose any of the six measurement analysis tools or diagrams to help you present your findings to your customers clearly.

Also, generate reports quickly with the help of ready templates and then customize them accordingly based on your clients' requirements.




Figure 7. TrueIR Analysis and Reporting Tools GUI

Features:

- Change color settings and corrective parameters, like emissivity, ambient temperature, atmospheric temperature, and more
- Set color alarm
- Choose between six measurement analysis tools or diagrams like spot, line, line profile, box, histogram and delta temperature
- Capable to display thermal image, visual image, thermal-visual side-by-side, or fusion images as well as its associated photo or note tags
- Create reports based on available templates and then customize them to suit your client' needs
- Generate reports in Microsoft Words or PDF
- Eleven local languages to choose from – English, Spanish, Italian, French, German, Portuguese, simplified Chinese, traditional Chinese, Japanese, Korean and Russian

Download for free from [www.keysight.com/find/TrueIR\\_ART](http://www.keysight.com/find/TrueIR_ART)





Figure 8. Sample of measurement analysis diagrams

# Front and Back Panels

## Front panel



## Back panel



# Specifications

Specifications are warranted in the temperature range of 0 to 40 °C and after 2 minutes of power up, unless otherwise noted. Supplemental characteristics – which are not warranted, but are descriptions of performance – are determined either by design or testing.

## Performance specifications

Parameter	Specification
<b>Basic Performance</b>	
Temperature measurement range	-20 ~ 350 °C Range 1: -20 to 120 °C Range 2: 0 to 350 °C
Thermal sensitivity	Range 1: 0.07 °C (at 30 °C) Range 2: 0.1 °C (at 30 °C)
Accuracy <sup>1</sup> At 0 ~ 40 °C ambient temperature	±2 °C or ±2% (whichever is greater)
Detector type	Uncooled Focal Plane Array (α-Si)
Detector Resolution	160 × 120
Fine Resolution	320 × 240 (IR pixels)
Spectral range	8 to 14 μm
Frame rate	9 Hz
Field of view (FOV)	28° (H) × 21° (V)
Spatial resolution (IFOV)	Fine Resolution OFF: 3.1 mrad Fine Resolution ON: 2.1 mrad
Focal distance	10 cm to infinity
Focus mechanism	Manual focus
<b>Image Processing and Enhancement</b>	
Correction parameters	Emissivity, reflected temperature, object distance, ambient temperature, humidity, transmissivity
Emissivity correction	0.1 to 1.0 Predefined emissivity table
Digital zoom	Zoom ratio: 4× continuous
Color palette	Rainbow, iris, hot iron, gray, inverted gray
Camera mode	IR image, visible image, picture in picture, blend
<b>Measurements and Alarm</b>	
Measurements	Center spot, 3x moveable spots, max/min tracking, delta temperature, 3x moveable boxes (with min/max/avg)
Color alarm	High/low temperature in all areas Alarm zones: Above/below/inside/outside

1. Minimum distance with accuracy, 10 cm to 50 cm: ±4 °C or ±4%.

## Supplemental characteristics

Parameter	Characteristic
Storage device	Supports up to 32 GB SDHC memory card with class 4 and above
Image format	IR image: Radiometric JPEG Visible image: JPEG
Image logging	Logs IR, visible or fusion images at a defined interval (7 to 3600 seconds)
State storage memory	Three user-configurable stored states
Tagging/annotation	3 photo tags, note tag, note tag from template (downloadable from the Keysight Technologies, Inc. Web site)
I/O	USB 2.0 mass storage NTSC/PAL via video RCA cable
Language	English, French, German, Italian, Japanese, Korean, Portuguese, Russian, Spanish, Simplified Chinese, Traditional Chinese
Built-in quick start tutorial	Available

## Product characteristics








Product	Characteristic
Power supply	
Power adapter	<ul style="list-style-type: none"> <li>- Line voltage range: 50/60 Hz, 100 – 240 VAC (Auto/Universal voltage), 1.2 A</li> <li>- MAINS supply voltage fluctuations not to exceed <math>\pm 10\%</math> of the nominal voltage</li> <li>- Output voltage: 12 VDC, 3 A</li> <li>- Installation Category I (Isolated ELV supply source – connected to MAINS through an AC/DC power adapter)</li> </ul>
Battery	<ul style="list-style-type: none"> <li>- Li-Ion rechargeable battery, 7.4 VDC, 2500 mAh</li> <li>- Operating time: 4 hours</li> </ul>
Display	3.5" TFT
Visible camera	3.1 MP
Built-in led torch	Available
Laser pointer	Class 2
Warm-up time	2 minutes
Operating environment	
Temperature	- -15 °C to 50 °C
Humidity	- 50% RH to 95% RH at 40 °C
Storage compliance	
Temperature	- -40 °C to 70 °C
Humidity	- 95% RH at 40 °C
Altitude	- Up to 2000 m
Pollution degree	- 2
Safety compliance	<ul style="list-style-type: none"> <li>- Laser safety: IEC 60825-1:2001/EN 60825-1:2001 (Laser Class 2)</li> <li>- IEC 61010-1:2010/EN 61010-1:2010</li> </ul>
EMC compliance	<ul style="list-style-type: none"> <li>- IEC 61326-1:2005/EN61326-1:2006</li> <li>- CISPR11:2003/EN55011:2007, Group 1 Class A</li> <li>- Canada: ICES/NMB-001: Issue 4, June 2006</li> <li>- Australia/New Zealand: AS/NZS CISPR 11:2004</li> </ul>
Shock	Tested to IEC 60068-2-27 Ed. 3.0
Vibration	Tested to IEC 60068-2-6
Tripod mount thread	ISO 1222:2010 Standard screw thread, 1/4 - 20 UNC
Drop test	2 m
Protection class	2
IP rating	IP 54
Dimensions (W × H × D)	95 × 250 × 85 mm
Weight	0.746 kg (with battery)
Warranty	Refer to <a href="http://www.keysight.com/go/warranty_terms">www.keysight.com/go/warranty_terms</a> 3 years for the product 3 months for the standard accessories unless otherwise specified
Calibration cycle	1 year

# Ordering information

Standard shipped accessories	
	Power adapter with power cord
	Rechargeable Li-Ion battery
	SD memory card
	Video RCA to RCA interface cable, 2 m
	USB Standard-A to Mini Type-B interface cable, 1 m
	Hand strap
	Rugged, hard carrying case
	Quick start guide
	Certificate of calibration



U5855A

Optional accessories		
U5751A	Power adapter (with power cord)	
U5752A	Rechargeable Li-Ion battery	
U5753A	External battery charger (2-bay)	
U5761A	Video RCA to RCA interface cable, 2 m	
U5762A	USB Standard-A to Mini Type-B interface cable, 1 m	
U5771A	Rugged carrying case, hard	
U5772A	Hand strap, Adjustable for right-handed and left-handed use	



**myKeysight**

myKeysight

[www.keysight.com/find/mykeysight](http://www.keysight.com/find/mykeysight)

A personalized view into the information most relevant to you.



**Three-Year Warranty**

[www.keysight.com/find/ThreeYearWarranty](http://www.keysight.com/find/ThreeYearWarranty)

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.



**Keysight Assurance Plans**

[www.keysight.com/find/AssurancePlans](http://www.keysight.com/find/AssurancePlans)

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.



[www.keysight.com/quality](http://www.keysight.com/quality)

Keysight Technologies, Inc.  
DEKRA Certified ISO 9001:2008  
Quality Management System

**Keysight Channel Partners**

[www.keysight.com/find/channelpartners](http://www.keysight.com/find/channelpartners)

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

[www.keysight.com/find/truelRimage](http://www.keysight.com/find/truelRimage)

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

**Americas**

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

**Asia Pacific**

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

**Europe & Middle East**

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:  
[www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)  
(BP-07-10-14)