VEMD4010X01

Vishay Semiconductors





LINKS TO ADDITIONAL RESOURCES



DESCRIPTION

VEMD4010X01 is a high speed and high sensitive PIN photodiode. It is a miniature surface mount device (SMD) with a 0.42 mm² sensitive area.

FEATURES

Silicon PIN Photodiode

- Package type: surface-mount
- Package form: 0805
- Dimensions (L x W x H in mm): 2 x 1.25 x 0.7
- Radiant sensitive area (in mm²): 0.42
- Operating temperature range: $T_{OP} = -40$ °C to +110 °C
- Angle of half sensitivity: $\phi = \pm 55^{\circ}$
- Floor life: 168 h, MSL 3, according to J-STD-020
- Lead (Pb)-free reflow soldering
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- High speed photo detector
- Photo interrupters
- Automotive sensors

PRODUCT SUMMARY			
COMPONENT	I _{ra} (μΑ) at E _e = 1 mW/cm ² , λ = 950 nm, V _R = 5 V	φ (°)	λ _{0.5} (nm)
VEMD4010X01	2.4	± 55	550 to 1040

Note

• Test conditions see table "Basic Characteristics"

ORDERING INFORMATION				
ORDERING CODE	PACKAGING	REMARKS	PACKAGE FORM	
VEMD4010X01	Tape and reel	MOQ: 3000 pcs, 3000 pcs/reel 0805		

Note

• MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25 \text{ °C}$, unless otherwise specified)				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage		V _R	20	V
Operating temperature range		T _{amb}	-40 to +110	°C
Storage temperature range		T _{stg}	-40 to +110	°C
Soldering temperature	According to reflow solder profile Fig. 8	T _{sd}	260	°C

1



e

RoHS

COMPLIANT HALOGEN

FREE

GREEN (5-2008)

VEMD4010X01



www.vishay.com

Vishay Semiconductors

BASIC CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	I _F = 50 mA	V _F	-	1.1	1.3	V
Reverse dark current	$V_{R} = 5 V, E = 0$	I _{ro}	-	1	3	nA
Diode capacitance	V _R = 0 V, f = 1 MHz, E = 0	CD	-	7	-	pF
	$V_{R} = 5 V, f = 1 MHz, E = 0$	CD	-	2.5	-	pF
Short circuit current	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	l _k	-	2.2	-	μA
Temperature coefficient of I_k	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	TK _{lk}	-	0.1	-	%/K
Reverse light current	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$, $V_R = 5 \text{ V}$	I _{ra}	1.9	2.4	3.1	μA
Angle of half sensitivity		φ	-	± 55	-	0
Wavelength of peak sensitivity		λρ	-	910	-	nm
Range of spectral bandwidth		λ _{0.5}	-	550 to 1040	-	nm
Rise time	V_R = 5 V, R_L = 1 k Ω , λ = 820 nm	t _r	-	100	-	ns
Fall time	V_R = 5 V, R_L = 1 k Ω , λ = 820 nm	t _f	-	100	-	ns

BASIC CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Reverse Dark Current vs. Ambient Temperature




Fig. 2 - Relative Reverse Light Current vs. Ambient Temperature



Vishay Semiconductors






Fig. 3 - Reverse Light Current vs. Irradiance




Fig. 4 - Reverse Light Current vs. Reverse Voltage




Fig. 5 - Relative Spectral Sensitivity vs. Wavelength




Fig. 6 - Relative Sensitivity vs. Angular Displacement

3

For technical questions, contact: <u>detectortechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



www.vishay.com

REFLOW SOLDER PROFILE




Fig. 7 - Lead (Pb)-free Reflow Solder Profile According to J-STD-020

PACKAGE DIMENSIONS in millimeters

DRYPACK

Devices are packed in moisture barrier bags (MBB) to prevent the products from moisture absorption during transportation and storage. Each bag contains a desiccant.

FLOOR LIFE

Floor life (time between soldering and removing from MBB) must not exceed the time indicated on MBB label:


Floor life: 168 h

Conditions: $T_{amb} < 30\ ^\circ C,\ RH < 60\ \%$

Moisture sensitivity level 3, according to J-STD-020.

DRYING

In case of moisture absorption devices should be baked before soldering. Conditions see J-STD-033D or label. Devices taped on reel dry using recommended conditions 192 h at 40 °C (+ 5 °C), RH < 5 %.



Drawing-No.: 6.550-5363.01-4 Issue: 2; 01.07.2020

Rev. 1.1, 15-Jul-2020

Document Number: 80134

For technical questions, contact: <u>detectortechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000





Vishay Semiconductors

BLISTER TAPE DIMENSIONS in millimeters




Tabelle			
TYPE	PIN 1	PIN 2	
VEMD4xxx	Anode	Cathode	
VEMT4xxx	Emitter	Collector	


Drawing-No.: 9.700-5411.0-4 Issue: 1; 31.01.2019





Vishay Semiconductors

REEL DIMENSIONS in millimeters





Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.