

Charging Resistor for EV Hybrid Wirewound Technology



LINKS TO ADDITIONAL RESOURCES

30 3D Mode

FEATURES

- Technology: hybrid wirewound
- High energy / volume ratio
- Easy mounting (faston connection 6.35 [0.250"])
- · Possibility to mount on heatsink
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Precharge
- Discharge
- Active discharge resistor

STANDARD ELECTRICAL SPECIFICATIONS					
GLOBAL MODEL	POWER RATING ON STAINLESS STEEL ⁽¹⁾ W	POWER RATING ON PAMITHERM ⁽¹⁾ W	$\begin{array}{c} \textbf{RESISTANCE RANGE}\\ \Omega \end{array}$	TOLERANCE ± %	
HRHA	90	54	1 to 1K	5, 10	

Note

⁽¹⁾ 6 mm thickness, see Fig. 2

TECHNICAL SPECIFICATIONS				
PARAMETER	UNIT	RESISTOR CHARACTERISTICS		
Temperature coefficient	ppm/°C	± 100 (typical)		
Operating temperature range	°C	-55 to +250		

GENERAL CHARACTERISTICS				
Dielectric base	Ceramic			
Resistive circuit	Hybrid wirewound			
Terminals	Stainless steel			
Ohmic values	E24 (other on request)			
Maximum operating voltage between terminals (by design)	1000 V _{DC}			
Dielectric voltage	3000 V _{RMS} (higher on request), 50 Hz, 1 min			
Creepage distance	14 mm			
Clearance distance	14 mm			
Weight	160 g max.			

Revision: 14-Dec-2021

1

RoHS

HRHA

Vishay MCB

VISHAY, www.vishay.com

HRHA

Vishay MCB



MOUNTING

For soldering recommendations please see www.vishay.com/doc?32595

DISSIPATION



Fig. 1 - Permanent Applicable Power as a Function of Ambient Temperature





2

www.vishay.com

Vishay MCB

HRHA

ENERGY		
Energy mode at 30 °C room temperature	Stainless steel (6 mm thickness)	Pamitherm (6 mm thickness)
Refer to Fig. 2 for bottom case temperature vs. pulse number	PULSE – DURATION – WAIT ⁽¹⁾	PULSE – DURATION – WAIT ⁽¹⁾
Continuous cycle - short circuit wave (refer to Fig. 3)	9000 J - 1.8 s - 100 s	9000 J – 1.8 s – 167 s
Continuous cycle - RC discharge wave (refer to Fig. 4)	1850 J - 0.74 s - 30 s	1850 J - 0.74 s - 34 s







Fig. 4 - Bottom Case Temperature With Continuous RC Discharge Cycle 1850 J at T_{amb} = 30 $^\circ C$

ORDERING INFORMATION						
HRHA	F	N	22U	5 %	BO12	
MODEL	TERMINATION	COATING	RESISTANCE VALUE	TOLERANCE	PACKAGING	

GLOBAL PART NUMBER INFORMATION						
н [Р Н	A F 	C 2 0 [3 4	0 0	J B 5 6	7
1	2	3	4	5	6	7
PRODUCT TYPE	TERMINATION	COATING (if applicable)	RESISTANCE VALUE	TOLERANCE	PACKAGING	INDUSTRIALIZATION NUMBER
HRHA	F = faston	C = coated N = not coated	The first three digits are significant figures and the last specifies the number of zeros to follow, R designates decimal point. $4702 = 47 \text{ k}\Omega$ $47R0 = 47 \Omega$	J = 5 % K = 10 %	B = box Box quantity depends of model and size	Specific digits for custom design (if applicable)

EXAMPLES				
MODEL	DESCRIPTION	PART NUMBER		
HRHA	HRHAFN22R0JB	HRHA F N 22U 5 % BO12		
HRHA	HRHAFC22R0JB	HRHA F C 22U 5 % BO12		

3



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.