

150W FAN COOLED 100W CONVECTION

The VFB150 is a series of open frame AC-DC single output power supplies with 100W convection and 150W fan cooled ratings.

This range of cost-competitive, high efficiency, single output AC-DC power supplies are packaged in an industry standard $5.0" \times 3.0"$ footprint making them suitable for industrial, information technology and domestic applications.

With world-wide industrial safety approvals, compliance with class B for conducted and radiated emissions, the VFB150 benefits system designers with easy integration into a wide range of applications.

Features

- Single outputs from 12V to 48VDC
- 90 to 264VAC input range
- 100W convection, 150W fan cooled rating
- High efficiency up to 91%
- 3kVAC input to output isolation
- 12VDC 0.3A fan supply
- 0.15W no load input power
- Overcurrent, overvoltage and short-circuit protection
- Operating temperature range: -10°C to +70°C
- 3 year warranty

AC-DC POWER SUPPLIES



Applications









Industrial Electronics

Instrumentation

Security

Technology

Dimensions

76.2 x 127.0 x 39.0mm (3.00" x 5.00" x 1.53")

Models & Ratings

Mardal Manakan	Outrot Description	Output Voltage	Output	F46 -: (2)	
Model Number	odel Number Output Power ⁽¹⁾		Fan Cooled	Convection Cooled	Efficiency ⁽²⁾
VFB150PS12	150W	12.0V	12.5A	8.3A	88%
VFB150PS15		15.0V	10.0A	6.7A	89%
VFB150PS24		24.0V	6.25A	4.17A	91%
VFB150PS48		48.0V	3.13A	2.08A	90%

Notes:

- 1. Fan cooled rating.
- 2. Typical efficiency measured at 230VAC and 150W load.

Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage Range	90		264	VAC	
Input Frequency	47		63	Hz	
Input Current - Full Load		2.3/1.5		A rms	At 115/230VAC
No Load Input Power			0.15	W	
Inrush Current			80	Α	At 230VAC, cold start 25°C
Earth Leakage Current			500	μΑ	At 264VAC, 60Hz
Input Protection	Internal T3.15A/30	nternal T3.15A/300VAC fuse fitted in line			

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage	12		48	VDC	
Initial Set Accuracy			1	%	
Minimum Load	No minimum loa	d required			
Start Up Delay			2	s	
Start Up Rise Time			35	ms	Full load, 115VAC
Hold Up Time	8	14		ms	Full load and 115/230VAC
Line Regulation			1	%	90-264VAC
Load Regulation			3	%	
Transient Response			4	%	Deviation, recovery within 1% in less than 500µs for a 25% load change
			200	mV pk-pk	For 12V & 15V versions, measured with 20MHz bandwidth and 47µF electrolytic in parallel with 0.1µF ceramic
Ripple and Noise			1.0	% pk-pk	For 24V & 48V versions, measured with 20MHz bandwidth and 47µF electrolytic in parallel with 0.1µF ceramic
Overload Protection	110		180	% Inom	
Overvoltage Protection	110		140	% Vnom	
Short Circuit Protection	Trip and restart (h	iccup), auto reset	ting		
Temperature Coefficient			0.05	%/°C	

General

Characteris	tic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency			89		%	See Models & Ratings table
	Input to Output	3000				
Isolation	Input to Ground	1500			VAC	
	Output to Ground	1500				
0 "1" 5		25		80	kHz	Mains converter, variable
Switching Frequency	40		230	PFC, variable		
Power Dens	sity		6.5		W/in³	
Mean Time	Between Failure		250		khrs	MIL-HDBK-217F, +25°C GB
Weight			340 (0.75)		g (lb)	




Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-10		+70	°C	Derate linearly from 100% load at 50°C to 50% load at 70°C.
Cooling	Convection cooled/fan cooled with 25.4m³/h				
Operating Humidity			95	%RH	Non-condensing
Operating Altitude			5000	m	
Shock	IEC68-2-27, 30g, 11ms half sine, 3 times in each of 6 axes				
Vibration	IEC68-2-6, 10-500Hz, 2g 10 mins/sweep, 60 mins for each of 3 axes				


Efficiency Curves

Efficiency vs. Load

VFB150PS12



VFB150PS24





EMC: Emissions

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55032	Class B	
Radiated	EN33032	Class B	
Harmonic Currents	EN61000-3-2	Class A	
Voltage Flicker	EN61000-3-3		

EMC: Immunity


Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
	EN55035	As below	As below	
ESD Immunity	EN61000-4-2	±6kV contact, ±8kV air discharge	А	
Radiated Immunity	EN61000-4-3	3V/m	А	
EFT/Burst	EN61000-4-4	3	А	
Surge	EN61000-4-5	Installation class 3	А	
Conducted	EN61000-4-6	3Vrms	А	
Magnetic Field	EN61000-4-8	1A/m	А	
		70% U⊤ for 500ms	А	
	EN61000-4-11 (115VAC)	<5% U⊤ for 10ms	А	
Ding and Intermedians	(1.01/10)	<5% U⊤ for 5000ms	В	
Dips and Interruptions		70% U⊤ for 100ms	А	
	EN61000-4-11 (230VAC)	<5% UT (0VAC) for 10ms	А	
	(===::0)	<5% UT (0VAC) for 5000ms	В	


Safety Approvals


Safety Agency	Standard	Notes & Conditions
UL	UL62368-1	
TUV	EN62368-1	ITE
СВ	IEC62368-1	
CE	Meets all applicable directives	
UKCA	Meets all applicable legislation	



Mechanical Details







32.6 (1.28) 36.3±1 (1.43±0.04)	
---	--

CN1 - Input Connector			
Pin	Function		
1	N		
2			
3	L		

Mates with JST housing VHR-3N and JST series SVH crimp terminals.

CN72 - Output Connector				
Pin	Function	Pin	Function	
1	+Vout	5	-Vout	
2	+Vout	6	-Vout	
3	+Vout	7	-Vout	
4	+Vout	8	-Vout	

Mates with JST housing VHR-8N and JST series SVH $\,$ crimp terminals.

CN71 - Sense Connector		
Pin	Function	
1	Sense+	
2	Sense-	

Mates with JST PHR-2 housing and SPH-002T-PO.5S crimps.

CN73 - Fan Connector	
Pin	Function
1	Fan+
2	Fan-

Mates with JST XHP-2 housing and SXH-002T-PO.6 crimps.

Notes:

- 1. Dimensions in mm (inches).
- 2. Weight: 340g (0.75lbs).
- 3. Tolerances: $x.xx = \pm 0.5$ ($x.x = \pm 0.02$), $x.xxx = \pm 0.25$ ($x.xx = \pm 0.01$).
- 4. Mounting holes marked with
 must be connected to safety earth.