

**Product data**

Product code	<b>VG03-0060</b>	STK-code	<b>1914377</b>	EAN-code	<b>6430051861765</b>
Product name	OJL connector 80 Blue			ETIM class	<b>EC000276</b>
Wires	IN 2x(Al/Cu) 2,5-16 mm <sup>2</sup> OUT: 6x (Cu) 2,5-6mm <sup>2</sup>				

**Technical data**


Nominal current (IEC)	Cu	<b>80</b>	A
	Al	<b>75</b>	A
Nominal voltage (IEC)	<b>1000 V AC / 1500 V DC</b>		V
	-		
	-		
	-		
Number of poles	<b>1</b>		pcs
Max. Cross section	<b>16</b>		mm <sup>2</sup>
Tightening torque			
	2,5-6 mm <sup>2</sup>	<b>1</b>	Nm
	10-16 mm <sup>2</sup>	<b>6</b>	Nm
	-		
	-		
Input	<b>2x Al/Cu 2,5-16 mm<sup>2</sup></b>		
Output	<b>6x Cu 2,5-6 mm<sup>2</sup></b>		
	-		
Operating temperature	<b>80</b>		°C
Weight	<b>38</b>		g
IP-protection	<b>IP20</b>		
Standards	<b>EN IEC 61238-1:2019; EN 60947-7-1:2009</b>		
Color / Material	<b>Blue Cover PC, Grey Housing RAL 7035 PA66/VO, Connector part tin plated aluminium</b>		
Mounting / Connection	<b>Din rail mounting</b>		



**Description**

The single pole distribution block for branching connection. Distribution block with 2 inputs and it will distribute the current through 6 output cables. Connector is made from tin plated aluminium and housing is PA66 VO.

**Drawing**



**Package**

Package	<b>Box</b>	Pcs / Package	<b>33</b>	Weight [kg]	<b>1,40</b>
Length [mm]	<b>210</b>	Width [mm]	<b>155</b>	Height [mm]	<b>105</b>

**Ouneva Oy**

Teollisuustie 21  
FI-82730 Tuupovaara  
Finland

Tel. +358 400 179 750  
[info@ouneva.fi](mailto:info@ouneva.fi)

[www.ounevagroup.fi](http://www.ounevagroup.fi)  
[www.ouneva.fi](http://www.ouneva.fi)