

solenoid valve



VSNC-FC-M52-MD-G14-F8

Part number: 577257

★ Core product range

NAMUR valve 1/4", monostable, F8 armature system.

FESTO



Data sheet

Feature	Value
Valve function	5/2 or 3/2, convertible
Type of actuation	electrical
Width	32 mm
Standard nominal flow rate	1,250 l/min
Operating pressure	2.5 ... 10 bar
Design structure	Piston slide
Type of reset	mechanical spring
Authorisation	c UL us - Recognized (OL)
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Conforms to standard	VDI/VDE 3845 (NAMUR)
Manual override	detenting Pushing
Type of piloting	Piloted
Pilot air supply	Internal
Flow direction	non reversible
Overlap	Positive overlap
Signal status display	with accessories
b value	0.4
C value	5.2 l/sbar
Standard nominal flow rate, exhaust air return 4→3	110 l/min
Switching time off	48 ms
Switching time on	11 ms
Duty cycle	100 %
Characteristic coil data	See solenoid coil, to be ordered separately
Certificate issuing department	DNVGL-TAA000011J
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	-20 ... 60 °C
Ambient temperature	-20 ... 60 °C
Product weight	335 g
Mounting type	with through hole
Scavenging orifice connection	Non-ducted
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	NAMUR port pattern
Pneumatic connection, port 3	G1/4
Pneumatic connection, port 4	NAMUR port pattern
Pneumatic connection, port 5	G1/4
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	Wrought Aluminium alloy
Material screws	High alloy steel, non-corrosive