196 DLC

www.vishay.com

Vishay BCcomponents

Energy Storage Double Layer Capacitors



FEATURES

- Polarized capacitor with high charge density, alternative product to rechargeable backup batteries
- Dielectric: electric double layer
- Radial leads, cylindrical case, insulated with a blue sleeve
- Available in both vertical and low-profile versions
- Unlimited charge and discharge cycle numbers
- No charge-discharge control circuitry and no series resistor necessary
- Maintenance-free, no periodic replacement or service necessary
- Ecologically beneficial (no Cd, no Li)
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Energy storage, for backup of semiconductor memories (CMOS) in all fields of electronics
- Telecommunication, audio-video, EDP
- · General industrial, clock and timer systems

MARKING

- The capacitors are marked with the following information:
- Rated capacitance (in F)
- Rated voltage (in V)
- Date code, in accordance with IEC 60062
- Name of manufacturer
- Negative terminal identification
- Upper category temperature (at 85 °C types only)

QUICK REFERENCE DATA								
	VALUE							
DESCRIPTION	STANDARD FORM A	HIGH VOLTAGE FORM A	HIGH TEMPERATURE FORM A	VERTICAL, MINIATURIZED FORM B				
Nominal case sizes (Ø D x L in mm)	13 x 7 and 21 x 7.5	13 x 9 and 21 x 9	13 x 9 and 21 x 9	11.5 x 13 (vertical)				
Rated capacitance range, C _R	0.047 F to 1.0 F	0.047 F to 0.68 F	0.047 F to 0.68 F	0.047 F to 0.33 F				
Tolerance on C _R at 20 °C		-20 % t	o +80 %					
Rated voltage, U _R	5.5 V	6.3 V	5.5 V	5.5 V				
Maximum surge voltage, U _S	6.3 V	7.0 V	6.3 V	6.3 V				
Category temperature range	-25 °C to +70 °C	-25 °C to +70 °C	-25 °C to +85 °C	-25 °C to +70 °C				
Useful life at U _R :								
at 85 °C	-	-	1000 h	-				
at 70 °C	1000 h	1000 h	2800 h	1000 h				
at 40 °C	8000 h	8000 h	23 000 h	8000 h				
at 25 °C	23 000 h	23 000 h	64 000 h	23 000 h				
Shelf life at 0 V	1000 h at upper category temperature							
Climatic category IEC 60068	25 / 070 / 21	25 / 070 / 21	25 / 085 / 21	25 / 070 / 21				

1

Document Number: 28362

For technical questions, contact: <u>energystorage@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

RoHS COMPLIANT



www.vishay.com

Vishay BCcomponents

SELECTION	SELECTION CHART FOR C_R , U_R , AND FORM AT UPPER CATEGORY TEMPERATURE (UCT)						
C _R	FORM	U _R =	5.5 V U _R = 6.3 V				
(F)		UCT = 85 °C	UCT = 70 °C	UCT = 70 °C			
0.047	A	13 x 9	13 x 7	13 x 9			
0.047	В	-	11.5 x 13	-			
0.1	A	13 x 9 x 9	13 x 7	13 x 9			
0.1	В	-	11.5 x 13	-			
0.22	A	-	13 x 7	-			
0.22	В	-	11.5 x 13	-			
0.33	A	-	13 x 7	-			
0.55	В	-	11.5 x 13	-			
0.47	A	21 x 9	21 x 7.5	21 x 9			
0.47	В	-	-	-			
0.68	A	21 x 9	-	21 x 9			
0.00	В	-	-	-			
1.0	A	-	21 x 7.5	-			

DIMENSIONS in millimeters **AND AVAILABLE FORMS**





Fig. 1 - Form A: Low profile



DIMENSIONS in millimeters, MASS AND PACKAGING QUANTITIES							
NOMINAL CASE SIZE Ø D x L (mm)	CASE CODE	FORM	Ø D _{max.}	L _{max.}	MASS (g)	PACKAGING QUANTITIES	
11.5 x 13	1	В	11.8	13.5	≈ 1.5	2000	
13 x 7	2	A	13.5	7.5	≈ 2.8	1000	
13 x 9	3	A	13.5	9.5	≈ 3.4	1000	
21 x 7.5	4	A	21.5	8.0	≈ 7.1	500	
21 x 9	5	A	21.5	9.5	≈ 8.8	500	

Note

• Packaging: bulk in box

Revision: 13-Mar-18

2

Document Number: 28362

For technical questions, contact: <u>energystorage@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

196 DLC

www.vishay.com

Vishay BCcomponents

ELECTRICAL DATA					
SYMBOL	DESCRIPTION				
C _R	Rated capacitance, tolerance -20 % / +80 %, measured by constant current discharge method				
UCT	Upper category temperature				
ار	Max. leakage current after 30 min at $U_{\rm R}$				
RI	Max. internal resistance at 1 kHz				

Note

- Unless otherwise specified, all electrical values in Table 1 apply at T_{amb} = 20 °C, P = 86 kPa to 106 kPa and RH = 45 % to 75 %

Table 1

ORDERING EXAMPLE

Double layer capacitor 196 series

1.0 F / 5.5 V

Nominal case size: Ø 21 mm x 7.5 mm; Form A Ordering code: MAL2 19612105E3 Former 12 NC: 2222 19612105

ELE	ELECTRICAL DATA AND ORDERING INFORMATION										
U _R (V)	C _R (F)	NOMINAL CASE SIZE Ø D x L (mm)	CASE CODE	FORM	UCT (°C)	I _L 30 min (μΑ)	R _I 1 kHz (Ω)	ORDERING CODE			
STAN	STANDARD SERIES										
	0.047	13 x 7	2	А	70	69	120	MAL219612473E3			
	0.10	13 x 7	2	А	70	100	75	MAL219612104E3			
5.5	0.22	13 x 7	2	А	70	135	75	MAL219612224E3			
5.5	0.33	13 x 7	2	А	70	182	75	MAL219612334E3			
	0.47	21 x 7.5	4	А	70	216	30	MAL219612474E3			
	1.0	21 x 7.5	4	А	70	315	30	MAL219612105E3			
HIGH	TEMPERATU	JRE SERIES									
	0.047	13 x 9	3	А	85	69	300	MAL219622473E3			
5.5	0.10	13 x 9	3	А	85	100	200	MAL219622104E3			
5.5	0.47	21 x 9	5	А	85	216	50	MAL219622474E3			
	0.68	21 x 9	5	А	85	260	50	MAL219622684E3			
VERT	CAL, MINIA	TURIZED SERIES									
	0.047	11.5 x 13	1	В	70	69	120	MAL219632473E3			
5.5	0.10	11.5 x 13	1	В	70	100	75	MAL219632104E3			
5.5	0.22	11.5 x 13	1	В	70	135	75	MAL219632224E3			
	0.33	11.5 x 13	1	В	70	182	75	MAL219632334E3			
HIGH	VOLTAGE SE	ERIES									
	0.047	13 x 9	3	А	70	69	300	MAL219613473E3			
6.3	0.10	13 x 9	3	А	70	100	200	MAL219613104E3			
0.0	0.47	21 x 9	5	А	70	216	50	MAL219613474E3			
	0.68	21 x 9	5	А	70	260	50	MAL219613684E3			

For technical questions, contact: <u>energystorage@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

Vishay BCcomponents



MEASURING OF CHARACTERISTICS

CAPACITANCE (C)

Capacitance shall be measured by constant current discharge method.

DISCHARGE CURRENT AS A FUNCTION OF RATED CAPACITANCE								
PARAMETER		VALUE UNIT						
Rated capacitance, C _R	0.047	0.1	0.22	0.33	0.47	0.68	1.0	F
Discharge current, I _D		0.	.1			1.0		mA




Fig. 3 - Voltage diagram for capacitance measurement

Capacitance value C_R is given by discharge current I_D , time T and rated voltage U_R , according to the following equation:





Fig. 4 - Test circuit for capacitance measurement

INTERNAL RESISTANCE (R_I) AT 1 kHz






Fig. 5 - Test circuit for RI measurement

LEAKAGE CURRENT (IL)

Leakage current shall be measured after 30 min application of rated voltage $U_{\rm B}$:






Fig. 6 - Test circuit for leakage current




Fig. 7 - Typical leakage current as a function of time





DISCHARGE CHARACTERISTICS

Backup time of 196 DLC series capacitors depends on minimum memory holding voltage and discharge current (corresponding with the current consumption of the load). For minimum backup times of standard and vertical miniaturized series see Figures 8 and 9 (charging time \ge 24 h).




Fig. 8 - Typical backup time as a function of discharge current




Fig. 9 - Typical backup time as a function of discharge current

Figure 10 shows the backup time when a 196 DLC capacitor is discharged by a constant resistance (charging time \ge 24 h).

The horizontal axis shows the initial value of discharge current if 5 V is connected to the capacitor via a fixed series resistor.

Example: 1 μA corresponds to 5 M Ω and 0.1 μA corresponds to 50 M Ω

The vertical axis shows that period of time during which the voltage drops from 5 V to 2 V.




Fig. 10 - Typical backup time as a function of initial discharge current





Vishay BCcomponents

Table 2

NAME OF TEST	IEC 60384-4 / EN130300 SUBCLAUSE	PROCEDURE (quick reference)	REQUIREMENTS
Robustness of terminations	4.4	Tensile strength; application of loading force for 10 s: 20 N (standard series) 5 N (vertical miniaturized series)	No breaks
Resistance to soldering heat	4.5	Solder bath; 260 °C; 5 s	Δ C/C: ± 10 % R _I and I _L ≤ spec. limit
Solderability	4.6	Solder bath; 235 °C; 2 s	≥ 75 % tinning
Vibration	4.8	10 Hz to 55 Hz; 1.5 mm; 3 directions; 2 h per direction	Δ C/C: ± 10 % R _I and I _L ≤ spec. limit
Damp heat, steady state	4.12	500 h at 55 °C; RH 90 % to 95 %; no voltage applied	$\label{eq:relation} \begin{split} & \Delta C/C: \pm 30 \ \% \\ & R_{I} \leq 4 \ x \ spec. \ limit \\ & I_{L} \leq 2 \ x \ spec. \ limit \end{split}$
Endurance	4.13	T _{amb} = 70 °C; 5.5 V applied; 1000 h	Δ C/C: ± 30 % R _I ≤ 4 x spec. limit I _L ≤ 2 x spec. limit
Useful life	-	T _{amb} = 70 °C; 5.5 V applied; 1000 h	$\label{eq:relation} \begin{split} & \Delta C/C: \pm 30 \ \% \\ & R_{I} \leq 4 \ x \ spec. \ limit \\ & I_{L} \leq 2 \ x \ spec. \ limit \end{split}$
Storage at upper category temperature	4.17	T _{amb} = 70 °C; no voltage applied; 1000 h	$\label{eq:relation} \begin{split} & \Delta C/C: \pm 30 \ \% \\ & R_{I} \leq 4 \ x \ spec. \ limit \\ & I_{L} \leq 2 \ x \ spec. \ limit \end{split}$
Self discharge	-	24 h storage at room temperature after application of 5 V for 1 h	Remaining voltage: \geq 4 V
Characteristics at high and low temperature	4.19	Step 1: reference measurement at +20 °C of C, R_I and I_L Step 2: measurement at -25 °C Step 3: measurement at +20 °C Step 4: measurement at +70 °C Step 5: measurement at +20 °C	$eq:linear_line$

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.