


START

1

Resistor - Weerstand - Résistance - Widerstand - Resistencia - Motstand - Vastus - Resistenze



◇ R1, R2 : 1K


◇ R3, R4 : 10K

(Brown, Black, Red) - (Bruin, Zwart, Rood) - (Brun, Noir, Rouge) - (Braun, Schwarz, Rot) - (Brun, Svart, Röd) - (Ruskea, Musta, Punainen) - (Marrón, Negro, Rojo) - (Castanho, Preto, Encarnado) - (Marrone, Nero, Rosso)

(Brown, Black, Orange) - (Bruin, Zwart, Oranje) - (Brun, noir, Orange) - (Braun, Schwarz, Orange) - (Brun, Svart, Orange) - (Ruskea, Musta, Oranssi) - (Marrón, Negro, Naranja) - (Castanho, Preto, Laranja) - (Marrone, Nero, Aranciato)

2

Trimmer




◇ RV1: 220K (250K)

◇ RV2: 220K (250K)

3


Transistor



◇ T1, T2 : BC547

4

Electrolytic capacitor




Watch the polarity!
Attention à la polarité!

◇ C1, C2 : 10µF

5


LED



Watch the polarity!
Att. la polarité!

◇ LD1, LD2 : 5mm

6



Red - Rood - Rouge - Rot - Röd - Punainen - Rojo - Encarnado - Rosso

