

HDD Mob Blue 1TB 2.5 SATA 128MB(WD10SPZX)
HDD Mob Blue 1TB 2.5 SATA 128MB



Boost your PC storage with WD Blue drives, the brand designed just for desktop and all-in-one PCs with a variety of storage capacities.

Key Selling Points

An excellent solution for your everyday computing needs
Plan for the future

Product Features

An excellent solution for your everyday computing needs

The WD Blue drive delivers performance, reliability, and capacity, making it an excellent solution for the everyday user.

Plan for the future

With better technology comes bigger storage needs. Digital cameras that record video at Ultra HD resolution and 30 frames per second require a ton of storage. Handling all that media is a snap with this drive.

Main Specifications

Product Description	WD Blue WD10SPZX - hard drive - 1 TB - SATA 6Gb/s
Type	Hard drive - internal
Capacity	1 TB
Form Factor	2.5"
Interface	SATA 6Gb/s
Data Transfer Rate	600 MBps
Buffer Size	128 MB
Spindle Speed	5400 rpm
Features	Advanced Format technology
Dimensions (WxDxH)	69.67 mm x 100.2 mm x 7 mm
Weight	90 g
Manufacturer Warranty	2 years warranty

Extended Specification

General

Device Type	Hard drive - internal
Capacity	1 TB
Form Factor	2.5"
Interface	SATA 6Gb/s
Buffer Size	128 MB
Features	Advanced Format technology
Width	69.67 mm
Depth	100.2 mm

Height	7 mm
--------	------

Weight	90 g
--------	------

Performance

Drive Transfer Rate	600 MBps (external)
---------------------	---------------------

Spindle Speed	5400 rpm
---------------	----------

Reliability

Non-Recoverable Errors	1 per 10 ¹⁴
------------------------	------------------------

Start / Stop Cycles	600,000
---------------------	---------

Expansion &Connectivity

Interfaces	1 x SATA 6 Gb/s
------------	-----------------

Compatible Bay	2.5"
----------------	------

Miscellaneous

Compliant Standards	RoHS
---------------------	------

Manufacturer Warranty

Service &Support	Limited warranty - 2 years
------------------	----------------------------

Environmental Parameters

Min Operating Temperature	0 °C
---------------------------	------

Max Operating Temperature	60 °C
---------------------------	-------

Min Storage Temperature	-40 °C
-------------------------	--------

Max Storage Temperature	65 °C
-------------------------	-------

Computer 2000 is not responsible for the errors in the documentation of products