

# **Encoder WDGI 58B**

www.wachendorff-automation.com/wdgi58b

## **Wachendorff Automation**

## ... systems and encoders

- · Complete systems
- Industrial rugged encoders to suit your application
- Standard range and customer versions
- Maximum permissible loads
- 48-hour express production
- Made in Germany
- Worldwide distributor network

**Industrie ROBUST** 



# **Encoder WDGI 58B**





- Rugged industrial standard encoder
- Housing cap die cast aluminum, with particularly eco-friendly powder coating
- Up to 25000 PPR by use of high grad electronics
- Protection to IP67, shaft sealed to IP65
- Maximum mechanical and electrical safety
- Full connection protection with 10 VDC up to 30 VDC
- High output frequency 600 kHz/2 MHz
- Optional:

   40 °C up to +85 °C,

   Protection to IP67 all around,
   Pressure equalising membrane

### www.wachendorff-automation.com/wdgi58b

Signal level H>	H > Vcc - 10 % Vcc		
Signal level L<	L < 2.5 VDC		
Output frequency	max. 200 kHz		
Circuit protection	inverse-polarity protection only		
Light reserve warning	no		

General Data			
Weight	approx. 250 g		
Connections	cable or connector outlet		
Protection rating (EN 60529)	Housing: IP65, IP67; shaft sealed: IP65		
Operating temperature	Connector: -40 °C up to +85 °C, cable: -20 °C up to +80 °C, (Option ACA: -40 °C up to +85 °C) 1 Vpp: -10 °C up to +70 °C		
Storage temperature	Connector: -30 °C up to +85 °C, cable: -30 °C up to +80 °C, option ACA: -40 °C up to +85 °C		

More Information	
General technical data and safety instructions http://www.wachendorff-automation.com/gtd	
Options http://www.wachendorff-automation.com/acc	

Resolution	
Max. pulses per revolution PPR	100 ppr

Mechanical Data	
Housing	
Flange	clamping flange
Flange material	aluminum
Housing cap	die cast aluminum, powder coated
Housing	Ø 58 mm
Cam mounting	pitch 69 mm
Shaft(s)	
Shaft material	stainless steel
Starting torque	approx. 1 Ncm at ambient temperature
Shaft	Ø 10 mm
Shaft length	L: 20 mm
Max. Permissible shaft loading radial	220 N
Max. Permissible shaft loading axial	120 N


Bearings			
Bearings type	2 precision ball bearings		
Nominale service life	1 x 10'9 revs. at 100 % rated shaft load 1 x 10'10 revs. at 40 % rated shaft load 1 x 10'11 revs. at 20 % rated shaft load		
Max. operating speed	8000 rpm		

Machinery Directive: basic data safety integrity level						
MTTF <sub>d</sub> 200 a						
Mission time (TM)	25 a					
Nominale service life (L10h)	1 x 10'11 revs. at 20 % rated shaft load and 8000 rpm					
Diagnostic coverage (DC)	0 %					

Electrical Data	
Power supply VDC	5 - 30 VDC
Current consumption	typ. 70 mA
Signal shape	square-wave
Output circuit	HTL inverted
Channels	AB, ABN, and inverted signals
Output	push-pull
Load	max. 40 mA / channel
Signal level mA	at 20 mA



## WDGI 58B: Cable connection K3, L3, radial, with 2 m cable



Description ABN inv. poss.

K3 radial, shield not connected

Assignments				
	К3			
Circuit	R30			
GND	WH			
(+) Vcc	BN			
Α	GN			
В	YE			
N	GY			
Light reserve warning	-			
A inv.	RD			
B inv.	BK, (BU at ACA)			
N inv.	VT			
Shield	flex			



### **Options**

Low-friction bearings		Order key
The encoder WDGI 58B is also available as a particularly smooth-running low-friction encoder. The starting torque is thereby changed to protection class at the shaft input to IP50.	0.5 Ncm and the	AAC

Shaft with flat	Order key	
The encoder WDGI 58B can be supplied with a shaft with flat.	AAF	



#### IP67 Shafts sealed to IP67 (not for 1 Vpp Sin/Cos) Order key AAO

The encoder WDGI 58B can be supplied in a full IP67 version.

Max. RPM: 3500 rpm

Permitted Shaft-Loading, axial: 100 N Permitted Shaft-Loading, radial: 110 N

Max. PPR: 2500 ppr

Starting-torque: approx. 4 Ncm at ambient temperature

#### Pressure equalising membrane Order key The WDGI 58B shaft encoder is also optionally available with a pressure equalising **ACR**

membrane. This prevents water from penetrating into the encoder housing in the case of

The IP67 protection level, temperature range and salt spray resistance are maintained. Resistant to chemicals and solvents in accordance with DIN EN ISO 2812-1.

Order key Cable length

XXX = Decimeter

The encoder WDGI 58B can be supplied with more than 2 m cable. The maximum cable length depends on the supply voltage and the frequency; see www.wachendorffautomation.com/atd

Please extend the standard order code with a three figure number, specifying the cable length in decimetres.

Example: 5 m cable = 050



xample Order No.	Туре					Your encoder
WDGI 58B	WDGI 58B					WDGI 58B
	Shaft					
10	10					10
	Pulses per	revolution PPR:				
100	100					100
	1					
	Channels:					
ABN	ABN					ABN
	Output circ		1		Т	
R30	Resolution PPR	Power supply VDC	Output circuit	Light reserve warning	Order key	R30
	up to 2500	5 - 30	HTL inverted	-	R30	
	Electrical c	onnections				
	Description	1		ABN inv. poss	Order key	
K3	Cable: leng	ıth (2 m standard	, WDG 58T: 1 m)			K3
	radial, shield not connected • K3					
	Options					
	Description			Order key		4
	Low-friction bearings AAC Shaft with flat AAF				_	
	IP67					
		Pressure equalising membrane ACR				
		Cable length Cable lenght				
	Without opti	Without option Empty				

Exa	mple Order No.=	WDGI 58B	10	100	ABN	R30	K3		WDGI 58B	10	100	ABN	R30	K3	Your encoder





For further information please contact our local distributor. Here you find a list of our distributors worldwide. https://www.wachendorff-automation.com/



Wachendorff Automation GmbH & Co. KG Industriestrasse 7 • 65366 Geisenheim Germany

Phone: +49 67 22 / 99 65 25 Fax: +49 67 22 / 99 65 70 E-Mail: wdg@wachendorff.de www.wachendorff-automation.de

