

# **Encoder WDGI 58A**

www.wachendorff-automation.com/wdgi58a

### **Wachendorff Automation**

#### ... systems and encoders

- · Complete systems
- Industrial rugged encoders to suit your application
- Standard range and customer versions
- Maximum permissible loads
- 48-hour express production
- Made in Germany
- Worldwide distributor network

**Industrie ROBUST** 



## **Encoder WDGI 58A**



Resolution



- Robust construction for industrial use
- Housing cap die cast aluminum, with particularly eco-friendly powder coating
- Up to 25000 PPR by use of high grad electronics
- Protection to IP67, shaft sealed to IP65
- High electrical immunity
- Full connection protection with 10 VDC up to 30 VDC
- High output frequency 600 kHz/2 MHz
- Optional: -40 °C up to +85 °C, Pressure equalising membrane

www.wachendorff-automation.com/wdgi58a

Max. pulses per revolution PPR	5000 ppr						
Mechanical Data							
Housing							
Flange	synchro flange						
Flange material	aluminum						
Housing cap	die cast aluminum, powder coated						
Housing	Ø 58 mm						
Cam mounting	pitch 69 mm						
Shaft(s)							
Shaft material	stainless steel						
Starting torque	approx. 0.5 Ncm at ambient temperature						
Shaft	Ø 6 mm						
Shaft length	L: 12 mm						
Max. Permissible shaft loading radial	125 N						
Max. Permissible shaft loading axial	70 N						

Bearings	
Bearings type	2 precision ball bearings
Nominale service life	3 x 10'8 revs. at 100 % rated shaft load 5 x 10'9 revs. at 40 % rated shaft load 4 x 10'10 revs. at 20 % rated shaft load
Max. operating speed	10000 rpm

Machinery Directive: basic data safety integrity level										
MTTF <sub>d</sub> 200 a										
Mission time (TM)	25 a									
Nominale service life (L10h)	4 x 10'10 revs. at 20 % rated shaft load and 10000 rpm									
Diagnostic coverage (DC)	0 %									

Electrical Data	
Power supply VDC	10 - 30 VDC
Current consumption	typ. 70 mA
Signal shape	square-wave
Output circuit	HTL inverted
Channels	AB, ABN, and inverted signals
Output	push-pull
Load	max. 40 mA / channel
Signal level mA	at 20 mA


Signal level H>	H > Vcc - 2.5 VDC
Signal level L<	L < 2.5 VDC
Output frequency	max. 200 kHz
Circuit protection	yes
Light reserve warning	yes

General Data	
Weight	approx. 230 g
Connections	cable or connector outlet
Protection rating (EN 60529)	Housing: IP65, IP67; shaft sealed: IP65
Operating temperature	Connector: -40 °C up to +85 °C, cable: -20 °C up to +80 °C, (Option ACA: -40 °C up to +85 °C) 1 Vpp: -10 °C up to +70 °C
Storage temperature	Connector: -30 °C up to +85 °C, cable: -30 °C up to +80 °C, option ACA: -40 °C up to +85 °C

More Information	
General technical data and safety instructions http://www.wachendorff-automation.com/gtd	
Options http://www.wachendorff-automation.com/acc	



### WDGI 58A: Cable connection K3, L3, radial, with 2 m cable



Description ABN inv. poss.

K3 radial, shield not connected

Assignments								
	К3							
Circuit	124							
GND	WH							
(+) Vcc	BN							
Α	GN							
В	YE							
N	GY							
Light reserve warning	PK							
A inv.	RD							
B inv.	BK, (BU at ACA)							
N inv.	VT							
Shield	flex							



### Options

Low-friction bearings	Order key
The encoder WDGI 58A is also available as a particularly smooth-running low-friction encoder. The starting torque is thereby changed to 0.25 Ncm and the protection class at the shaft input to IP50.	AAC
Low temperature	Order key
The encoder WDGI 58A with the output circuit types F24, G24, H24, I24, P24, R24, F05, G05, H05, I05, P05, R05, 245, 524, 645 is also available with the extended temperature range -40 °C up to +85 °C [-40 °F up to +185 °F] (measured at the flange).	ACA
Pressure equalising membrane	Order key
The WDGI 58A shaft encoder is also optionally available with a pressure equalising membrane. This prevents water from penetrating into the encoder housing in the case of high air humidity.  The IP67 protection level, temperature range and salt spray resistance are maintained. Resistant to chemicals and solvents in accordance with DIN EN ISO 2812-1.	ACR
Cable length	Order key
The encoder WDGI 58A can be supplied with more than 2 m cable. The maximum cable length depends on the supply voltage and the frequency; see www.wachendorff-automation.com/atd  Please extend the standard order code with a three figure number, specifying the cable length in decimetres.  Example: 5 m cable = 050	XXX = Decimeter



ample Order No.	. Type												
WDGI 58A	WDGI 58A												
	Shaft												
06	06												
	Pulses per	revolution PPR:											
5000	5000						5000						
	0						1						
	Channels:												
ABN	ABN						ABN						
	0						1						
	Output circ		1		ght reserve								
124	Resolution PPR	Power supply VDC	Output circuit	Order key	124								
	up to 5000	10 - 30	HTL inverted	124									
	Electrical c	onnections											
	Description	1		ABI	N inv. poss.	Order key							
K3	Cable: leng	th (2 m standard	, WDG 58T: 1 m)				K3						
	radial, shield	d not connected			•	К3							
	Options			1.									
	Description Order key												
	Low-friction bearings AAC												
	Low temperature ACA												
		lualising membrar	ne		AC		4						
	Cable lengtl				Cable		4						
	Without opti	on			Em	pty							

Example Order No.= WDG	I 58A	06	5000	ABN	124	K3		WDGI 58A	06	5000	ABN	124	K3	Your encoder





For further information please contact our local distributor. Here you find a list of our distributors worldwide. https://www.wachendorff-automation.com/



Wachendorff Automation GmbH & Co. KG Industriestrasse 7 • 65366 Geisenheim Germany

Phone: +49 67 22 / 99 65 25 Fax: +49 67 22 / 99 65 70 E-Mail: wdg@wachendorff.de www.wachendorff-automation.de

