# XMLBS35R2S11

Electromechanical pressure sensor, Pressure sensors XM, switch XMLB 330 mbar, adjustable scale 2 thresholds, 1 C/O





### Main

IVIAIII	
Range of product	OsiSense XM
Product or component type	Electromechanical pressure sensor
Pressure sensor type	Electromechanical pressure sensor
Device short name	XMLB
Pressure rating	0.35 bar
Controlled fluid	Air (0160 °C) Fresh water (0160 °C) Hydraulic oil (0160 °C)
Fluid connection type	G 1/4 (female) conforming to ISO 228
Electrical connection	Screw-clamps terminals, 1 x 0.52 x 2.5 mm <sup>2</sup>
AWG gauge	AWG 20AWG 14
Cable entry	Cable gland 913 mm
Contacts type and composition	1 C/O
Product specific application	30 bar overpressure
Pressure switch type of operation	Regulation between 2 thresholds
Electrical circuit type	Control circuit
Scale type	Adjustable differential
Local display	With
Adjustable range of switching point on rising pressure	0.0420.33 bar
Adjustable range of switching point on falling pressure	0.0090.272 bar
Possible differential maximum at high setting	0.25 bar
Maximum permissible accidental pressure	37.5 bar
Destruction pressure	67.5 bar
Pressure actuator	Diaphragm
Materials in contact with fluid	304L stainless steel FPM, FKM Steel
Enclosure material	Zinc alloy
[In] rated current	3 A, B300, AC-15 (Ue = 120 V) conforming to EN/ IEC 60947-5-1 1.5 A, B300, AC-15 (Ue = 240 V) conforming to EN/ IEC 60947-5-1 0.1 A, R300, DC-13 (Ue = 250 V) conforming to EN/ IEC 60947-5-1

### Complementary

Possible differential minimum at low setting	0.033 bar (- 8 mbar, + 3 mbar)
Possible differential minimum at high setting	0.058 bar (+/- 8 mbar)
Maximum permissible pressure - per cycle	30 bar
Terminal block type	4 terminals
Maximum operating rate	120 cyc/mn

Repeat accuracy	2 %	
[Ui] rated insulation voltage	300 V conforming to UL 508 500 V conforming to EN/IEC 60947-1 300 V conforming to CSA C22.2 No 14	
[Uimp] rated impulse withstand voltage	6 kV EN/IEC 60947-1	
Auxiliary contacts operation	Snap action	
Contacts material	Silver contacts	
Maximum resistance across terminals	25 MOhm conforming to IEC 255-7 category 3 25 mOhm conforming to NF C 93-050 method A	
Short-circuit protection	10 A cartridge fuse, type gG (gl)	
Mechanical durability	2000000 cycles	
Setting	External	
Height	162 mm	
Depth	110 mm	
Width	110 mm	
Net weight	3.5 kg	

### Environment

Standards	UL 508 CE CSA C22.2 No 14
	EN/IEC 60947-5-1
Product certifications	BV
	CCC
	EAC
	LROS (Lloyds register of shipping)
	UL
	CSA
Protective treatment	TC standard version
Ambient air temperature for operation	-2570 °C
Ambient air temperature for storage	-4070 °C
Operating position	Any position
Vibration resistance	4 gn conforming to IEC 60068-2-6 (f = 30500 Hz)
Shock resistance	50 gn conforming to IEC 60068-2-27
Electrical shock protection class	Class I conforming to IEC 1140
	Class I conforming to IEC 536
	Class I conforming to NF C 20-030
IP degree of protection	IP66 conforming to EN/IEC 60529

## Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Weight	2.795 kg	
Package 1 Height	15.5 cm	
Package 1 width	15.5 cm	
Package 1 Length	16 cm	


## Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	☑ REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	₫Yes

Environmental Disclosure	Product Environmental Profile
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Contractual warranty	
Warranty	18 months

# XMLBS35R2S11

### **Dimensions**



Ø a =110 mm / 4.33 in.


- (1) 1 fluid entry, tapped G1/4 (BSP female)
  (2) 1 electrical connections entry, tapped Pg 13.5

# Wiring Diagram


## **Terminal Model**



## **Operating Curves**



- (y)
- Rising pressure Falling pressure Maximum differential (x) 1:
- Minimum differential 2:



- Pressure (y)
- Time (x)
- (1) Adjustable value
- PH: High point
- PB: Below point