

100W FAN COOLED 80W CONVECTION COOLED

The FCB100 is a series of open frame AC-DC power supplies designed for medical devices (including BF), industrial electronics, ITE & household applications. The FCB100 is compliant with class B conducted & radiated emissions, can be used in both class I & class II installations and the wide 80VAC to 264VAC operating input range makes it ideal for both home healthcare applications and in hospital use.

With both convection and fan cooled ratings, extremely low emissions and safety & EMC certification for global use, the FCB100 benefits system designers with easy integration into a wide range of applications across multiple end markets

Features

- 100W fan cooled
- 80W convection cooled
- 4" x 2" footprint, low 1.25" profile
- Class I & Class II applications
- Medical (BF), ITE & household approvals
- Class B conducted & radiated emissions
- Input Range 80 to 264VAC
- < 0.3W no load input power
- Regulated single outputs from 12 to 48VDC
- Short circuit, overvoltage & overload protection
- -25°C to +70°C operating temperature
- 3 year warranty

AC-DC POWER SUPPLIES



Applications







Medical

Household Appliances

Electronics

Dimensions

4.00" x 2.00" x 1.25" (101.6 x 50.8 x 31.8mm)

Models & Ratings

Model number	Output Power	Output Voltage	Convection cooled (40°C)	Convection cooled (50°C)	Fan cooled (10cfm)
FCB100US12		12.0VDC	7.5A	6.7A	8.3A
FCB100US15		15.0VDC	6.0A	5.3A	6.7A
FCB100US19	100W	19.0VDC	4.7A	4.2A	5.3A
FCB100US24		24.0VDC	4.0A	3.5A	4.2A
FCB100US36		36.0VDC	2.6A	2.4A	2.8A
FCB100US48		48.0VDC	2.0A	1.8A	2.1A

Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage	80		264	VAC	Derate from 100% at 90VAC to 90% at 85VAC and 80% at 80VAC
Input Frequency	47		63	Hz	
Input Current - Full Load		1.8/1.1		A rms	115/230VAC full load
No Load Input Power			0.3	W	
Inrush Current			60	А	At 264VAC, cold start 25°C
Earth Leakage Current			270	μΑ	
Input Protection	Internal T3.15A/300VAC fuse fitted in line and neutral				

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Output Voltage	12		48	VDC		
Initial Set Accuracy			1.5	%	At 50% load	
Minimum Load	No minimum	load required				
Line Regulation			±0.5	%	90-264VAC	
Load Regulation			±1	%		
Start Up Delay			2	s		
Start Up Rise Time			50/150	ms	≥0°C/≤10°C	
Overshoot			5	%		
Hold Up Time	8	14		ms	At full load and 115/230VAC	
Transient Response			4	%	Deviation, recovery within 1% in less than 500µs for a 25% load change	
Ripple & Noise			1	%	0°C to 70°C	
Overvoltage Protection	110		150	%Vnom	Recycle input to reset	
Overload Protection	110		175	%		
Short Circuit Protection	Trip and resta	rt (hiccup mo	de)			
Patient Leakage Current			95	μA		
Overtemperature Protection	Measured int	Measured internally, recycle input to reset				
Temperature Coefficient			0.02	%/°C		

General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		87		%	Model dependant
Isolation: Input to Output	4000				2 x MOPP
Input to Ground	1500			VAC	1 x MOPP
Output to Ground	1500				1 x MOPP
Switching Frequency	22		70	kHz	
Power Density			10	W/in³	
Mean Time Between Failure		390		khrs	MIL-HDBK-217F, 25°C GB.
Weight		0.35 (160)		lb (g)	

EMC: Emissions

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Conducted	EN55032, EN55011	Class B		
Radiated	EN55032, EN55011	Class B		
Harmonic Current	EN61000-3-2	Class A		
Voltage Flicker	EN61000-3-3			

EMC: Immunity

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
ITE	EN55024 EN55035 EN55014-2	As below	As below	
ESD Immunity	EN61000-4-2	4	Α	±8kV contact / ±15kV air discharge
Radiated Immunity	EN61000-4-3	3	А	
EFT	EN61000-4-4	3	А	
Surge	EN61000-4-5	Installation class 3	А	
Conducted	EN61000-4-6	3	А	
Magnetic Fields	EN61000-4-8	4	А	
		100% (0VAC) for 8.4ms	А	Pout = 85W
		100% (0VAC) for 16.7ms	В	
	EN61000-4-11	60% (40VAC) for 200ms	В	
	(100VAC/60Hz)	30% (70VAC) for 500ms	А	Pout = 60W
		20% (80VAC) for 5000ms	А	
		100% (0VAC) for 5000ms	В	
	EN61000-4-11 (115VAC/60Hz)	100% (0VAC) for 8.4ms	А	
		100% (0VAC) for 16.7ms	В	
		60% (46VAC) for 200ms	В	
		30% (80VAC) for 500ms	А	Pout = 60W
		20% (92VAC) for 5000ms	А	
		100% (0VAC) for 5000ms	В	
		100% (0VAC) for 10ms	А	
5		100% (0VAC) for 20ms	А	
Dips and Interruptions	EN61000-4-11	60% (96VAC) for 200ms	А	
	(240VAC/50Hz)	30% (168VAC) for 500ms	А	
		20% (192VAC) for 5000ms	А	
		100% (0VAC) for 5000ms	В	
		100% (0VAC) for 10ms	А	Pout = 65W
		100% (0VAC) for 20ms	А	Pout = 40W
	EN60601-1-2	60% (40VAC) for 100ms	А	Pout = 20W
	(100VAC/50Hz)	30% (70VAC) for 500ms	А	Pout = 60W
		100% (0VAC) for 5000ms	В	
		100% (0VAC) for 10ms	А	
		100% (0VAC) for 20ms	А	
	EN60601-1-2 (240VAC/50Hz)	60% (96VAC) for 100ms	А	
	(24UVAC/SUHZ)	30% (168VAC) for 500ms	А	
		100% (0VAC) for 5000ms	В	

Environmental


Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
	-25		+70	°C	Derate linearly from 80W at +50°C to 40W at +70°C (12, 15, 19V models), Convection cooled	
Operating Temperature					Derate linearly from 85W at +50°C to 45W at +70°C (24, 36, 48V models), Convection cooled	
					Derate linearly from 100W at +50°C to 50W at +70°C, Fan cooled	
Storage Temperature	-40		+85	°C		
Cooling	Convection/Fan cooled (see models and ratings)					
Humidity			95	%RH	Non-condensing	
Operating Altitude			4000/5000	m	Medical/ITE and Household	
Shock	$\pm 3 \times 30$ g shocks in each plane, total 18 shocks. 30 g = 11ms (± 0.5 ms) half sine. Conforms to EN60068-2-27 and EN60068-2-47					
Vibration	Single axis 10-500Hz at 2g sweep and endurance at resonance in all 3 planes. Conforms to EN50068-2-6					

Safety Approvals

Certification	Standard	Notes & Conditions
CB Report	IEC60950-1, IEC62368-1, IEC60335	Audio/Video, Information and Communication Technology Equipment, Household and Similar Appliances (report only)
	IEC60601-1	Medical
UL	UL62368-1	Audio/Video, Information and Communication Technology Equipment
	ANSI/AAMI ES60601-1	Medical
EN	EN62368-1	Audio/Video, Information and Communication Technology Equipment - Pending
	EN60601-1	Medical
CE	Meets all applicable directives	
UKCA	Meets all applicable legislation	

Isolation	Standard	Notes & Conditions
Primary to Secondary	2 x MOPP (Means of Patient Protection)	
Primary to Earth	1 x MOPP (Means of Patient Protection) IEC60601-1 Ed.3	
Secondary to Earth	1 x MOPP (Means of Patient Protection)	

Mechanical Details



Input Connector J1				
Function				
N				
No connection				
L				

Output Connector J2				
Function				
Return				
Return				
+Vout				
+Vout				

Pin **Function** 6.35 faston Е

MOLEX series 5194 crimp terminals.

Mates with MOLEX housing 09-50-1031, Mates with MOLEX housing 09-50-1041, MOLEX series 5194 crimp terminals.

Notes:

- 1. Dimensions in inches (mm).
- 2. Weight: 0.35lbs (160g)

3. Tolerances x.xx = ± 0.02 , .xxx = ± 0.010 .

Thermal Considerations

In order to ensure safe operation of the PSU in the most adverse conditions permitted in the end-use equipment, the temperature of the components listed in the table below must not be exceeded. See mechanical drawing for component locations. Temperature should be monitored using K type thermocouples placed on the hottest part of the component (out of direct air flow).

Temperature Measurements at Maximum Ambient 50°C				
Component	Max Temperature °C			
T1	120°C			
C9	90°C			
C19	100°C			
Q1	110°C			
Q2	110°C			