# Product data sheet Characteristics

## XS118BLPAM12

inductive sensor XS1 M18 - L64mm - brass - Sn5mm - 12..24VDC - M12





#### Main

Man		
Range of product	OsiSense XS	
Series name	General purpose	
Sensor type	Inductive proximity sensor	
Sensor name	XS1	;
Sensor design	Cylindrical M18	
Size	64 mm	:
Body type	Fixed	
Enclosure material	Nickel plated brass	
Type of output signal	Discrete	
Wiring technique	3-wire	
[Sn] nominal sensing distance	5 mm	:
Discrete output function	1 NO	
Discrete output type	PNP	
Electrical connection	4 pins M12 male connector	
[Us] rated supply voltage	1224 V DC with reverse polarity protection	
Switching capacity in mA	<= 200 mA with overload and short-circuit protection	
IP degree of protection	IP67 conforming to IEC 60529	

#### Complementary

ISO thread	M18 x 1	<u>a</u>
Detection face	Frontal	. <u>.</u>
Detector flush mounting acceptance	Flush mountable	. <u>w</u>
Material	Metal	
Front material	PBT	
Sensing range	> 48 mm	
Operating zone	04 mm	
Differential travel	115% of Sr	 

Output circuit type	DC
Status LED	1 LED yellow for output state
Supply voltage limits	1036 V DC
Switching frequency	<= 1200 Hz
Voltage drop	<= 2 V at closed state
Current consumption	<= 10 mA at no-load
Delay first up	<= 15 ms
Delay response	<= 0.1 ms
Delay recovery	<= 0.3 ms
Marking	CE
Threaded length	43 mm
Height	18 mm
Length	64 mm
Product weight	0.035 kg

#### Environment

Product certifications	CSA UL	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4085 °C	
Vibration resistance	25 gn amplitude = +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn for 11 ms conforming to IEC 60068-2-27	

### Offer Sustainability


Sustainable offer status	Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0903 - Schneider Electric declaration of conformity	
	Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	
Product environmental profile	Available	
	Product environmental	
Product end of life instructions	Available	
	☑ End of life manual	

#### Contractual warranty

Warranty period	18 months

# XS118BLPAM12

#### **Dimensions**




# Product data sheet Mounting and Clearance

## XS118BLPAM12


## Minimum Mounting Distances

#### Side by side




e (1)  $\geq$  10 mm/0.39 in.

Face to face



e (2) ≥ 60 mm/2.36 in. Facing a metal object



e (3) ≥ 15 mm/0.60 in

## Product data sheet Connections and Schema


## XS118BLPAM12

### Wiring Schemes

#### M12 connector



#### PNP




- 1: (+) 2: Not connected
- 3 : (-) 4 : NO Output

## Product data sheet **Performance Curves**

## XS118BLPAM12

#### Performance Curves

#### Standard Steel Target: 18x18x1 mm



- (1) (2) (y) Pick-up points
- Drop-out points (object approaching from the side)
- Sensing distance in mm