Product data sheet Characteristics

XPSPVT1180

module XPS-PV - hydraulic valves on linear presses - 24 V DC





Main

Range of product	Preventa Safety automation
Product or component type	Preventa safety module
Safety module name	XPSPVT
Safety module application	For dynamic monitoring of hydraulic valves on linear presses
Function of module	Monitoring hydraulic valves
Safety level	Can reach PL e/category 4 conforming to EN/ISO 13849-1 Can reach SILCL 3 conforming to EN/IEC 62061
Safety reliability data	MTTFd = 50.9 years conforming to EN/ISO 13849-1 DC = 099 % conforming to EN/ISO 13849-1 PFHd = 2.24E-8 1/h conforming to EN/IEC 62061
[Us] rated supply voltage	24 V DC - 1010 %
Output type	Relay, 2 NO + 1 NC circuit(s), volt-free
Enclosure type	Removable

Complementary

Maximum power consumption in W	6 W
Breaking capacity	180 VA holding AC-15 C300 relay output
	1800 VA inrush AC-15 C300 relay output
Breaking capacity	1.5 A at 24 V (DC-13) time constant: 50 ms for relay output
Minimum output wiping time	100 ms
[lth] conventional free air thermal current	2.5 A
Associated fuse rating	4 A gG for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum output current	10 mA for relay output
Minimum output voltage	17 V for relay output
Maximum response time on input open	15 ms
[Ui] rated insulation voltage	300 V (pollution degree 2) conforming to IEC 60647-5-1, DIN VDE 0110 part 1
[Uimp] rated impulse withstand voltage	4 kV overvoltage category III conforming to IEC 60647-5-1, DIN VDE 0110 part 1
Local signalling	8 LEDs
Enclosure material	Polycarbonate
Number of terminal blocks	20
Connections - terminals	Captive screw clamp terminals, 2 x 0.52 x 1.5 mm² with cable end
	Captive screw clamp terminals, 2 x 2.5 mm ² without cable end
Mounting support	35 mm symmetrical DIN rail
Depth	118 mm
Height	73 mm
Width	100 mm
Net weight	0.54 kg

Environment

Standards	EN 693 EN 60204-1 EN/IEC 60947-5-1	
Product certifications	CSA UL TÜV	
IP degree of protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529	
Ambient air temperature for operation	-1055 °C	
Ambient air temperature for storage	-2585 °C	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	599.0 g
Package 1 Height	11.3 cm
Package 1 width	13.2 cm
Package 1 Length	8.3 cm
Unit Type of Package 2	S03
Number of Units in Package 2	18
Package 2 Weight	11.55 kg
Package 2 Height	30.0 cm
Package 2 width	30.0 cm
Package 2 Length	40.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	☑ REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EVEU RoHS
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	[™] China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months