# Product data sheet Characteristics

# XS112BLPAM12

inductive sensor XS1 M12 - L55mm - brass - Sn2mm - 12..24VDC - M12





#### Main

-
:
;
:

## Complementary

		7
ISO thread	M12 x 1	4 6
Detection face	Frontal	. <u>.</u>
Detector flush mounting acceptance	Flush mountable	. <u>v</u>
Material	Metal	i i i
Front material	PBT	
Sensing range	> 02.5 mm	
Operating zone	01.6 mm	F
Differential travel	115% of Sr	

DC
1 LED yellow for output state
1036 V DC
<= 2500 Hz
<= 2 V at closed state
<= 10 mA at no-load
<= 15 ms
<= 0.1 ms
<= 0.15 ms
CE
34 mm
12 mm
55 mm
0.015 kg

## Environment

Product certifications	CSA UL	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4085 °C	
Vibration resistance	25 gn amplitude = +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn for 11 ms conforming to IEC 60068-2-27	

## Offer Sustainability

Sustainable offer status	Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0903 - Schneider Electric declaration of conformity	
	Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	
Product environmental profile	Available	
	Product environmental	
Product end of life instructions	Available	
	☑End of life manual	


#### Contractual warranty

Warranty period	18 months	

# Product data sheet Dimensions Drawings

# XS112BLPAM12

## **Dimensions**




# Product data sheet Mounting and Clearance

# XS112BLPAM12


# Minimum Mounting Distances

### Side by side




e (1) ≥ 4 mm/0.16 in.

Face to face



e (2) ≥ 24 mm/0.94 in. Facing a metal object



e (3) ≥ 6 mm/0.24 in.

# Product data sheet Connections and Schema


# XS112BLPAM12

# Wiring Schemes

#### M12 connector



#### PNP




- 1 : (+) 2 : Not connected
- 3 : (-) 4 : NO Output

# Product data sheet Performance Curves

# XS112BLPAM12

### Performance Curves

## Standard Steel Target: 12x12x1 mm



- (1) (2) (y) Pick-up points
- Drop-out points (object approaching from the side) Sensing distance in mm